

HDMI Over Cat5 / Cat6 Extender, Receiver for Video and Audio, 1920x1200 1080p at 60Hz

MODEL NUMBER: **B126-1P0**



Description

The B126-1P0 is a receiver unit that is used with the [B126-002](#) and [B126-004](#) transmitter units. It extends a 1080p (60Hz) signal to a monitor up to 50 ft. away using Cat5e/6 cable. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) No power is required, and its built-in HDMI male connector plugs directly into a monitor without the need for an additional cable. Supports 24-bit True Color (8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*).

Installation is simple. Connect the transmitter unit to an HDMI source using a Tripp Lite P568-Series HDMI cable (not included). Connect the built-in HDMI connector on the receiver unit directly to a display. Finally, connect the receiver to the RJ45 port on the transmitter using a single Cat5e/6 cable.

- A 1080p (60Hz) signal can be transmitted up to 50 ft.
- A 1080i (60Hz) signal can be transmitted up to 100 ft.
- Cannot be used for a 3D signal

Features

- For use with [B126-002](#) and [B126-004](#) transmitter units.
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, is required to achieve maximum distance and resolution.
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source.
- HDCP and 3D compatible.
- Compatible with both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*).
- Supports 24-bit True Color (8-bits per channel).
- No external power required.
- Compatible with all operating systems.
- Plug and play; No drivers required.

Highlights

- For use with the [B126-002](#) and [B126-004](#) transmitter units
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*)
- Supports 24-bit True Color (8-bits per channel)
- No external power required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-1P0 HDMI Over Cat5 Passive Extender Remote Unit
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Specifications

| General Info | |
|-------------------------------------|---------------------------------|
| Product Group | SPLITTERS, SWITCHES & EXTENDERS |
| OVERVIEW | |
| Cable Type | CAT5/CAT5E |
| Display Style | Splitter |
| Model Type | HDMI |
| PHYSICAL | |
| Color | Black |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0 to 40 C (32 to 104 F) |
| Storage Temperature Range | -20 to 60 C (-4 to 140 F) |
| Relative Humidity | 20 to 90% |
| CONNECTIONS | |
| Connector A | RJ45 (FEMALE) |
| Connector B | HDMI (MALE) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.