



Buck Chopper with Trench Power MOSFET and Schottky Diode

in ISOPLUS i4-PAC™

Preliminary data



MOSFET		
Symbol	Conditions	Maximum Ratings
V_{DSS}	$T_{VJ} = 25^{\circ}\text{C to } 150^{\circ}\text{C}$	55 V
V_{GS}		± 20 V
I_{D25}	$T_C = 25^{\circ}\text{C}$	100 A
I_{D90}	$T_C = 90^{\circ}\text{C}$	80 A

Symbol	Conditions	Characteristic Values ($T_{VJ} = 25^{\circ}\text{C}$, unless otherwise specified)		
		min.	typ.	max.
R_{DSon}	$V_{GS} = 10\text{ V}; I_D = I_{D90}$		5.7	7.2 m Ω
V_{GSth}	$V_{DS} = 20\text{ V}; I_D = 1\text{ mA}$	2		4 V
I_{DSS}	$V_{DS} = 55\text{ V}; V_{GS} = 0\text{ V}; T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 125^{\circ}\text{C}$		0.1	0.01 mA mA
I_{GSS}	$V_{GS} = \pm 20\text{ V}; V_{DS} = 0\text{ V}$			0.1 μA
Q_g Q_{gs} Q_{gd}	$V_{GS} = 10\text{ V}; V_{DS} = 14\text{ V}; I_D = 50\text{ A}$		100 22 36	nC nC nC
$t_{d(on)}$ t_r $t_{d(off)}$ t_f	$V_{GS} = 10\text{ V}; V_{DS} = 30\text{ V}$ $I_D = 25\text{ A}; R_G = 10\ \Omega$		35 115 230 155	ns ns ns ns
R_{thJC} R_{thJH}	with heat transfer paste		1.5	1 K/W K/W

Features

- trench MOSFET
 - very low on state resistance R_{DSon}
 - fast switching
- Schottky diode
 - low forward voltage drop
 - fast switching
- ISOPLUS i4-PAC™ package
 - isolated back surface
 - low coupling capacity between pins and heatsink
 - enlarged creepage towards heatsink
 - application friendly pinout
 - low inductive current path
 - high reliability
 - industry standard outline
 - UL registered, E 72873

Applications

- automotive
 - choppers - replacing series resistors for DC drives, heating etc.
 - control of SR drives
 - DC-DC converters
 - electronic switches -replacing relays and fuses
- power supplies
 - DC-DC converters
 - solar inverters
- battery supplied systems
 - choppers for drives in hand held tools
 - battery chargers

Schottky Diode

Symbol	Conditions	Maximum Ratings		
V _{RRM}	T _{VJ} = 25°C to 150°C	45	V	
I _{F25}	T _C = 25°C	110	A	
I _{F90}	T _C = 90°C	80	A	
Symbol	Conditions	Characteristic Values		
		min.	typ.	max.
V _F	I _F = 50 A; T _{VJ} = 25°C T _{VJ} = 125°C		0.7	0.9 V V
I _R	V _R = V _{RRM} ; T _{VJ} = 25°C T _{VJ} = 125°C		1	0.5 mA mA
R _{thJC}	with heat transfer paste	1.9		1.5 K/W
R _{thJH}				K/W

Component

Symbol	Conditions	Maximum Ratings	
I_{RMS}	per pin	75	A
T_{VJ}		-55...+175	°C
T_{stg}		-55...+125	°C
V_{ISOL}	$I_{\text{ISOL}} \leq 1 \text{ mA}; 50/60 \text{ Hz}$	2500	V~
F_{c}	mounting force with clip	20...120	N

Symbol	Conditions	Characteristic Values		
		min.	typ.	max.
C_{p}	coupling capacity between shorted pins and mounting tab in the case		40	pF
$d_{\text{S}}, d_{\text{A}}$	pin - pin	1.7		mm
$d_{\text{S}}, d_{\text{A}}$	pin - backside metal	5.5		mm
Weight			9	g

Dimensions in mm (1 mm = 0.0394")

