








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0	AL1	REVISED	PER ECO-11-004820	11MAR11	RK	HMR



- WIRE RANGE: 0.5–2mm² (20–14 AWG).
- INSULATION RANGE: 3.56 [.140] MAX. DIA.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 0.00076 [.000030] MIN GOLD STRIPE OVER 0.00127 [.000050] MIN NICKEL ON INSIDE OF SOCKET.



METRIC

PRE-TIN	0.25 [.010] PHOS BRZ	350415-6
	0.25 [.010] BRASS	350415-5
PRE-TIN	0.25 [.010] BRASS	350415-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 22NOV2005	TE Connectivity			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK D. COLEY 22NOV2005				
	0 PLC ± -	APVD D. COLEY 22NOV2005	NAME .093 SOCKET			
	1 PLC ± -	PRODUCT SPEC	COMMERICAL PIN AND SOCKET			
	2 PLC ± -	APPLICATION SPEC	-			
	3 PLC ± 0.13 [.005]	WEIGHT	A1 00779C=350415			
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV AL1	RESTRICTED TO -