

SEE TABLE

68046 - XXX - LF


—LEAD FREE OPTION

- PACKAGING OPTION NOTE 6.0 MIT IF NOT REQUIRED


-NO OF POSITIONS PER ROW

-PLATING CODE

-BASE PART NUMBER



VACUUM CAP FOR
TAPE & REEL PACKAGING
OPTION. NOTE 8



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX			
litr ecn nodr date				tolerances unless otherwise specified						title			
AV N-005264 SH 2011-8-23				angles		XX±.01/XX±.3		INCH/MM		SMT DOUBLE ROW			
AN V04-0986 DAI 10/13/04				lineal		~XXX±0.005/XXX±.13				VCC ASSEMBLY			
AP V04-1003 DAI 10/25/04				0'±2"		XXXXX.0020/XXXX.05		scale 1:1					
AR V05-0463 DPU 06/28/05				dr J. SHREINER		11/07/90				dwg no sheet# of 5 size			
AS M07-0143 ERE 03/03/07				engr M. HAHN		11/07/90				68046 A3			
AT M07-0203 AGS 5/02/07				chr M. HAHN		11/07/90							
AU M08-0065 MHT 3/04/05				appd M. HAHN		11/07/90				type Product Customer Drawing			
sheet revision		AV AV AV AV AV											
index sheet		1 2 3 4 5											

PRODUCT NUMBER NOTE 15	PLATING CONTACT AREA	PLATING SOLDER TAIL	MATERIAL REF
68046-2XX	15μ"/.38μ Au OR GXT MIN OVER 50μ"/1.27μ Ni MIN	100μ"/160μ" 2.54μ"/4.06μ" SN	NOTE 3&4
68046-3XX	30μ"/.76μ Au OR GXT MIN OVER 50μ"/1.27μ Ni MIN	100μ"/160μ" 2.54μ"/4.06μ" SN	NOTE 3&4
68046-4XX	100μ"/2.54 SN MIN OVER 50μ"/1.27μ Ni MIN	100μ"/160μ" 2.54μ"/4.06μ" SN	NOTE 3,4&17
68046-6XX	30μ"/.76μ Au OR GXT MIN OVER 50μ"/1.27μ Ni MIN	100μ"/160μ" 2.54μ"/4.06μ" SN	NOTE 3&4
68046-8XX	30μ"/.76μ Au MIN OVER 50μ"/1.27μ Ni MIN	200μ"/5.08μ SL MIN	NOTE 3&4

OBSOLETE




FIGURE A
TOP ENTRY
.025/.64 SQ PIN





FIGURE B
BOTTOM ENTRY (THROUGH PWB)
.025/.64 SQ PIN

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family DUBOX	
l'tecn nodr date		tolerances unless otherwise specified		angles 0°±2'		linea XXX±.01/XX±.3 XXX±.005/XX±.13 XXX±.0020/XXX±.05		title SMT DOUBLE ROW VCC ASSEMBLY	
AV								dwg no 68046	
		dr J. SHREINER		11/07/90				sheet 2 of 5	
		enr M. HAHN		11/07/90				size A3	
		chr M. HAHN		11/07/90					
		appd M. HAHN		11/07/90				type Product Customer Drawing	
sheet index		revision sheet							

VACUUM PICK-UP CAP
CENTRALLY LOCATED

DUBOX VERTICAL RECEPTACLE
DOUBLE ROW



TAPE AND REEL PACKAGING

SEE NOTE 7

NOTES:

- ①. TERMINAL MATERIAL: PHOSPHOR BRONZE.
EXTRA HARD
2. RECOMMENDED APPLICATION DATA:
 - A. RECOMMENDED SOLDER PAD PATTERN IS SHOWN IN FIGURE A & B.
 - B. ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF
ON GIVEN TERMINAL SPACING WITHIN .015/.38 DIA.
 - C. SUGGESTED MATING PIN LENGTH .210±.010 [5.33±.51]
- ③. HOUSING MATERIAL: P.P.S. FILLED.
FLAME RETARDANT PER UL-94-V0.
COMPATIBLE WITH INFRA-RED SOLDERING.
COLOR: BLACK
PART WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE
FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR
VAPOR PHASE SOLDER PROCESS.
- ④. PRESTAMPED POST PLATED TERMINAL.
5. FCI, FCI FINAL PART NUMBER AND DATE CODE
TO BE MARKED ON TUBE LABEL.
6. ADD SUFFIX 'P' TO DASH NUMBER AS FOURTH DIGIT FOR TAPE & REEL
PACKAGING.
- ⑦. TAPE AND REEL PACKAGING PER GES-14-334.
- ⑧. VACUUM CAP MATERIAL: L.C.P., FLAME RETARDANT UL 94 V-0.
COLOR : BLACK
CAP IS USED WITH TAPE AND REEL PACKAGING.
CAP IS TO BE CENTRALLY LOCATED ON PART.
9. TAPE AND REEL PACKAGING FOR 24mm WIDE AND BELOW HAVE PILOT HOLES ON
ONE SIDE OF TAPE ONLY. SIZES ABOVE 24mm HAVE PILOT HOLES ON BOTH
OF TAPE.
- ⑩. TAPE & REEL PACKAGING 24mm AND 32mm TAPE WIDTH, WITH 112mm POCKET
PITCH.
11. MAXIMUM LENGTH OF CONNECTOR FOR TAPE AND REEL PACKAGING IS 2.50
LONG /63.5mm
- ⑫. PART NUMBER WITH SUFFIX "U" IS FOR SAWING PURPOSES ONLY.
13. STANDARD TUBE PACKAGE PER BUS-14-097/3.
- ⑭. TAPE & REEL PACKAGING 72mm TAPE WIDTH WITH 16mm POCKET PITCH.
- ⑮. ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION
16. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑰. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT
ENVIRONMENTS".

mat'l. code	surface	tolerance	projection	product family
	ISO 1302 ✓	ISO 406 ISO 1101		DUBOX
ltr ecn nodr date	tolerances unless otherwise specified			title
AV	angles	linear	INCH/MM	SMT DOUBLE ROW VCC ASSEMBLY
	0°±2°	linear	scale 1:1	
	dr J. SHREINER 11/07/90	engr M. HAHN 11/07/90		dwg no 68046
	chr M. HAHN 11/07/90	appr M. HAHN 11/07/90		sheet 3 of 5
sheet index	revision sheet			size A3
				type Product Customer Drawing

1

2

3

4

5

6

PRODUCT NUMBER

NO. OF POS.

C DIM

D DIM

TAPE & REEL PACKAGING

LF OPTION

68046-Y02

2 X 2

.100/2.540

.217/5.511

NO

-Y03

2 X 3

.200/5.080

.317/8.051

NO

-Y04

2 X 4

.300/7.620

.417/10.591

NO

-Y05

2 X 5

.400/10.160

.517/13.131

NO

-Y06

2 X 6

.500/12.700

.617/15.671

NO

-Y07

2 X 7

.600/15.240

.717/18.211

NO

-Y08

2 X 8

.700/17.780

.817/20.751

NO

-Y09

2 X 9

.800/20.320

.917/23.291

NO

-Y10

2 X 10

.900/22.860

1.017/25.831

NO

-Y11

2 X 11

1.000/25.400

1.117/28.371

NO

-Y12

2 X 12

1.100/27.940

1.217/30.911

NO

-Y13

2 X 13

1.200/30.480

1.317/33.451

NO

-Y14

2 X 14

1.300/33.020

1.417/35.991

NO

-Y15

2 X 15

1.400/35.560

1.517/38.531

NO

-Y16

2 X 16

1.500/38.100

1.617/41.071

NO

-Y17

2 X 17

1.600/40.640

1.717/43.611

NO

-Y18

2 X 18

1.700/43.180

1.817/46.151

NO

-Y19

2 X 19

1.800/45.720

1.917/48.691

NO

-Y20

2 X 20

1.900/48.260

2.017/51.231

NO

-Y21

2 X 21

2.000/50.800

2.117/53.771

NO

-Y22

2 X 22

2.100/53.340

2.217/56.311

NO

-Y23

2 X 23

2.200/55.880

2.317/58.851

NO

-Y24

2 X 24

2.300/58.420

2.417/61.391

NO

68046-Y25

2 X 25

2.400/60.960

2.517/63.931

NO

NOTE 15

FCI

FCIconnect.com

Copyright FCI

mat'l. code

surface
ISO 1302 ✓

tolerance
ISO 406
ISO 1101

projection
INCH/MM

product family
DUBOX

ltr ecn nodr date

tolerances unless otherwise specified

title
SMT DOUBLE ROW
VCC ASSEMBLY

AV

angles

linea

XXXX±.01/XX±.3

XXXX±.005/XX±.13

XXXX±.0020/XXX±.05

scale 1:1

dwg no
68046

sheet # of 5
A3

dr J. SHREINER 11/07/90

engr M. HAHN 11/07/90

chr M. HAHN 11/07/90

appd M. HAHN 11/07/90

type Product Customer Drawing

sheet index

revision sheet

41

STATUS Released

Printed: Aug 24, 2011

Copyright FCI

FCIconnect.com

FCI

1

2

3

4

5

6

PROD. NUMBER	NO. POSI.	C DIM	D DIM	TAPE & REEL PACKAGING	LF OPTION
68046-Y26	2 X 26	2.500/63.500	2.617/66.471	NO	NOTE 15
↑ -Y27	2 X 27	2.600/66.040	2.717/69.011	NO	
-Y28	2 X 28	2.700/68.580	2.817/71.551	NO	
-Y29	2 X 29	2.800/71.120	2.917/74.091	NO	
-Y30	2 X 30	2.900/73.660	3.017/76.631	NO	
-Y31	2 X 31	3.000/76.200	3.117/79.171	NO	
-Y32	2 X 32	3.100/78.740	3.217/81.711	NO	
-Y33	2 X 33	3.200/81.280	3.317/84.251	NO	
-Y34	2 X 34	3.300/83.820	3.417/86.791	NO	
-Y35	2 X 35	3.400/86.360	3.517/89.331	NO	
-Y36	2 X 36	3.500/88.900	3.617/91.871	NO	
-Y37	2 X 37	3.600/91.440	3.717/94.411	NO	
-Y38	2 X 38	3.700/93.980	3.817/96.951	NO	
-Y39	2 X 39	3.800/96.520	3.917/99.491	NO	
-Y40	2 X 40	3.900/99.060	4.017/102.031	NO	
-Y41	2 X 41	4.000/101.600	4.117/104.571	NO	
-Y42	2 X 42	4.100/104.140	4.217/107.111	NO	
-Y43	2 X 43	4.200/106.680	4.317/109.651	NO	
-Y44	2 X 44	4.300/109.220	4.417/112.191	NO	
-Y45	2 X 45	4.400/111.760	4.517/114.731	NO	
-Y46	2 X 46	4.500/114.300	4.617/117.271	NO	
-Y47	2 X 47	4.600/116.840	4.717/119.811	NO	
-Y48	2 X 48	4.700/119.380	4.817/122.351	NO	
-Y49	2 X 49	4.800/121.920	4.917/124.891	NO	
-Y50	2 X 50	4.900/124.460	5.017/127.431	NO	
-Y50U	2 X 50	4.900/124.460	5.017/127.431	NO	
-Y03P	2 X 3	0.200/5.080	0.317/8.051	YES	
-Y04P	2 X 4	0.300/7.620	0.417/10.592	YES	
↓ -Y05P	2 X 5	0.400/10.160	0.517/13.131	YES	
68046-Y06P	2 X 6	0.500/12.700	0.617/15.671	YES	
68046-Y07P	2 X 7	0.600/15.240	0.717/18.211	YES	
68046-Y12P	2 X 12	1.100/27.94	1.217/30.91	YES	
68046-Y13P	2 X 13	1.200/30.48	1.317/33.45	YES	
68046-Y20P	2 X 20	1.900/48.260	2.017/51.231	YES	

NOTE 12

NOTE 6 & 9

NOTE 6 & 10

NOTE 6 & 10

NOTE 6 & 10

NOTE 6 & 10

NOTE 6 & 9 — OBSOLETE

NOTE 6 & 14

NOTE 6 & 14

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302 ✓		ISO 406 ISO 1101				DUBOX	
ltr ecn nodr date		tolerances unless otherwise specified						title	
AV		angles	linear	XX±.01/XX±.3		INCH/MM		SMT DOUBLE ROW VCC ASSEMBLY	
		0°±2°		XXX±.0005/XXX±.13		scale 1:1			
		dr	J. SHREINER	11/07/90				dwg no	
		engr	M. HAHN	11/07/90				shee5 of5 size	
		chr	M. HAHN	11/07/90				68046 A3	
		appd	M. HAHN	11/07/90				type Product Customer Drawing	
sheet	revision								
index	sheet								

FCI

Copyright FCI

Form A3

1

2

3

4

5

6

PDS: Rev :AV

STATUS: Released

Printed: Aug 24, 2011