




FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code SEE NOTE 3					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC										
ltr	ecn	no	dr	date	tolerances unless otherwise specified						title	4 ROW R/A HEADER SOLDER TO BOARD, 0 G.P.									
J	V90523	HTB	3/1/99	angles	linear	.XX±.01/.3	INCH/MM														
K	V00262	JWS	1/26/00			.XXX±.005/.13															
L	V05-0740	DAI	10/7/05	0'±2'		.XXXX±.0020/.051	scale 1:1														
M	V05-1040	HTB	11/14/05	dr	D.SHEAFFER	6/5/91			dwg no	sheet 1 of 3	size										
N	M06-0283	MHT	7/27/06	enrg	S.CLARK	6/5/91			50122	A3											
				chr	S.CLARK	6/5/91															
				appd	S.CLARK	6/5/91			type	Product	Customer	Drawing									
sheet		revision		N	N	N															
index		sheet		1	2	3															


form: A3





FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE



SECTION U-U



SECTION X-X


mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ec	n	dr	date	tolerances unless otherwise specified	scale 1:1 FCI	title 4 ROW R/A HEADER SOLDER TO BOARD, 0 G.P.
N					angles linear .XX±.01/.3		dwg no 50122 sheet 2 of 3 size A3
					0'±2' .XXX±.005/.13		
					.XXXX±.0020/.051		
			dr	D.SHEAFFER	6/5/91		
			enr	S.CLARK	6/5/91		
			chr	S.CLARK	6/5/91		
			appd	S.CLARK	6/5/91		
sheet index	revision sheet						type Product Customer Drawing

form: A3


PRODUCT NUMBER	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH REF.	TERMINAL PLATING
50122 -1YYYY	YYY	.180/4.57	30μ"/.76μ GOLD
50122 -1YYYJ	YYY	.120/3.05	30μ"/.76μ GOLD
50122 -3YYYY	YYY	.180/4.57	50μ"/1.27μ GOLD
50122 -3YYYJ	YYY	.120/3.05	50μ"/1.27μ GOLD
50122 -5YYYY	YYY	.180/4.57	30μ"/.76μ GXT
50122 -5YYYYLF	YYY	.180/4.57	30μ"/.76μ GXT
50122 -5YYYJ	YYY	.120/3.05	30μ"/.76μ GXT
50122 -5YYYJLF	YYY	.120/3.05	30μ"/.76μ GXT

NOTES:

1. PRODUCT NUMBERING CODE:



PRODUCT NUMBERING CODE FOR SELECT LOAD PART NUMBERS:



- THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 100 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6,7,8,9,.....98,99,100.
- HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
- LENGTH FORMULAS:
DIM "A" = .100/2.54 x NO. OF COLUMNS + .75/19.1
DIM "B" = .100/2.54 x NO. OF COLUMNS + .450/11.43
DIM "C" = .100/2.54 x NO. OF COLUMNS - .100/2.54

- THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecr	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
N					angles linear .XX±.01/.3	scale 1:1	4 ROW R/A HEADER
					0'±2' .XXX±.005/.13		SOLDER TO BOARD, 0 G.P.
					dr D.SHEAFFER 6/5/91		dwg no sheet 3 of 3 size
					enr S.CLARK 6/5/91		50122 A3
					chr S.CLARK 6/5/91		type Product Customer Drawing
					appd S.CLARK 6/5/91		
sheet index	revision sheet						

form: A3