

PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

ELFA artikelnr

48-379-02 Koppl plint 2-pol	CUU 10/2 NU
48-379-10 Koppl plint 3-pol	CUU 10/3 NU
48-379-28 Koppl plint 2-pol	CUU 5/2 NU
48-379-36 Koppl plint 3-pol	CUU 5/3 NU
48-379-44 Koppl plint 4-pol	CUU 5/4 NU
48-379-51 Koppl plint 5-pol	CUU 5/5 NU
48-379-69 Koppl plint 6-pol	CUU 5/6 NU
48-379-77 Koppl plint 7-pol	CUU 5/7 NU
48-379-85 Koppl plint 8-pol	CUU 5/8 NU
48-379-93 Koppl plint 10-pol	CUU 5/10 NU

48-382-15 Koppl plint 2-pol vinklad	CUU 5/2 SQ NU
48-382-23 Koppl plint 3-pol vinklad	CUU 5/3 SQ NU
48-382-31 Koppl plint 4-pol vinklad	CUU 5/4 SQ NU
48-382-49 Koppl plint 5-pol vinklad	CUU 5/5 SQ NU
48-382-80 Koppl plint 6-pol vinklad	CUU 5/6 SQ NU



**MORSETTIERE PER C.S.
TERMINAL BLOCKS FOR P.C.B.
BARRETTES DE CONNEXION POUR C.I.
ANSCHLUßKLEMMEN FÜR LEITERPLATTE**

TIPO
TYPE
TYPE
TYP



CUU

PASSO
PITCH
PAS
RASTERMAß

5 10 mm




CUU 5/...



P	L mm
5	5 x p
10	10 x p-5

CUU 5/...SQ



MODULI
A CARRELLO

RISING CLAMP
MODULES

BORNE ETRIEZ MOBILE

BEWEGLICHER
KLEMMKÖRPER
ANREIHBAR



Corpo isolante Grigio	Insulating body Grey	Corps isolant Gris	Isolierkörper Grau	PC UL94VO
Vite	Screw	Vis	Schraube	M2,5-CB15+Zn
Morsetto	Clamp	Borne	Klemmkörper	C60+Zn
Contatto	Pin	Contacte	Kontakt	CuZn37+Ni+Sn
Coppia di torsione	Testing torque	Couple de serrage	Zul. Drehmoment	0,5 Nm
Sezione	Section	Section	Querschnitt	2,5 mm ²
Vite imperdibile	Captive screw	Vis imperdable	Schraube unvelierbar	-
Foro di montaggio	P.C.B. mounting hole	Perçage C. I.	Leiterplattenbohrung	Ø 1,3 mm
Corrente nominale	Nominal current	Courant nominal	Strombelastbarkeit	24 A
Tensione	Voltage	Tension	Betriebsspannung	450/750 V
Temperatura	Temperature	Température	Temperatur	85°C
Grado di protezione	Protection index	Degré de protection	Schutzklasse	IP00
Resistenza di isolamento	Insulation resistance	Résistance d'isolement	Isolationswiderstand	≥ 5 MΩ
Rigidità dielettrica	Dielectric strength	Rigidité diélectrique	Durchschlagsfestigkeit	≥ 2500 Vac/60"

Ref. EN 60998-1

SCHEMA
PER ORDINAZIONE

ORDER
SCHEME

TABLEAU
DE COMMANDE

BESTELLSCHHEMA

P	p	
Passo	N° di Poli	Numerazione
Pitch	Nr. of Poles	Printing
Pas	Nb. Pôles	Marquage
Rastermaß	Polzahl	Bedruckung

CUU

5
10
MIN 1÷ MAX 36
MIN 2÷ MAX 18

Pin 90°

SQ

NU