





Snap-in Terminal Type, 105°C Low-Profile Sized  
series




- Withstanding 3000 hours application of rated ripple current at 105°C.
- Ideally suited for flat design for switching power supply.
- Addition of 450V rated voltage.
- Compliant to the RoHS directive (2011/65/EU).

## Specifications

| Item                          | Performance Characteristics                                                                                                                                                                                                 |                 |           |                                       |                                                   |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------|---------------------------------------|---------------------------------------------------|
| Category Temperature Range    | − 40 to +105°C (200 ・ 250V) , − 25 to +105°C (400 ・ 450V)                                                                                                                                                                   |                 |           |                                       |                                                   |
| Rated Voltage Range           | 200 to 450V                                                                                                                                                                                                                 |                 |           |                                       |                                                   |
| Rated Capacitance Range       | 47 to 680μF                                                                                                                                                                                                                 |                 |           |                                       |                                                   |
| Capacitance Tolerance         | ± 20% at 120Hz, 20°C                                                                                                                                                                                                        |                 |           |                                       |                                                   |
| Leakage Current               | 3√CV (μA) (After 5 minutes' application of rated voltage) [C : Rated Capacitance (μF) V : Voltage (V)]                                                                                                                      |                 |           |                                       |                                                   |
| Tangent of loss angle (tan δ) | Rated voltage(V)                                                                                                                                                                                                            | 200 to 400      | 450       | Measurement frequency : 120Hz at 20°C |                                                   |
|                               | tan δ (MAX.)                                                                                                                                                                                                                | 0.15            | 0.20      |                                       |                                                   |
| Stability at Low Temperature  | Measurement frequency : 120Hz                                                                                                                                                                                               |                 |           |                                       |                                                   |
|                               | Rated voltage(V)                                                                                                                                                                                                            |                 | 200 ・ 250 | 400 ・ 450                             |                                                   |
|                               | Impedance ratio ZT/Z20(MAX.)                                                                                                                                                                                                | Z − 25°C/Z+20°C | 3         | 8                                     |                                                   |
| Z − 40°C/Z+20°C               |                                                                                                                                                                                                                             | 12              | —         |                                       |                                                   |
| Endurance                     | The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 3000 hours at 105°C, the peak voltage shall not exceed the rated voltage. |                 |           | Capacitance change                    | Within ±20% of the initial capacitance value      |
|                               |                                                                                                                                                                                                                             |                 |           | tan δ                                 | 200% or less than the initial specified value     |
|                               |                                                                                                                                                                                                                             |                 |           | Leakage current                       | Less than or equal to the initial specified value |
| Shelf Life                    | After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the requirements listed at right.                        |                 |           | Capacitance change                    | Within ±15% of the initial capacitance value      |
|                               |                                                                                                                                                                                                                             |                 |           | tan δ                                 | 150% or less than the initial specified value     |
|                               |                                                                                                                                                                                                                             |                 |           | Leakage current                       | Less than or equal to the initial specified value |
| Marking                       | Printed with white color letter on black sleeve.                                                                                                                                                                            |                 |           |                                       |                                                   |


Since rating other than the above can be manufactured a please ask for detail.

## Drawing



※ The other terminal is also available upon request.  
Please refer to page 326 for schematic of terminal dimensions.

## Type numbering system (Example : 400V 120µF)



## Frequency coefficient of rated ripple current

| Frequency (Hz) | 50          | 60   | 120  | 300  | 1 k  | 10k  | 50k or more |
|----------------|-------------|------|------|------|------|------|-------------|
| Coeff.         | 200 to 250V | 0.81 | 0.85 | 1.00 | 1.17 | 1.32 | 1.45        |
|                | 400 to 450V | 0.77 | 0.82 | 1.00 | 1.16 | 1.30 | 1.41        |

Minimum order quantity : 50pcs.



# Dimensions

| 200V(2D)           |                                 |                      |                         |                |
|--------------------|---------------------------------|----------------------|-------------------------|----------------|
| Cap.<br>( $\mu$ F) | Size<br>$\phi$ D $\times$ L(mm) | Rated ripple<br>(mA) | Leakage Current<br>(mA) | Code           |
| 180                | 20 $\times$ 20                  | 680                  | 0.56                    | LGJ2D181MELY20 |
| 220                | 22 $\times$ 20                  | 760                  | 0.62                    | LGJ2D221MELZ20 |
| 270                | 22 $\times$ 20                  | 780                  | 0.69                    | LGJ2D271MELZ20 |
| 330                | 25 $\times$ 20                  | 960                  | 0.77                    | LGJ2D331MELA20 |
| 390                | 30 $\times$ 20                  | 1080                 | 0.83                    | LGJ2D391MELB20 |
| 470                | 30 $\times$ 20                  | 1120                 | 0.91                    | LGJ2D471MELB20 |
| 560                | 35 $\times$ 20                  | 1440                 | 1.00                    | LGJ2D561MELC20 |
| 680                | 35 $\times$ 20                  | 1520                 | 1.10                    | LGJ2D681MELC20 |

| 250V(2E)           |                                 |                      |                         |                |
|--------------------|---------------------------------|----------------------|-------------------------|----------------|
| Cap.<br>( $\mu$ F) | Size<br>$\phi$ D $\times$ L(mm) | Rated ripple<br>(mA) | Leakage Current<br>(mA) | Code           |
| 150                | 20 $\times$ 20                  | 660                  | 0.58                    | LGJ2E151MELY20 |
| 180                | 22 $\times$ 20                  | 750                  | 0.63                    | LGJ2E181MELZ20 |
| 220                | 25 $\times$ 20                  | 920                  | 0.70                    | LGJ2E221MELA20 |
| 270                | 30 $\times$ 20                  | 1040                 | 0.77                    | LGJ2E271MELB20 |
| 330                | 30 $\times$ 20                  | 1080                 | 0.86                    | LGJ2E331MELB20 |
| 390                | 35 $\times$ 20                  | 1410                 | 0.93                    | LGJ2E391MELC20 |
| 470                | 35 $\times$ 20                  | 1470                 | 1.02                    | LGJ2E471MELC20 |

| 400V(2G)           |                                 |                      |                         |                |
|--------------------|---------------------------------|----------------------|-------------------------|----------------|
| Cap.<br>( $\mu$ F) | Size<br>$\phi$ D $\times$ L(mm) | Rated ripple<br>(mA) | Leakage Current<br>(mA) | Code           |
| 56                 | 20 $\times$ 20                  | 550                  | 0.44                    | LGJ2G560MELY20 |
| 68                 | 22 $\times$ 20                  | 620                  | 0.49                    | LGJ2G680MELZ20 |
| 82                 | 25 $\times$ 20                  | 700                  | 0.54                    | LGJ2G820MELA20 |
| 100                | 25 $\times$ 20                  | 760                  | 0.60                    | LGJ2G101MELA20 |
| 120                | 30 $\times$ 20                  | 860                  | 0.65                    | LGJ2G121MELB20 |
| 150                | 30 $\times$ 20                  | 900                  | 0.73                    | LGJ2G151MELB20 |
| 180                | 35 $\times$ 20                  | 1160                 | 0.80                    | LGJ2G181MELC20 |
| 220                | 35 $\times$ 20                  | 1210                 | 0.88                    | LGJ2G221MELC20 |

| 450V(2W)           |                                 |                      |                         |                |
|--------------------|---------------------------------|----------------------|-------------------------|----------------|
| Cap.<br>( $\mu$ F) | Size<br>$\phi$ D $\times$ L(mm) | Rated ripple<br>(mA) | Leakage Current<br>(mA) | Code           |
| 47                 | 20 $\times$ 20                  | 520                  | 0.43                    | LGJ2W470MELY20 |
| 56                 | 22 $\times$ 20                  | 600                  | 0.47                    | LGJ2W560MELZ20 |
| 68                 | 25 $\times$ 20                  | 670                  | 0.52                    | LGJ2W680MELA20 |
| 82                 | 25 $\times$ 20                  | 740                  | 0.57                    | LGJ2W820MELA20 |
| 100                | 30 $\times$ 20                  | 830                  | 0.63                    | LGJ2W101MELB20 |
| 120                | 30 $\times$ 20                  | 870                  | 0.69                    | LGJ2W121MELB20 |
| 150                | 35 $\times$ 20                  | 1170                 | 0.77                    | LGJ2W151MELC20 |

Rated ripple current (mA<sub>rms</sub>) at 105°C 120Hz