

V3L-3003-D8

CATALOG LISTING

PAGE 1 OF 1

REPLACES

PR-1056

RELEASE NO.

M

ISSUE

17

CHECK

29APR05

AK

CHECK

9 OCT 98

J A F

CHECK

9 OCT 98

CHECK

9 OCT 98


T S M

DRAWN

FORMTEK

REVISIONS

A	CO	92173
	TSM	9 OCT 98
B	0012902	
	KR	29APR05




NOTES

- 1 - SWITCH MATERIALS WILL WITHSTAND TEMPERATURE OF 302°F
- 2 - CAUTION: OVERTRAVEL FORCE ON LEVER MUST NOT RESULT IN AN OVERTRAVEL FORCE ON PLUNGER EXCEEDING FIVE POUNDS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - 195 GRAMS MAX

RELEASE FORCE - - - - - 15 GRAM MIN

DIFFERENTIAL TRAVEL - - - .013 MAX

OVERTRAVEL - - - - - .040 MIN

RELEASE TRAVEL - - - - - .007 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

L83

15.1A 1/2HP 125 OR 250 VAC

1/2A 125 VDC, 1/4A 250 VDC

5A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT