



58-A11.00-R52CU

4.5" Loudspeaker
Paper Cone
Treated Fabric Surround
Pressed Steel Chassis
Excellent Transient
Response
ROHS COMPLIANT



After the following tests the speaker operates normally.

Thermal Shock Test

-30°C±2°C/2Hrs +80°C/2Hrs 20 Cycles

Humidity Test

+40°C 95%RH 96Hrs

High Temperature Test

+85°C 240 Hrs

Low Temperature Test

-40°C 72 Hrs

A (mm)
120
B (mm)
102
C (mm)
50

Magnet Dia (mm)
80
Gasket thickness (mm)
0.9
Mounting holes in pitch
4

Output S P L
1W @ 1m

88

Nominal
impedance Ω

4

Rated Power
input (W)

20

Speaker
weight (g)

740

Voice coil
dia (mm)

25

FS 111.3 Hz

RE 3.68 Ohm

RES 13.101 Ohm

QMS 2.4

QES 0.68

QTS 0.52


MMs 3.93 grams

CMs 519 µm/Newton

BL 3.87 Tesla-m

File: D:\MLS\A11C.FRQ 8-31-2005 2:14 PM

Sensitivity Mag - dB SPL/watt (4.0 ohms, @1.00 M) (0.33 oct)



CURSOR: y = 49.051 x = 35003.9063 (8961)

SPECIFICATION

THIELE SMALL