



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER		S	POWER	
		E1	P1 P2		P3 P4	E2
51939-558-- NOTE 3	D C B A		PA PA	UUTTSRR	PA PA	



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
HA	[N/A]	HOLD-DOWN

mat'l code				SEE NOTE				tolerances unless otherwise specified				CUSTOMER																	
litr		ecn no.		dr		date		linear	0.X ±0.50				COPY				www.fciconnect.com												
A		DG10-0336		WL		09/25/10			0.XX ±0.25				projection																
									0.XXX ±0.10																				
									angles								0° ±2°												
								dr		WL ZHANG		09/25/10						product family				PwrBlade				code			
								enrg		Jerome Chen		09/25/10						size				dwg no				213			
								chr		PM ZHENG		09/25/10		scale				A				51939-558				sheet 1 of 4			
								appd		JOSEPH HSIA		09/25/10																	
sheet index		revision sheet		A		A		A		A		A																	
				1		2		3		4																			

Pro/E


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51939-558--
NOTE: 3




BROKEN-OUT SECTION A-A
SCALE 2:1



SECTION C-C



BROKEN-OUT SECTION B-B
SCALE 2:1



SECTION E-E

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A				linear		0.X ±0.50		projection		title	2ACP + 8S + 2ACP
						0.XX ±0.25					RIGHT ANGLE SOLDER HEADER
				angles		0.XXX ±0.10					
						0° ±2°				product family	PwrBlade
				dr	WL ZHANG	09/25/10				code	213
				enrg	Jerome Chen	09/25/10				size	dwg no
				chr	PM ZHENG	09/25/10				A	51939-558
				appd	JOSEPH HSIA	09/25/10				sheet	2 of 4
sheet index	revision sheet							scale	1:1		
										cage code	22526


Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-558-
NOTE: 3



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date			linear	0.X ± 0.50	COPY		www.fciconnect.com	
A						linear	0.XX ± 0.25	projection		title	
						angles	0.XXX ± 0.10			2ACP + 8S + 2ACP	
						angles	0° ± 2°			RIGHT ANGLE SOLDER HEADER	
						dr	WL ZHANG 09/25/10			product family	
						enrg	Jerome Chen 09/25/10			PwrBlade	
						chr	PM ZHENG 09/25/10			code	
						appd	JOSEPH HSIA 09/25/10			213	
sheet index	revision sheet							scale		size	
								1:1		dwg no	
										51939-558	
										sheet	
										3 of 4	

cage code 22526

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

B

F