

B9C202 Fiber - LooseTube Indoor/Outdoor All Dielectric Dry Core-Plenum OFNP

For more Information
please call

1-800-Belden1

**Description:**

FiberExpress Loose Tube Optical Fiber Cables are loose-tube buffered cables suited for outdoor applications such as lashed aerial or underground conduit.

Physical Characteristics (Overall)

Fiber Type:	50 Micron (OM3)
Number of Fibers:	6
Buffer Tube Material:	Thermoplastic

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Strength Member

Strength Member Material:	Aramid Yarn
----------------------------------	-------------

Overall Cable

Overall Nominal Diameter:	0.265 in.
----------------------------------	-----------

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +80°C
Installation Temperature Range:	0°C To +60°C
Operating Temperature Range:	-40°C To +70°C
Bulk Cable Weight:	33 lbs/1000 ft.
Min. Bend Radius/Minor Axis:	5.300 in.
Min. Bend Radius for Long Term Application:	4 in.
Max. Load for Installation:	300 lbs.
Max. Load for Long Term Application:	90 lbs.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	OFNP
CEC/C(UL) Specification:	OFNP
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/22/2008
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

B9C202 Fiber - LooseTube Indoor/Outdoor All Dielectric Dry Core-Plenum OFNP**Flame Test**

UL Flame Test:	UL910 Steiner Tunnel
----------------	----------------------

CSA Flame Test:	FT6
-----------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Suitability - Aerial:	No
-----------------------	----

Suitability - Burial:	Yes
-----------------------	-----

Sunlight Resistance:	Yes
----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Optical Characteristics (Overall)

Maximum Attenuation @ 850nm:	3 dB/km
------------------------------	---------

Maximum Attenuation @ 1300nm:	1.2 dB/km
-------------------------------	-----------

Minimum Bandwidth @ 850nm:	1500 MHz*km
----------------------------	-------------

Minimum Bandwidth @ 1300nm:	500 MHz*km
-----------------------------	------------

Maximum Gigabit Ethernet Length @ 850nm:	1000 meters
--	-------------

Maximum Gigabit Ethernet Length @ 1300nm:	550 meters
---	------------

Fiber Coding MLT EMEA:

Fiber/Tube No. Color	
1	Blue
2	Orange
3	Green
4	Brown
5	Slate
6	White

Related Documents:

[Loose Tube Single Jacket All Dielectric.pdf](#) - Loose Tube Single Jacket All Dielectric technical information.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
B9C202	1 FT	0.044	BLACK		SJAD 6F OM3 OFNP LT

Revision Number: 2 Revision Date: 12-11-2012

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[B9C202](#)