



- 2 Way
- 0 Degree
- Surface Mount
- 75 Ohm



M/A-COM's ELPD-20-1 is a 2 Way 0° Power Divider in a low cost, surface mount package. Ideally suited for high volume CATV applications.

SM- 93 Package



Parameter	Units	Typical	Minimum	Maximum
Frequency Range	5 - 1000	MHz	—	—
Insertion Loss	5 - 50 MHz	dB	0.2	0.5
	50 - 500 MHz	dB	0.5	0.8
	500 - 1000 MHz	dB	1.0	1.3
Isolation	5 - 50 MHz	dB	26	22
	50 - 500 MHz	dB	29	22
	500 - 1000 MHz	dB	22	18
Amplitude Unbalance	5 - 50 MHz	dB	—	—
	50 - 500 MHz	dB	—	—
	500 - 1000 MHz	dB	—	—
Phase Unbalance	5 - 50 MHz	°	—	—
	50 - 500 MHz	°	—	—
	500 - 1000 MHz	°	—	—
Output Return Loss	5 - 750 MHz	dB	—	18
	750 –1000 MHz	dB	—	15
Input Return Loss	5 - 1000 MHz	dB	—	18
	750 –1000 MHz	dB	—	12

Specifications subject to change without notice.

V5.00 S 1380 H

- **North America:** Tel. (800) 366-2266, Fax (800) 618-8883
- **Asia/Pacific:** Tel. +81-44-844-8296, Fax +81-44-844-8298
- **Europe:** Tel. +44 (1344) 869 595, Fax +44 (1344) 300 020

Visit www.macom.com for additional data sheets and product information.

Absolute Maximum Ratings


Parameter	Absolute Maximum
Maximum Power Rating	1 Watt
Internal Load Dissipation	0.125 Watt
Pin Temp (10 Sec)	260°C
Storage Temperature	-55°C to 100°C
Operating Temperature	-55°C to 100°C

Functional Configuration


Function	Pin No.
Not Connected	2,5
External 75 Ohms	—
Ground	6
Case Ground	—
Input	1
Port 1	3
Port 2	4

Typical Performance @ +25°C


Insertion Loss




Isolation




Amplitude Unbalance




Phase Unbalance



Output Return Loss



Input Return Loss



Specifications subject to change without notice.

V5.00

S 1380 H

■ North America: Tel. (800) 366-2266, Fax (800) 618-8883
 ■ Asia/Pacific: Tel. +81-44-844-8296, Fax +81-44-844-8298
 ■ Europe: Tel. +44 (1344) 869 595, Fax +44 (1344) 300 020

Visit www.macom.com for additional data sheets and product information.

tyco Electronics

MACOM