






LOC	DIST	REVISIONS					
		P	LYR	DESCRIPTION	DATE	DWN	APVD
		C2		REVISED ECO-17-016624	06DEC17	DD	E.J
		C3		REVISED ECO-18-016296	15DEC2018	DD	E.J
		C4		SEAL ADD A NEW MATERIAL AND COLOR	19FEB2024	A.L	E.J
		D		BUSHING LOCALIZATION IN CHINA	18JUL2024	A.L	E.J

- NOTES
1. FINAL TEST: VISUAL INSPECTION FOR COMPLETENESS
 2. LAYER PACKING WITH CORRUGATED
 3. MUST MEET TOUCH SAFE REQUIREMENT PER IEC 60529
 4. RECOMMENDED TIGHTENING TORQUE OF THE SCREW: M8=10±1NM.
 5. USABLE 2P MOS SOCKET HOUSING P/N:1-1718333-1
 6. CODING AREA
 7. MIN SEALING AREA AROUND, NO BURR, TOOLING PARTING, SHRINKAGE PERMITTED, SURFACE QUALITY: Ra<=0.8um
 8. V0 MAIRKING ONLY FOR V0 PART,P/N:3-2137740-*



(0-)*-1
3-*1 AS SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. WANG	08NOV11	TE Connectivity HVP1100 1POS HEADER ASSY			
DIMENSIONS:		CHK N. ZHOU	08NOV11				
mm		APVD K. ODA	08NOV11	NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		0-BLC ±0.3		108-101010			
		1-PLC ±0.5		APPLICATION SPEC			
		2-PLC ±0.13		114-101010			
MATERIAL		ANGLES ±0.0001°		WEIGHT			
FINISH		±1°		CUSTOMER DRAWING			
				SCALE	2:1	SHEET	1 OF 5
				REV	D		





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. WANG	08NOV11	TE Connectivity	
DIMENSIONS:		CHK N. ZHOU	08NOV11		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K. ODA	08NOV11	NAME	HVP1100 1POS HEADER ASSY
	0-PLC	PRODUCT SPEC		SIZE	CAGE CODE
	1-PLC	108-101010		DRAWING NO	RESTRICTED TO
	2-PLC	APPLICATION SPEC			
	3-PLC	114-101010			
MATERIAL		WEIGHT	A100779	C=2137740	
FINISH		CUSTOMER DRAWING		SCALE	2:1
				SHEET	4 OF 5
				REV	D

