



Planetary Gearhead GP 16 A Ø16 mm, 0.1 - 0.3 Nm



M 1:1

Technical Data

Planetary Gearhead	straight teeth
Output shaft	stainless steel, hardened
Bearing at output	sleeve bearing
Radial play, 6 mm from flange	max. 0.1 mm
Axial play	0.02 - 0.10 mm
Max. permissible axial load	8 N
Max. permissible force for press fits	100 N
Sense of rotation, drive to output	=
Recommended input speed	< 8000 rpm
Recommended temperature range	-15 ... +100°C
Extended area as option	-35 ... +100°C
Number of stages	1 2 3 4 5
Max. radial load, 6 mm from flange	8 N 12 N 16 N 20 N 20 N

- Stock program
- Standard program
- Special program (on request)

Order Number

Gearhead Data

	110321	110322	110323	118186	110324	134782	110325	134785
1 Reduction	4.4 : 1	19 : 1	84 : 1	157 : 1	370 : 1	690 : 1	1621 : 1	3027 : 1
2 Reduction absolute	57/13	3249/169	185193/2197	19683/125	10556001/28561	1121931/1625	601692057/371293	63950067/21125
3 Max. motor shaft diameter	2	2	2	1.5	2	2	2	2
Order Number	118184	134777	134778		134780	118187	134783	134786
1 Reduction	5.4 : 1	24 : 1	104 : 1		455 : 1	850 : 1	1996 : 1	3728 : 1
2 Reduction absolute	27/5	1539/65	87723/845		5000211/10985	531441/625	285012027/142805	30292137/8125
3 Max. motor shaft diameter	1.5	2	2		2	1.5	2	2
Order Number		118185	134779		134781		134784	118188
1 Reduction		29 : 1	128 : 1		561 : 1		2458 : 1	4592 : 1
2 Reduction absolute		729/25	41553/325		2368521/4225		135005697/54925	14348907/3125
3 Max. motor shaft diameter		1.5	2		2		2	1.5
4 Number of stages	1	2	3	3	4	4	5	5
5 Max. continuous torque	0.10	0.15	0.20	0.20	0.25	0.25	0.30	0.30
6 Intermittently permissible torque at gear output	0.150	0.225	0.300	0.300	0.375	0.375	0.450	0.450
7 Max. efficiency	90	81	73	73	65	65	59	59
8 Weight	20	23	27	27	31	31	35	35
9 Average backlash no load	1.4	1.6	2.0	2.0	2.4	2.4	3.0	3.0
10 Mass inertia	0.07	0.05	0.05	0.04	0.05	0.05	0.05	0.05
11 Gearhead length L1	15.5	19.1	22.7	22.7	26.3	26.3	29.9	29.9




maxon Modular System

+ Motor	Page	+ Sensor / Brake	Page	Overall length [mm] = Motor length + gearhead length + (sensor / brake) + assembly parts							
RE 16, 2 W	72			37.9	41.5	45.1	45.1	48.7	48.7	52.3	52.3
RE 16, 2 W	72	MR	260/262	43.6	47.2	50.8	50.8	54.4	54.4	58.0	58.0
RE 16, 3.2 W	73/74			56.0	59.6	63.2	63.2	66.8	66.8	70.4	70.4
RE 16, 3.2 W	74	MR	260/262	61.0	64.6	68.2	68.2	71.8	71.8	75.4	75.4
RE 16, 3.2 W	74	MEnc 13	275	62.1	65.7	69.3	69.3	72.9	72.9	76.5	76.5
RE 16, 4.5 W	75/76			59.0	62.6	66.2	66.2	69.8	69.8	73.4	73.4
RE 16, 4.5 W	76	MR	260/262	64.0	67.6	71.2	71.2	74.8	74.8	78.4	78.4
RE 16, 4.5 W	76	MEnc 13	275	65.1	68.7	72.3	72.3	75.9	75.9	79.5	79.5
A-max 16	93-96			41.0	44.6	48.2	48.2	51.8	51.8	55.4	55.4
A-max 16	94/96	MR	260/262	46.0	49.6	53.2	53.2	56.8	56.8	60.4	60.4
A-max 16	94/96	MEnc 13	275	49.1	52.7	56.3	56.3	59.9	59.9	63.5	63.5
RE-max 17	123-126			41.0	44.6	48.2	48.2	51.8	51.8	55.4	55.4
RE-max 17	124/126	MR	260/262	46.0	49.6	53.2	53.2	56.8	56.8	60.4	60.4
EC 16, 15 W	147			55.8	59.4	63.0	63.0	66.6	66.6	70.2	70.2
EC 16, 15 W	147	MR	263	65.9	69.5	73.1	73.1	76.7	76.7	80.3	80.3
EC-max 16, 5 W	165			39.6	43.2	46.8	46.8	50.4	50.4	54.0	54.0
EC-max 16, 5 W	165	MR	263	46.9	50.5	54.1	54.1	57.7	57.7	61.3	61.3
EC-max 16, 2-wire	166			49.1	52.7	56.3	56.3	59.9	59.9	63.5	63.5

Option Ball Bearing

Order Number

Technical Data



4.4 : 1	138333	455 : 1	138343	Planetary Gearhead	straight teeth
5.4 : 1	138334	561 : 1	138344	Output shaft	stainless steel, hardened
19 : 1	138335	690 : 1	138345	Bearing at output	preloaded ball bearings
24 : 1	138336	850 : 1	138346	Radial play, 6 mm from flange	max. 0.08 mm
29 : 1	138337	1621 : 1	138347	Axial play at axial load	< 4 N 0 mm
84 : 1	138338	1996 : 1	138348		> 4 N max. 0.05 mm
104 : 1	138339	2458 : 1	138349	Max. permissible axial load	8 N
128 : 1	138340	3027 : 1	138350	Max. permissible force for press fits	25 N
157 : 1	138341	3728 : 1	138351	Sense of rotation, drive to output	=
370 : 1	138342	4592 : 1	138352	Recommended input speed	< 8000 rpm
				Recommended temperature range	-15 ... +100°C
				Extended area as option	-35 ... +100°C
				Number of stages	1 2 3 4 5
				Max. radial load, 6 mm from flange	10 N 15 N 20 N 20 N 20 N
				Gearhead values according to sleeve bearing version	