

NUMBER OF POSITIONS	DIMENSION	
	A	B
08	7.62	14.86
10	10.16	17.40
12	12.70	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
22	25.40	32.64
24	27.94	35.18
26	30.48	37.72
30	35.56	42.80
34	40.64	47.88
36	43.18	50.42
40	48.26	55.50
44	53.34	60.58
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: Nickel 50μ"

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.










Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C

RoHS


REV.	DESCRIPTION	DATE
A	RELEASE	2012/11/7



8P

10P-12P

14P-64P



Mating Part Number

3020-ALL	3010-XX-001-11-XX	3010-XX-001-12-XX
3010-XX-002-12-XX	3010-XX-003-12-XX	

UNLESS TOLERANCE		DRAW BY		CnC Tech,LLC Part NO. 3030-XX-0102-99
GENERAL	ANGLE	DESIGN BY		
X. ± 0.30	X.* ± 3.0°	CHECK BY		
.X ± 0.25	.X* ± 2.0°	APPROVE BY		
.XX ± 0.20	.XX* ± 1.0°			
.XXX ± 0.10	.XXX* ± 0.5°			
		SCALE	SHEET	UNIT
		1:1	1/1	MM
		DRW NO:		REV: A