

## SPECIFICATIONS:

## ELECTRICAL:

INSULATOR RESISTANCE: 5,000 MegOHMS Min.  
 DIELECTRIC WITHSTANDING: 1,000VAC r.m.s.  
 OPERATING TEMPERATURE: -55° C ~ +125° C  
 CONTACT RESISTANCE: 30 MillioHMS Max.  
 COAXIAL PINS: 50 OHM  
 SIGNAL PINS: 3 AMPS

## MECHANICAL:

CONTACT INSERTION FORCE: 4.5 Kg Max.  
 CONTACT SEPARATOR FORCE: 0.3Kg Min.

## MATERIALS:

CONTACTS: BRASS  
 INSULATOR: PBT UL94V-0 RATED,  
 SHELL: 230°C PROCESS TEMP.  
 STEEL

## FINISH:

SHELL: NICKEL

68211W1203L001

00 = 50 OHM COAXIAL

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS  
 ARE THE PROPERTY OF NorComp AND  
 SHALL NOT BE REPRODUCED, COPIED  
 OR USED AS THE BASIS FOR THE  
 MANUFACTURE OF SALE OF APPARATUS  
 WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH DATE: 09-21-06


CHECKED: X DATE: X

SCALE: N.T.S. SHEET OF 1 2 REV 2


DWG NO. 68211W1203L001

NorComp


NOTE:  
SIGNAL CONTACTS COME PRE-LOADED INTO INSULATORS.  
COAXIAL CONTACTS SUPPLIED - NOT PRE-LOADED.



SIGNAL CONTACTS  
ACCEPTS UP TO 20 AWG WIRE



COAXIAL CONTACT  
ACCEPTS 50 OHM COAX, RG316/RG174



FEMALE COAXIAL CONTACT



MALE COAXIAL CONTACT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF NorComp AND  
SHALL NOT BE REPRODUCED, COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OF SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

DRAWN:  
C. SMITH

DATE:  
09-21-06

CHECKED:  
X

DATE:  
X

SCALE:  
N.T.S.

OF  
2 2

REV  
2

DWG NO.

68211W1203L001

NorComp