




Date	SYM	REVISION RECORD	AUTH	DR.	CK.
9/23/06	B	DELETED DIM. 0.960 [24.4]	T.B.	B.S.	
11/11/06	C	ADDED UL FILE NO.	T.B.	B.S.	
3/10/07	D	30% GLASS FILLED WAS 33%	T.B.	B.S.	
07/29/11	E	MATERIAL NYLON 66 WAS FR-NYLON	T.B.	B.S.	



PCB HOLE LAYOUT

MATERIAL

BODY: NYLON 66 WITH 30% GLASS FILLED, UL FILE NO. E196894

FLAMMABILITY RATING: UL94V-0

CONTACT: PHOSPHOR BRONZE

FINISH

CONTACT: NICKEL PLATED

SPECIFICATIONS

APPLICATION FOR 3V LITHIUM BATTERY

INSULATOR RESISTANCE: 5000 M MIN.

OPERATION TEMPERATURE: -40°C TO +200°C

DURABILITY: 50 CYCLES MIN

CONTACT RESISTANCE: 30 M MAX

ROHS COMPLIANT

Tolerance (Except as noted)	 Memory protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal $\pm .5$ (.020)		Scale 4=1	Drawn By T.S. Approved By T.B.
Fractional $\pm .8$ (.030)	Title BR/CR 2032 VERTICAL LITHIUM BATTERY HOLDER		
Angular $\pm 3^\circ$	Date 07/29/11	Drawing Number BS-5	