

ADAPTERS, IN SERIES

SMA, DC - 26.5 GHz, Bulkhead Mount

SPECIFICATIONS:

Models: 5211, 5218

RoHS
Compliant

Electrical:

Frequency Range _____ DC - 26.5 GHz

Standard Freq. Values _____ 18 & 26.5 GHz

VSWR

DC - 4 GHz _____ 1.05:1 Max.

4 - 8 GHz _____ 1.10:1 Max.

8 - 18 GHz _____ 1.15:1 Max.

18 - 26.5 GHz _____ 1.30:1 Max.

Nominal Impedance _____ 50 Ohms

Operating Temp Range _____ -55°C to +125°C

Mechanical:

Connectors _____ Passivated Stainless Steel


Mates with MIL-STD-348

Conductors _____ Gold Plated Beryllium Copper

Nut & Washer: _____ Passivated Stainless Steel

O-Ring _____ Silicone Rubber

AEROFLEX
A passion for performance.




Recommended
Mounting Hole

Model Number: 5211

Frequency Range _____ DC - 18 GHz

Model Number: 5218

Frequency Range _____ DC - 26.5 GHz



Panel Nut, Lock Washer & O-Ring are Shipped Unassembled

Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

Design specifications are subject to change without notice.

Contact factory for technical specifications before purchasing or use.

5211: REV G

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmet@aeroflex.com