# Switches
# Core Program

Tyco Electronics

Our commitment. Your advantage.

## Contents

**DIP Switches**
GDS Series . . . page 2
GDP Series . . . page 2
GDR Series . . . page 2
GDH Series . . . page 2
GDHL Series . . . page 2
ADE Series . . . page 3
ADF Series . . . page 3
ADP Series . . . page 3
STV, STR Series . . . page 3
DIP Series . . . page 3
HTH DIP Shunts . . . page 4
DIP-Fix . . . page 4
MRD Series . . . page 4
DR-/D/M/S/W Series . . . page 4

**Tactile Switches**
FSM . SM/JM Series, 3.5 x 6 . . . page 5
FSM . SM/JM LP Series, 4 x 6 . . . page 5
FSM 6 x 6 Series . . . page 5
FSM 10 Series, 12 x 12 . . . page 5
FSM Turtle . . . page 6
FSMMSH Series . . . page 6
FSM . MS Series . . . page 6
FSMCT Series . . . page 6
FSMLPU . . . page 6

**Slide Switches**
ASE, ASF Series . . . page 7
S, SE Series . . . page 7
STS, SDS Series . . . page 7
TSS Series . . . page 7
MSS, MSSA Series . . . page 7
MSSA-01/04 . . . page 7
MHS Series . . . page 8
SSJ Series . . . page 8
SSA Series . . . page 8
SLS/SL/SLSA Series . . . page 8
MLL Series . . . page 8

**Toggle Switches**
TST Series . . . page 9
TT Series . . . page 9
Gemini A Series . . . page 9
Gemini AE Series . . . page 9
MT Series . . . page 9
AW Series . . . page 10
F Series . . . page 10

**Push Buttons**
TP Series . . . page 11
MP Series . . . page 11

**Micro Switches**
MP Miniature Micro Switch . . . page 12
SP Sub Miniature Micro Switch . . . page 12
UP Ultra Miniature Micro Switch . . . page 12

**Power Rocker Switches**
PRA Series . . . page 13
PRC Series . . . page 13
PRE Series . . . page 13
PRF Series . . . page 13
PRG Series . . . page 13

**Preferred Parts List**
DIP Switches . . . page 14
Tactile Switches . . . page 17
Slide Switches . . . page 19
Toggle Switches . . . page 22
Push Buttons . . . page 22
Micro Switches . . . page 25
Power Rocker Switches . . . page 26

Please note that the product range in this catalog represents a part of the complete range of Tyco Electronics switches only.

For additional products in the listed product groups as well as for

- Rotary Switches,
- Keylock Switches,
- Industrial Controls,
- Pushwheel Switches and
- Accessories as knobs, caps, boot seals and the respective hardware

please contact our sales office or see our products under www.tycoelectronics.com.



Catalogue No. 1308111
Issued 03/2008

# DIP Switches - GD Series, High Feature Line

## GDS Series

- Low profile
- End stackable
- Auto insertable
- Gold contacts

## GDP Series

- Piano actuator
- Classic profile
- Gold contacts

## GDR Series

- Recessed rocker actuator
- Classic profile
- Gold contacts

| Dips | | | |
|---|---|---|---|
| Standard number of positions | 2, 4, 6, 8, 10 | 2, 4, 6, 8, 10 | 2, 4, 6, 8, 10 |
| Mounting style | THT, SMT | THT, SMT | THT, SMT |
| Tape seal | Yes | Yes | Yes |
| Contact rating | 25 mA @ 24 Vdc | 25 mA @ 24 Vdc | 25 mA @ 24 Vdc |
| Electrical endurance | 1000 ops. | 1000 ops. | 1000 ops. |
| Operating temperature range | -30…+85°C | -30…+85°C | -30…+85°C |
| Dimensions (WxH) | 6.2 x 2.7 mm | 9.6 x 8.7 mm | 9.6 x 6.9 mm |
| Packaging | Tube, Tape and Reel | Tube, Tape and Reel | Tube, Tape and Reel |

## GDH Series

- Low profile
- Half pitch
- Gold contacts

## GDHL Series

- Ultra low profile
- Half pitch
- Gold contacts

| Dips | | |
|---|---|---|
| Standard number of positions | 2, 4, 6, 8, 10 | 2, 4, 6, 8, 10 |
| Mounting style | SMT | SMT |
| Tape seal | Yes | Yes |
| Contact rating | 25 mA @ 24 Vdc | 25 mA @ 24 Vdc |
| Electrical endurance | 1000 ops. | 1000 ops. |
| Operating temperature range | -30…+85°C | -30…+85°C |
| Dimensions (WxH) | 6.2 x 3.2 mm | 4.5 x 1.45 mm |
| Packaging | Tape and Reel | Tube, Tape and Reel |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# DIP Switches - AD Series, SIP Switches, DIP Series

## ADE Series

- Extended actuator
- High pressure contact system
- Processable without tape seal
- Auto insertable

## ADF Series

- Flush actuator
- High pressure contact system
- Processable without tape seal
- Auto insertable

## ADP Series

- Piano actuator
- High pressure contact system
- Processable without tape seal
- Auto insertable

| Dips | | | |
|---|---|---|---|
| Standard number of positions | 2…12 | 2…12 | 2, 4, 6, 8, 10 |
| Mounting style | THT, SMT | THT, SMT | THT, SMT |
| Tape seal | No | Optional | No |
| Contact rating | 100 mA @ 24 Vdc | 100 mA @ 24 Vdc | 100 mA @ 24 Vdc |
| Electrical endurance | 1000 ops. | 1000 ops. | 1000 ops. |
| Integral resistors | Optional | Optional | No |
| Operating temperature range | -30…+85°C | -30…+85°C | -30…+85°C |
| Dimensions (WxH) | 7.5 x 3.5 mm | 7.5 x 3.5 mm | 8.8 x 6.8 mm |
| Packaging | Tube | Tube, Tape and Reel | Tupe, Tape and Reel |

## STV, STR Series

- Low profile
- High pressure contact system
- Processable without tape seal

## DIP Series

- Up to 30 poles
- Action pins up to 9 poles
- High contact force to break through oxide or dirt layers

| Dips | | |
|---|---|---|
| Standard number of positions | 2, 4, 6, 8, 10 | 1-30 |
| Mounting style | THT | THT, Action pins |
| Tape seal | No | No |
| Contact rating | 25 mA @ 24 Vdc | 25 mA @ 50 Vdc |
| Electrical endurance | 1000 ops. | 2000 ops. |
| Operating temperature range | -30…+85°C | -25…+70°C |
| Dimensions (WxH) | 3.2 x 6.2 mm | 10.0 x 8.5 mm |
| Packaging | Tube | Tube |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# DIP Shunts, DIP-Fix, Rotary DIP Switches

## HTH DIP Shunts

- **Machine insertable shunt on request**

## DIP-Fix

- **Highly simplified DIP switch with change over option**
- **Low cost alternative**
- **Predetermined breaking points**

| Shunts, DIP-Fix | | |
|---|---|---|
| Standard number of positions | 4, 6, 8, 10, 12 | 1-10, 12, 16, 24 |
| Mounting style | THT | THT |
| Tape seal | No | No |
| Contact rating | up to 2 A | up to 0.5 A |
| Electrical endurance | - | 50 ops. |
| Operating temperature range | -30…+85°C | -40…+85°C |
| Dimensions (WxH) | 6.,0 x 2.0 mm | 12.4 x 8.1 mm |
| Packaging | Tube | Tray |

## MRD Series

- **Low profile**
- **Process sealed**
- **7 mm edge length**

## DR-/D/M/S/W Series

- **Process sealed**
- **10 mm edge length**

| Rotary Dips | | |
|---|---|---|
| Right angle versions | for THT version only | for THT version only |
| Standard number of positions | 10, 16 | 10, 16 |
| Mounting style | THT, SMT | THT, SMT |
| Actuator style | Flush actuator only | Flush, Mini plastic shaft, Wheel, Metal shaft |
| Flush actuator versions | Yes | Yes |
| Output Code | BCD, BCD compl., Hex, Hex compl. | BCD, BCD compl., Hex, Hex compl. |
| Tape seal | Optional | Optional |
| Contact rating | 20 mA @ 20 Vdc | 20 mA @ 20 Vdc |
| Electrical endurance | 20,000 ops. | 20,000 ops. |
| Operating temperature range | -30…+85°C | -30…+85°C |
| Dimensions (LxWxH) | 7 x 7 x 3.3 mm | 10 x 10 x 6.8 mm |
| Packaging | Tube, Tape and Reel | Tube, Tape and Reel (for SMT version only) |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Tactile Switches

## FSM . SM/JM Series

- **Small PCB footprint**

## FSM . SM/JM LP Series

- **Small PCB footprint**
- **Low profile**
- **SMT and SMT up pinning**

NEW

## FSM 6 x 6 Series

- **Different actuator and mounting versions**
- **105°C versions available**

| Tactiles | | | |
|---|---|---|---|
| Style | 3.5 x 6 | 4 x 6 | 6 x 6 |
| Mounting style | THT, SMT | SMT | THT, SMT |
| Right angle versions | No | No | Yes |
| Low profile versions | No | Standard | Yes |
| Flush actuator version | Yes | No | Yes |
| Different actuator styles | Yes | No | Yes |
| ESD grounding term./locating post | No / No | No / No | Optional / No |
| Sealed versions | Yes | No | Yes |
| Standard actuation force | 1.3, 1.8 N | 1.6, 2.6 N | 1.0, 1.6, 2.6, 5.2 N |
| Electrical endurance | up to 100,000 ops. | up to 1,000,000 ops. | up to 2,000,000 ops. |
| Operating temperature range | -40…+85°C | -40…+85°C | -40…+85°C, (+105°C) |
| Dimensions horizontal ver. (LxWxH) | 3.5 x 6 x 4.3...5 mm | 4.2 x 6 x 2.5 mm | 6 x 6 x 4.3…17 mm |
| Dimensions sealed ver. (LxWxH) | 4.7 x 6.8 x 4.3…5 mm | - | - |
| Packaging | Tape and Reel, Bulk | Tape and Reel | Tape and Reel, Bulk |

## FSM 10 Series

- **Different actuator and mounting versions**

| Tactiles | |
|---|---|
| Style | 12 x 12 |
| Mounting style | THT, SMT |
| Right angle versions | Yes |
| Low profile versions | No |
| Flush actuator version | Yes |
| Different actuator styles | Yes |
| ESD grounding term./locating post | No / Optional |
| Sealed versions | Yes |
| Standard actuation force | 1.6, 2.6 N |
| Electrical endurance | up to 1,000,000 ops. |
| Operating temperature range | -35…+85°C |
| Dimensions horizontal ver. (LxWxH) | 12 x 12.5 x 4.3…12 mm |
| Dimensions sealed ver. (LxWxH) | 12 x 12.5 x 4.3…7.3 mm |
| Packaging | Tape and Reel, Bulk |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Tactile Switches

## FSM Turtle

■ **Side actuated tactile**

## FSMMSH Series

■ **Small PCB space required**

■ **Side actuated**

## FSM . MS Series

■ **Low profile**

■ **Side actuated**

| **Tactiles** | | | |
|---|---|---|---|
| Style | Turtle | Miniature side actuated | Miniature side actuated |
| Mounting style | SMT | SMT | SMT |
| Right angle versions | No | Yes | Yes |
| Low profile versions | No | No | No |
| Flush actuator version | No | No | No |
| Different actuator styles | No | No | No |
| ESD grounding term./locating post | No / Optional | No / Optional | No / Optional |
| Sealed versions | No | No | No |
| Standard actuation force | 1.6 N | 1.6 N | 2.2, 2.5 N |
| Electrical endurance | 100,000 ops. | 100,000 ops. | 100.000 ops. |
| Operating temperature range | -20…+85°C | -20…+70°C | -20…+85°C |
| Dimensions horizontal ver. (LxWxH) | 4.0 x 7.15 x 1.7 mm | 4.5 x 2.55 x 3.3 mm | refer to catalogue |
| Dimensions sealed ver. (LxWxH) | - | - | - |
| Packaging | Tape and Reel, Bulk | Tape and Reel | Tape and Reel |

## FSMCT Series

■ **Low profile**

## FSMLPU

■ **Ultra low profile**

■ **0.6 mm high only**

| **Tactiles** | | |
|---|---|---|
| Style | 5 x 5 | 5 x 5 |
| Mounting style | SMT | SMT |
| Right angle versions | No | No |
| Low profile versions | No | Standard |
| Flush actuator version | No | Standard |
| Different actuator styles | No | No |
| ESD grounding term./locating post | No / No | No / No |
| Sealed versions | No | No |
| Standard actuation force | 1.6, 2.6 N | 1.6 N |
| Electrical endurance | up to 1,000,000 ops. | 500.000 ops. |
| Operating temperature range | -20…+85°C | -20…+70°C |
| Dimensions horizontal ver. (LxWxH) | 5.2 x 5.2 x 1.5 mm | 4.8 x 4.8 x 0.6 mm |
| Dimensions sealed ver. (LxWxH) | - | - |
| Packaging | Tape and Reel | Tape and Reel |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Slide Switches

## ASE, ASF Series

- **Bifurcated double wipe contacts, also for telecom grade switching**
- **ASF for auto insertion on standard IC equipment**

## S, SE Series

- **Compact slide switch**
- **S: unsealed**
  **SE: sealed (IP 67)**

## STS, SDS Series

- **Miniature slide switch**
- **STS: economy grade**
  **SD: instrumentation grade**
- **Low profile**

| **Slide switch** | | | |
|---|---|---|---|
| Number of poles | 2, 4, 6 | 1 or 2 | 1 or 2 |
| Number of throws | 2, 3 (available in 4 pole only) | 1,2 | up to 6 |
| Contact timing | Make before Break | Break before Make | Make before Break |
| Right angle versions | Yes | Yes | Yes |
| Mounting style | SMT, THT | SMT, THT | THT |
| Actuator style | ASF: Flush top actuator<br>ASE: Extended top or side<br>ASFO: Flush top or side | SE: Actuator with boot sealing | SDS: on request |
| Flush actuator version | ASF: Yes, ASE: No | No | No |
| Tape seal | ASF: Yes, ASE: No | No | No |
| Contact rating | Gold: 20 mA @ 20 Vdc<br>Silver: 300 mA @ 115 Vac, 28 Vdc | 20 mA@ 20 Vdc | 300 mA @ 125 Vac |
| Electrical endurance | 10,000 ops. | 10,000 ops. | 10,000 ops. |
| Operating temperature range | -40…+80°C | -20…+80°C | -15…+60°C |
| Dimensions (LxWxH) | refer to catalogue | 9.5 x 5 x 8.0 mm | refer to catalogue |
| Packaging | Tube | Tray, Tape and Reel | Bulk |

## TSS Series

- **Single or dual actuator**

## MSS, MSSA Series

- **Instrumentation grade**

## MSSA-01/04 Series

- **Instrumentation grade**
- **Top and side actuator**

| **Slide switch** | | | |
|---|---|---|---|
| Number of poles | up to 4 | up to 6 | up to 2 |
| Number of throws | 1 or 2 | up to 4 | 2 |
| Contact timing | Break before Make | Make before Break | Break before Make |
| Right angle versions | Yes | Yes | Yes |
| Mounting style | THT | THT | THT |
| Actuator style | Standard | Standard / MSSA: Position snap | Standard |
| Flush actuator version | Yes | No | Yes |
| Tape seal | No | No | No |
| Contact rating | 20 mA @ 20 Vdc | Gold: 20 mA @ 20 Vdc<br>Silver: 300 mA @ 125 Vac | Gold: 20 mA @ 20 Vdc<br>Silver: 3A@115Vac, 1.5A@230Vac |
| Electrical endurance | 80,000 ops. | 15,000 ops. | 30,000 ops. |
| Operating temperature range | -20…+80°C | -20…+85°C | -20…+85°C |
| Dimensions (LxWxH) | refer to catalogue | refer to catalogue | MSSA1: 11.9 x 6.4 x 8 mm<br>MSSA2: 11.9 x 11.4 x 8 mm |
| Packaging | Bulk | Tray | Bulk |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Slide Switches

## MHS Series

- **Low profile**
- **Instrumentaion grade**

| Slide switch | |
|---|---|
| Number of poles | up to 2 |
| Number of throws | up to 3 |
| Contact timing | Make before Break |
| Right angle versions | Yes |
| Mounting style | THT |
| Actuator style | Standard and Baton |
| Flush actuator version | No |
| Tape seal | No |
| Contact rating | Gold: 20 mA @ 20 Vdc<br>Silver: 300 mA @ 125 Vac |
| Electrical endurance | 15,000 ops. |
| Operating temperature range | -20…+100°C |
| Dimensions (LxWxH) | 16.0 x 6.7 x 7.5 mm |
| Packaging | Tray |

## SSJ Series

- **Micro size**
- **Instrumentation grade**

| | |
|---|---|
| 1 |
| 3 |
| Make before Break |
| Yes |
| THT |
| Standard |
| No |
| No |
| 100 mA @ 12 Vdc |
| 10,000 ops. |
| -10…+60°C |
| 10.2...15.8 x 4 x 5.5 mm |
| Tray |

## SSA Series

- **Micro size**
- **Instrumentation grade**

| | |
|---|---|
| up to 2 |
| 2 |
| Make before Break |
| Yes |
| THT |
| Standard |
| No |
| No |
| Gold: 20 mA @ 20 Vdc<br>Silver: 100 mA @ 30 Vac |
| up to 10,000 ops. |
| -20…+80°C |
| 9.0…15.0 x 3.4…5.6 x 4.8 mm |
| Bulk |

## SLS/SL/SLSA Series

- **Wiping contact**
- **Consumer grade**

| Slide switch | |
|---|---|
| Number of poles | up to 2 |
| Number of throws | up to 10 |
| Contact timing | Break before Make |
| Right angle versions | Yes |
| Mounting style | THT |
| Actuator style | Standard, Lever / Knob Actuator |
| Flush actuator version | No |
| Tape seal | No |
| Contact rating | SLS/SL: 250 mA @ 125 Vac,<br>150 mA @ 12 Vdc<br>SLA: 500 mA @ 125 Vac |
| Electrical endurance | 10,000 ops. |
| Operating temperature range | SLS/SL: -10…+60°C,<br>SLA: -20…+85°C |
| Dimensions (LxWxH) | refer to catalogue |
| Packaging | Bulk |

## MLL Series

- **Low profile**

NEW

| | |
|---|---|
| 1 |
| up to 3 |
| Make before Break |
| Standard |
| SMT |
| Standard |
| No |
| No |
| 300 mA; 4 Vdc |
| 10,000 ops. |
| 20…+85°C |
| 6.7...9.7 x 2.6 x 1.4 |
| Tube, Tape and Reel |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Toggle Switches

## TST Series

- **Sub miniature toggle switch**
- **Sealed**

## TT Series

- **Sub miniature toggle switch**
- **Boot seal available**

## Gemini Series A

- **Miniature toggle switch**

| Toggles | | | |
|---|---|---|---|
| Number of poles | 1 | up to 4 | 1 or 2 |
| Contact timing | Break before Make | Break before Make | Break before Make |
| Right angle versions | Yes | right angle and vertical right angle | right angle and vertical right angle |
| Standard number of positions | 2 or 3 | 2 or 3 | 2 or 3 |
| Terminals / Mounting style | THT | THT, Wire lug, Wire wrap; Various bushings versions | THT, Wire lug, Quick connect, Wire wrap, Support brackets; Various bushings versions |
| Actuator style | Various lenghts | Various lengths, round, flat, locking | different lenghts, round, flat, locking; rocker style |
| Contact rating | 20 mA @ 20 Vac/dc | Gold: 20 mA @ 20 Vdc<br>Silver (2pos): 3A@125Vac, 28Vdc<br>Silver (3pos): 2A@125Vac, 28Vdc | 2 A @ 250 Vac |
| Electrical endurance | 80,000 ops. | 60,000 ops. | 40,000 ops. |
| Operating temperature range | -30…+85°C | -30…+85°C | -30…+85°C |
| Dimensions case (LxWxH) | 8.1 x 5.0 x 9.1 mm | 8.1 x 6 x 8.8...15.7 mm | 12.7 x 6.9…16.8 x 10.4 mm |
| Packaging | Bulk | Bulk | Bulk |

## Gemini Series AE

- **Miniature toggle switch sealed**
- **Meets requirements of IP67**

## MT Series

- **Toggle switch**

| Toggles | | |
|---|---|---|
| Number of poles | 1 or 2 | up to 4 |
| Contact timing | Break before Make | Break before Make |
| Right angle versions | right angle and vertical right angle | right angle and vertical right angle |
| Standard number of positions | 2 or 3 | 2 or 3 |
| Terminals / Mounting style | THT, Wire lug, Quick connect, Wire wrap, Support brackets | THT, Wire lug |
| Actuator style | different lenghts, round, flat; rocker style | Lenghts, round, flat, Mustang, splash proof bat actuator, locking, decorative bat actuator |
| Contact rating | 2 A @ 250 Vac | 3 A @ 250 Vac,4 A @ 28 Vdc |
| Electrical endurance | 30,000 ops. | 80,000 ops. |
| Operating temperature range | -30…+85°C | -20…+85°C |
| Dimensions case (LxWxH) | 12.7 x 6.6…11.4 x 10.3 mm | 13 x 8…22.5 x 11.5 mm |
| Packaging | Bulk | Bulk |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Toggle Switches

## AW Series

- **IP67 panel mounting seal**
- **Sleeve & Frame perfect sealed**

## F Series

- **Terminals are gold-flashed**
- **Wide range of switching functions**
- **Wide choice of toggles**

| Toggles | | |
|---|---|---|
| Number of poles | 1, 2 and 4 | up to 4 |
| Contact timing | Break before Make | Break before Make |
| Right angle versions | No | No |
| Standard number of positions | 2 or 3 | 2 or 3 |
| Terminals / Mounting style | Quick connect | Leadwire hooking |
| Actuator style | Standard Toogle | Standard, long, locking; rocker style |
| Contact rating | 20 A @ 250 Vac | 6 A @ 250 Vac |
| Electrical endurance | 20,000 ops. | 50,000 ops. |
| Operating temperature range | -20…+70°C | -20…+70°C |
| Dimensions case (LxWxH) | 33 x 19.5...36.5 x 24.5 mm | 14.8 x 8...23 x 10.5 mm |
| Packaging | Bulk | Bulk |

# Push Buttons

## TP Series

- **Miniature**
- **Dual actuator available**

## MP Series

- **Caps in different colours**

| **Push buttons** | | |
|---|---|---|
| Number of poles | 1 or 2 | up to 4 |
| Contact timing | Break before Make | Break before Make |
| Right angle versions | right angle and vertical right angle | No |
| Sealing | Process sealed optional | MPE: splash proof (meets IP65) |
| Mounting style | THT, Wire lug, different bushing styles | THT, Panel mount, Wire lug |
| Actuator style | round, rectangular | Optional caps for MPA, MPE |
| Flush actuator versions | Yes | No |
| Contact rating | Gold: 20 mA @ 20 Vdc<br>Silver: 1 A @ 125 Vac, 28 Vdc | 6 A @ 120 Vac, 3 A @ 250 Vac |
| Electrical endurance | 100,000 ops. | 50,000 ops. |
| Operating temperature range | -30…+65°C | -20…+80°C |
| Dimensions case (LxWxH) | 8.1 x 5.2 x 8.1 mm | 13 x 8.1...22.5 x 14...17.3 mm |
| Packaging | Bulk | Bulk |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

## Micro Switches

### MP Miniature Micro Switch Series

- **Low and high current versions**

### SP Sub Miniature Micro Switch Series

- **Various actuator and mounting options**

### UP Ultra Miniature Micro Switch Series

- **Different mounting options**
- **Silver or gold contacts**

| **Micro switch** | | | |
|---|---|---|---|
| Contact configuration | SPDT, SPNC, SPNO | SPDT | SPDT |
| Right angle versions | No | No | left and right |
| Mounting style | Solder or Spade | TAB, THT, Solder terminals | THT |
| Actuator style | Pin plunger, short, normal, simulator lever, roller | Pin plunger, normal, long, simulator lever, roller | Straight lever, without lever |
| Standard actuation force | 16 A Version: 1.2, 2.0, 3.0 N<br>0.1 A Version: 0.55 N | 0.8…2.5 N | 0.3…1.5 N |
| Contact rating | 16 A @ 250 Vac<br>0.1 A @ 250 Vac | 5 A @ 250 Vac | UP3 version: 3A @ 125 Vac<br>UP01 version: 0.1 @ 30 Vdc |
| Electrical endurance | up to 100,000 ops. | up to 50,000 ops. | 1,000,000 ops. |
| Operating temperature range | -25…+130°C | -25…+80°C | -25…+80°C |
| Approvals | UL, cUL, ENEC | UL, cUL, ENEC | UL |
| Dimensions (LxWxH) | 27.8 x 10.2 x 15.9 mm | 19.8 x 6.4 x 10.6 mm | 12.7 x 5.8 x 6.7 mm |
| Packaging | Tray | Tray | Tray |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Power Rocker Switches

## PRA Series

- **13.0 mm x 19.2 mm panel cut-out**
- **Easy snap-in mounting**

## PRC Series

- **IP 66 waterproof**
- **21.2 mm x 36.6 mm panel cut-out**
- **Easy snap-in mounting**

NEW

## PRE Series

- **19.4 mm x 22.2 mm panel cut-out**
- **Easy snap-in mounting**

| Power Rocker Switch | | | |
|---|---|---|---|
| Number of poles | 1 or 2 | 1 or 2 | 2 |
| Sealing | Dust resistant, optional waterproof cover | IP 66 waterproof | Dust resistant |
| Type of terminals | Solder lug or Quick connect | Solder lug, Quick connect, Screw | Solder lug or Quick connect |
| Illumination versions | single pole versions only | No | Yes |
| Contact rating | 1 pole version: 10A @ 250 Vac<br>2 pole version: 6A @ 250 Vac | 10A @ 250 Vac | 6 A @ 250 Vac |
| Electrical endurance | ≥ 6,000 ops. | ≥ 6,000 ops. | ≥ 10,000 ops. |
| Operating temperature range | -20…+85°C | -20…+85°C | -20…+85°C |
| Approvals | 1 pole vers.: cUL (VDE, ENEC)<br>2 pole vers.: cUL | UL | UL, VDE, ENEC |
| Packaging | Tray | Tray | Tray |

## PRF Series

- **22.2 mm x 30.2 mm panel cut-out**
- **Easy snap-in mounting**

## PRG Series

- **11.2 mm x 30.2 mm panel cut-out**
- **Easy snap-in mounting**

| Power Rocker Switch | | |
|---|---|---|
| Number of poles | 2 | 1 |
| Sealing | Dust resistant | Dust resistant |
| Type of terminals | Solder lug or Quick connect | Solder lug or Quick connect |
| Illumination versions | Yes | Yes |
| Contact rating | 10 A @ 250 Vac | 10 A @ 250 Vac |
| Electrical endurance | ≥ 10,000 ops. | ≥ 6,000 ops. |
| Operating temperature range | -20…+85°C | -20…+85°C |
| Approvals | UL, VDE, ENEC | UL, VDE, ENEC |
| Packaging | Tray | Tray |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Preferred Part Numbers - DIP Switches

## GDS Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| GDS0204 | 2 | THT | tube | 1825006-1 |
| GDS02S04 | | SMT | | 1825006-3 |
| GDS02STR04 | | | tape and reel | 1825006-4 |
| GDS0404 | 4 | THT | tube | 1825006-5 |
| GDS04S04 | | SMT | | 1825006-7 |
| GDS04STR04 | | | tape and reel | 1825006-8 |
| GDS0604 | 6 | THT | tube | 1825006-9 |
| GDS06S04 | | SMT | | 1-1825006-1 |
| GDS06STR04 | | | tape and reel | 1-1825006-2 |
| GDS0804 | 8 | THT | tube | 1-1825006-3 |
| GDS08S04 | | SMT | | 1-1825006-5 |
| GDS08STR04 | | | tape and reel | 1-1825006-6 |
| GDS1004 | 10 | THT | tube | 1-1825006-7 |
| GDS10S04 | | SMT | | 1-1825006-9 |
| GDS10STR04 | | | tape and reel | 2-1825006-0 |

## GDP Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| GDP0204 | 2 | THT | tube | 1571998-1 |
| GDP02STR04 | | SMT | tape and reel | 1571998-4 |
| GDP0404 | 4 | THT | tube | 1571998-5 |
| GDP04STR04 | | SMT | tape and reel | 1571998-8 |
| GDP0604 | 6 | THT | tube | 1571998-9 |
| GDP06STR04 | | SMT | tape and reel | 1-1571998-2 |
| GDP0804 | 8 | THT | tube | 1-1571998-3 |
| GDP08STR04 | | SMT | tape and reel | 1-1571998-6 |
| GDP1004 | 10 | THT | tube | 1-1571998-7 |
| GDP10STR04 | | SMT | tape and reel | 2-1571998-0 |

## GDR Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| GDR0404 | 4 | THT | tube | 1825286-3 |
| GDR04S04 | | SMT | | 1825286-4 |
| GDR0804 | 8 | THT | | 1825286-7 |
| GDR08S04 | | SMT | | 1825286-8 |

## GDH Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| GDH02S04 | 2 | SMT | tube | 1571983-1 |
| GDH02STR04 | | | tape and reel | 1571983-3 |
| GDH04S04 | 4 | | tube | 1571983-4 |
| GDH04STR04 | | | tape and reel | 1571983-5 |
| GDH06STR04 | 6 | | | 1571983-9 |
| GDH08S04 | | | tube | 1-1571983-0 |
| GDH08STR04 | 8 | | tape and reel | 1-1571983-1 |

## GDHL Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| GDHL04S | 4 | SMT | tube | 1977103-3 |
| GDHL04STR | | | tape and reel | 1977103-4 |
| GDHL08S | 8 | | tube | 1977103-7 |
| GDHL08STR | | | tape and reel | 1977103-8 |

## ADE Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| ADE0204 | 2 | THT | tube | 1825057-1 |
| ADE0404 | 4 | | | 1825057-3 |
| ADE04S04 | | SMT | | 1825058-7 |
| ADE0604 | 6 | THT | | 1825057-5 |
| ADE0804 | 8 | | | 1825057-7 |
| ADE08S04 | | SMT | | 1-1825058-9 |
| ADE1004 | 10 | THT | | 1825057-9 |

## ADF Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| ADF flush actuator | | | | |
| ADF0204 | 2 | THT | tube | 1825002-1 |
| ADF0404 | 4 | | | 1825002-5 |
| ADF0604 | 6 | | | 1825002-9 |
| ADF0804 | 8 | | | 1-1825002-3 |
| ADF1004 | 10 | | | 1-1825002-7 |
| ADF flush actuator with seal tape | | | | |
| ADF02STTR04 | 2 | SMT | tape and reel | 1825059-6 |
| ADF04STTR04 | 4 | | | 1-1825059-8 |
| ADF06STTR04 | 6 | | | 3-1825059-0 |
| ADF08STTR04 | 8 | | | 4-1825059-2 |
| ADF10STTR04 | 10 | | | 5-1825059-4 |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

## Preferred Part Numbers - DIP Switches, DIP Shunts, Rotary (Continued)

### ADP Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| ADP0204 | 2 | THT | tube | 1571999-1 |
| ADP02STR04 | | SMT | tape and reel | 1571999-4 |
| ADP0404 | 4 | THT | tube | 1571999-6 |
| ADP04STR04 | | SMT | tape and reel | 1571999-9 |
| ADP0604 | 6 | THT | tube | 1-1571999-6 |
| ADP06STR04 | | SMT | tape and reel | 1-1571999-9 |
| ADP0804 | 8 | THT | tube | 2-1571999-6 |
| ADP08STR04 | | SMT | tape and reel | 2-1571999-9 |
| ADP1004 | 10 | THT | tube | 3-1571999-6 |
| ADP10STR04 | | SMT | tape and reel | 3-1571999-9 |

### STV, STR Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| STV04 | 4 | THT, vertical | tube | 1977104-2 |
| STV08 | 8 | | | 1977104-4 |
| STR04 | 4 | THT, horizontal | | 1977105-2 |
| STR08 | 8 | | | 1977105-4 |

### DIP Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| DIP01 | 1 | THT | tube | 5161390-1 |
| DIP02 | 2 | | | 5161390-2 |
| DIP03 | 3 | | | 5161390-3 |
| DIP04 | 4 | | | 5161390-4 |
| DIP05 | 5 | | | 5161390-5 |
| DIP08 | 8 | | | 5161390-8 |

### HTH DIP Shunts

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| HTH04 | 4 | THT | tube | 1825190-3 |
| HTH08 | 8 | | | 1825190-7 |

### DIP-Fix

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| DIP-FIX-A104 | 4 | THT | trays | 1393546-4 |
| DIP-FIX-A108 | 8 | | | 1393546-8 |
| DIP-FIX-A124 | 24 | | | 1-1393546-3 |
| DIP-FIX-A201 | 1 changeover | | | 1-1393546-4 |
| DIP-FIX-A202 | 2 changeover | | | 1-1393546-5 |
| DIP-FIX-A204 | 4 changeover | | | 1-1393546-7 |
| DIP-FIX-A212 | 12 changeover | | | 2-1393546-0 |

### MRD Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| MRD1004 | 10/BCD | THT | tube | 1825013-1 |
| MRD10STR04 | | SMT | tape and reel | 1-1825013-1 |
| MRD10CSTR04 | 10/BCD compl. | | | 1825013-6 |
| MRD1604 | 16/Hex | THT | tube | 1-1825013-1 |
| MRD16STR04 | | SMT | tape and reel | 2-1825013-0 |
| MRD16CSTR04 | 16/Hex compl. | | | 1-1825013-6 |

### DR-/D/M/S/W Series

| Product key | Positions | Mounting | Packaging | Part number |
|---|---|---|---|---|
| DRD10CE04 | 10/BCD compl. | THT | tube | 1825007-1 |
| DRD10E04 | 10/BCD | | | 1825007-6 |
| DRD10SETR04 | | SMT | tape and reel | 1-1825007-0 |
| DRD16CE04 | 16/Hex compl. | THT | tube | 1-1825007-1 |
| DRD16E04 | 16/Hex | | | 1-1825007-6 |
| DRD16SETR04 | | SMT | tape and reel | 2-1825007-0 |
| DRM10RA04 | 10/BCD | THT | tube | 1825008-6 |
| DRM16RA04 | 16/Hex | | | 1825008-8 |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.
Specifications subject to change.
www.tycoelectronics.com

## Preferred Part Numbers - Tactile Switches

### FSM . SM/JM Series, 3,5 x 6

| Product key | Act. Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSM SM/JM | | | | | |
| FSM2L | 1.3 N | 5 mm | THT | bulk | 1825965-1 |
| FSM1L | | 4.3 mm | | | 1825966-1 |
| FSM1SM | 1.8 N | | SMT | | 1437566-3 |
| FSM1SMTR | | | | tape and reel | 1437566-4 |
| FSM1JMTR | | 4.3 mm | SMT/J | | 147873-2 |
| FSM2JMTR | | 5 mm | | | 147873-1 |
| FSM SM/JM S, Sealed | | | | | |
| FSM2S | 1.3 N | 5 mm | THT | bulk | 1571297-1 |
| FSM2SSMTR | | | SMT | tape and reel | 1571298-2 |
| FSM1SJMTR | | 4.3 mm | SMT/J | | 1571299-2 |
| FSM2SJMTR | | 5 mm | | | 1571299-4 |

### FSM . SM/JM LP Series, 4 x 6

| Product key | Act. Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSMJMLPTR | 1.6 N | 2.5 mm | SMT/J | tape and reel | 1571528-1 |
| FSMJMLPATR | 2.6 N | | | | 1571528-2 |
| FSMSMLPTR | 1.6 N | | SMT | | 1825086-1 |
| FSMSMLPATR | 2.6 N | | | | 1825086-2 |

## Preferred Part Numbers - Tactile Switches (Continued)

**FSM 6 x 6 Series**

| Product key | Act. Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| **FSMJ Series** | | | | | |
| FSM2JH | 1.6 N | 4.3 mm | THT | bulk | 1825910-2 |
| FSM2JAH | 2.6 N | | | | 1825910-3 |
| **FSMCD, Square Button** | | | | | |
| FSMCD1H | 1.6 N | 7.5mm, □ 2.42mm | THT | bulk | 1825967-1 |
| FSMCD2H | | 7.5mm, □ 2.8mm | | | 1825967-2 |
| **FSMRACD, Square Button, Right Angle** | | | | | |
| FSMRACD1H | 1.6 N | 6.35mm, □ 2.42mm | THT | bulk | 1825968-1 |
| FSMRACD2H | | 6.35mm, □ 2.8mm | | | 1825968-2 |
| **FSMJSM, SMT Mounting** | | | | | |
| FSM2JSMLS | 1.0 N | 4.3 mm | SMT | bulk | 1977223-1 |
| FSM2JSMLSTR | | | | tape and reel | 1977223-2 |
| FSM2JSMAS | 1.6 N | | | bulk | 1977223-3 |
| FSM2JSMASTR | | | | tape and reel | 1977223-4 |
| FSM2JSMAAS | 2.6 N | | | bulk | 1977223-5 |
| FSM2JSMAASTR | | | | tape and reel | 1977223-6 |
| FSM4JSMXLS | 0.7 N | 5 mm | | bulk | 1-1977223-3 |
| FSM4JSMXLSTR | | | | tape and reel | 1-1977223-4 |
| FSM4JSMAS | 1.6 N | | | bulk | 1977223-9 |
| FSM4JSMASTR | | | | tape and reel | 1-1977223-0 |
| FSM4JSMAAS | 2.6 N | | | bulk | 1-1977223-1 |
| FSM4JSMAASTR | | | | tape and reel | 1-1977223-2 |
| FSM6JSMAS | 1.6 N | 7 mm | | bulk | 1-1977223-7 |
| FSM6JSMASTR | | | | tape and reel | 1-1977223-8 |
| FSM6JSMAAS | 2.6 N | | | bulk | 1-1977223-9 |
| FSM6JSMAASTR | | | | tape and reel | 2-1977223-0 |
| **FSMJEL, Extendet Life, J-Lead** | | | | | |
| FSM2JELJ | 1.6 N | 2.5 mm | SMT/J | bulk | 1571625-5 |
| FSM2JELJTR | | | | tape and reel | 1571625-6 |
| **FSMJEL, Extendet Life, Gull Wing** | | | | | |
| FSM2JELG | 1.6 N | 2.5 mm | SMT/G | bulk | 1571626-5 |
| FSM2JELGTR | | | | tape and reel | 1571626-6 |
| **FSMJEL, Extendet Life, Gull Wing, Ground Terminal** | | | | | |
| FSM2JELGE | 1.6 N | 2.5 mm | SMT/G | bulk | 1571636-5 |
| FSM2JELGETR | | | | tape and reel | 1571636-6 |
| **FSM1LP, Low Profile** | | | | | |
| FSM1LPS | 1.6 N | 3.09 mm | SMT | bulk | 1977263-1 |
| FSM1LPSTR | | | | tape and reel | 1977263-2 |
| FSM1LPAS | 2.6 N | | | bulk | 1977263-3 |
| FSM1LPASTR | | | | tape and reel | 1977263-4 |
| **FSMJS, Sealed 7.6 mm** | | | | | |
| FSM1JSSM | 1.6 N | 3.3 mm | SMT | bulk | 1571296-1 |
| FSM1JSSMTR | | | | tape and reel | 1571296-2 |
| FSM2JS | | 4.3 mm | THT | bulk | 1571295-1 |
| FSM2JSSM | | | SMT | | 1571294-1 |
| FSM2JSSMTR | | | | tape and reel | 1571294-2 |
| FSM4JS | | 5 mm | THT | bulk | 1571295-2 |
| FSM4JSSM | | | SMT | | 1571294-3 |
| FSM4JSSMTR | | | | tape and reel | 1571294-4 |
| **FSMJS, Sealed 6 mm** | | | | | |
| FSM1JS6 | 1.6 N | 4,3 mm | THT | bulk | 1977121-1 |
| FSM2JS6SM | | | SMT | | 1977265-1 |
| FSM2JS6SMTR | | | | tape and reel | 1977265-2 |
| **FSMRAJS, Sealed Right Angle** | | | | | |
| FSMRAJS1SM | 2.6 N | | SMT | bulk | 1571407-1 |
| FSMRAJS1SMTR | | | | tape and reel | 1571407-2 |
| **FSMRAJ, Right Angle** | | Shaft length | | | |
| FSMRA1JH | 1.6 N | 0.55 mm | THT | bulk | 1825027-2 |
| FSMRA2JH | | 1.25 mm | | | 1825027-5 |
| FSMRA3JH | | 3.25 mm | | | 1825027-8 |
| FSMRA4JH | | 5.74 mm | | | 1-1825027-1 |
| FSMRA5JH | | 3.55 mm | | | 1-1825027-4 |
| FSMRA6JH | | 4.25 mm | | | 1-1825027-7 |
| FSMRA7JH | | 9.25 mm | | | 2-1825027-0 |
| FSMRA8JH | | 13.26 mm | | | 2-1825027-3 |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

## Preferred Part Numbers - Tactile Switches (Continued)

### FSM 10 Series, 12 x 12

| Product key | Act Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSM10 | | | | | |
| FSM100 | 1.6 N | 4.3 mm | THT | bulk | 1437565-2 |
| FSM101 | | 7.5 mm | | | 1437565-3 |
| FSM102 | | 12 mm | | | 1437565-4 |
| FSM103 | | 7.3 mm | THT, square button | | 1437565-5 |
| FSM104 | | - | THT, right angle | | 1437565-6 |
| FSM10, Sealed | | | | | |
| FSM100SSM | 1.6 N | 4.3 mm | SMT | bulk | 1571218-1 |
| FSM100SSMTR | | | | tape and reel | 1571218-3 |
| FSM100S | | | THT | bulk | 1571220-1 |

### FSM Turtle

| Product key | Act Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSMMST | 1.6 N | 1.8 mm | SMT | bulk | 1571262-1 |
| FSMMSTTR | | | | tape and reel | 1571262-2 |

### FSMMSH Series

| Product key | Act Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSMMSHPTR | 1.6N | 3.3 mm | SMT, w/loc. pegs | tape and reel | 1977066-1 |
| FSMMSHTR | | | SMT, no pegs | | 1977067-1 |

### FSM . MS Series

| Product key | Act Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSM1MSJMPTR | 2.2±.8 N | 1.5 mm | SMT/J w/loc | tape and reel | 1571908-1 |
| FSM1MSJMTR | | | SMT/J wo/loc | | 1571908-2 |
| FSM2MSSMATR | 2.5±.5 N | 1.65 mm | SMT wo/loc | | 1571895-1 |
| FSM3MSJMPTR | 2.2±.8 N | | SMT/J w/loc | | 1571910-1 |
| FSM3MSJMTR | | | SMT/J wo/loc | | 1571910-2 |
| FSM3MSSMPTR | | | SMT w/loc | | 1571909-1 |
| FSM3MSSMTR | | | SMT wo/loc | | 1571909-2 |

### FSMCT Series

| Product key | Act Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSMCTTR | 1.6 N | 1.5 mm | SMT | tape and reel | 8-1437565-0 |
| FSMCTATR | 2.6 N | | | | 8-1437565-1 |

### FSMLPU

| Product key | Act Force | Height | Mounting | Packaging | Part number |
|---|---|---|---|---|---|
| FSMLPUTR | 1.6 N | 0.5 mm | SMT | tape and reel | 1825534-1 |

# Preferred Part Numbers - Slide Switches

## ASE Series

| Product key | Type | Contact material | Mounting | Part number |
|---|---|---|---|---|
| **ASE** | | | | |
| ASE2204 | DPDT | Ag | THT | 1825010-1 |
| ASE22G04 | | Au | | 1825010-2 |
| ASE22GL04 | | | SMT/L | 1825010-5 |
| ASE22GS04 | | | SMT/rev. L | 1825010-7 |
| ASE22L04 | | Ag | SMT/L | 1825010-6 |
| ASE22S04 | | | SMT/rev. L | 1825010-8 |
| ASE4204 | 4PDT | | THT | 1-1825010-3 |
| ASE42G04 | | Au | | 1-1825010-4 |
| ASE42GL04 | | | SMT/L | 1-1825010-7 |
| ASE42L04 | | Ag | | 1-1825010-8 |
| ASE42S04 | | | SMT/rev. L | 2-1825010-0 |
| ASE6204 | 6PDT | | THT | 3-1825010-7 |
| ASE62G04 | | Au | | 3-1825010-8 |
| ASE62GL04 | | | SMT/L | 4-1825010-1 |
| ASE62L04 | | Ag | | 4-1825010-2 |
| **ASE Side Actuator** | | | | |
| ASE22R04 | DPDT | Ag | THT | 1825010-3 |
| ASE22RG04 | | Au | | 1825010-4 |
| ASE22RGS04 | | | SMT/rev. L | 1-1825010-1 |
| ASE22RL04 | | Ag | SMT/L | 1-1825010-0 |
| ASE22RS04 | | | SMT/rev. L | 1-1825010-2 |
| ASE42R04 | 4PDT | | THT | 1-1825010-5 |
| ASE42RG04 | | Au | | 1-1825010-6 |
| ASE42RGL04 | | | SMT/L | 2-1825010-1 |
| ASE42RL04 | | Ag | | 2-1825010-2 |
| ASE42RS04 | | | SMT/rev. L | 2-1825010-4 |
| ASE43R04 | 4P3T | | THT | 2-1825010-7 |
| ASE43RG04 | | Au | | 2-1825010-8 |
| ASE62R04 | 6PDT | Ag | | 3-1825010-9 |
| ASE62RG04 | | Au | | 4-1825010-0 |
| ASE62RGL04 | | | SMT/L | 4-1825010-5 |
| ASE62RL04 | | Ag | | 4-1825010-6 |

## ASF Series

| Product key | Type | Contact material | Mounting | Part number |
|---|---|---|---|---|
| **ASF** | | | | |
| ASF2204 | DPDT | Ag | THT | 1825011-1 |
| ASF22G04 | | Au | | 1825011-2 |
| ASF22GL04 | | | SMT/L | 1825011-5 |
| ASF22GS04 | | | SMT/rev. L | 1825011-9 |
| ASF22L04 | | Ag | SMT/L | 1825011-7 |
| ASF22S04 | | | SMT/rev. L | 1-1825011-1 |
| ASF4204 | 4PDT | | THT | 2-1825011-1 |
| ASF42G04 | | Au | | 2-1825011-2 |
| ASF42GL04 | | | SMT/L | 2-1825011-5 |
| ASF42L04 | | Ag | | 2-1825011-7 |
| ASF42S04 | | | SMT/rev. L | 3-1825011-1 |
| ASF6204 | 6PDT | | THT | 6-1825011-1 |
| ASF62G04 | | Au | | 6-1825011-2 |
| ASF62GL04 | | | SMT/L | 6-1825011-5 |
| ASF62L04 | | Ag | | 6-1825011-7 |
| ASF62S04 | | | SMT/rev. L | 7-1825011-1 |
| **ASF Side Actuator** | | | | |
| ASF22R04 | DPDT | Ag | THT | 1825011-3 |
| ASF22RG04 | | Au | | 1825011-4 |
| ASF22RGL04 | | | SMT/L | 1-1825011-3 |
| ASF22RGS04 | | | SMT/rev. L | 1-1825011-7 |
| ASF22RS04 | | Ag | | 1-1825011-9 |
| ASF42R04 | 4PDT | | THT | 2-1825011-3 |
| ASF42RG04 | | Au | | 2-1825011-4 |
| ASF42RGL04 | | | SMT/L | 3-1825011-3 |
| ASF42RL04 | | Ag | | 3-1825011-5 |
| ASF42STR04 | | | SMT/rev. L | 3-1825011-2 |
| ASF62R04 | 6PDT | | THT | 6-1825011-3 |
| ASF62RG04 | | Au | | 6-1825011-4 |
| ASF62RGL04 | | | SMT/L | 7-1825011-3 |
| ASF62RGS04 | | | SMT/rev. L | 7-1825011-7 |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

## Preferred Part Numbers - Slide Switches (Continued)

### S, SE Series

| Product key | Type | Mounting | Packaging | Part number |
|---|---|---|---|---|
| **S** | | | | |
| S1EGPC04 | 1 Pole, On-Off-On | THT | bulk | 5-1571005-2 |
| S2EGPC04 | 2 Pole, On-Off-On | | | 5-1571005-4 |
| **S Right Angle** | | | | |
| S1EGRA04 | 1 Pole, On-Off-On | THT | bulk | 5-1571006-2 |
| S2EGRA04 | 2 Pole, On-Off-On | | | 5-1571006-4 |
| **SE Sealed** | | | | |
| SE1EGPC04 | 1 Pole, On-Off-On | THT | bulk | 1825032-2 |
| SE2EGPC04 | 2 Pole, On-Off-On | | | 1825032-4 |
| SE1GSMTTR04 | 1 Pole, On-Off | SMT | tape and reel | 5-1571004-4 |
| SE1EGSMTTR04 | 1 Pole, On-Off-On | | | 5-1571004-5 |
| **SE Sealed Right Angle** | | | | |
| SE1EGRA04 | 1 Pole, On-Off-On | THT | bulk | 1825031-2 |
| SE2EGRA04 | 2 Pole, On-Off-On | | | 1825031-4 |

### STS, SDS Series

| Product key | Type | Mounting | Throw function | Part number |
|---|---|---|---|---|
| STS121PC04 | SPDT | THT | | 1825159-1 |
| STS1300PC04 | SP3T | | common pin 2 | 1825161-1 |
| STS131PC04 | | | | 1825159-2 |
| STS1400PC04 | SP4T | | common pin 3 | 1825161-2 |
| STS141PC04 | | | | 1825159-3 |
| STS151PC04 | SP5T | | | 1825159-4 |
| STS161PC04 | SP6T | | | 1825159-5 |
| STS220PC04 | DPDT | | | 1825163-1 |
| STS2300PC04 | DP3T | | common pin 2 | 1825164-1 |
| STS230PC04 | | | | 1825163-2 |
| STS2400PC04 | DP4T | | common pin 3 | 1825165-1 |
| STS240PC04 | | | | 1825163-3 |
| STS250PC04 | DP5T | | | 1825163-4 |
| STS260PC04 | DP6T | | | 1825163-5 |

### TSS Series

| Product key | Type | Positions | Packaging | Part number |
|---|---|---|---|---|
| **TSS Single** | | | | |
| TSS11DGPC04 | SPDT | On-None-On | bulk | 1571982-1 |
| TSS11EGPC04 | | On-Off-On | | 1571982-4 |
| **TSS Single, Flush actuator** | | | | |
| TSS11DG1PC04 | SPDT | On-None-On | bulk | 1571982-2 |
| TSS11EG1PC04 | | On-Off-On | | 1571982-3 |
| **TSS Dual** | | | | |
| TSS21KGPC04 | DPST | On-None-Off | bulk | 1571982-5 |
| TSS21NGPC04 | DPDT | On-None-On | | 1571982-7 |
| TSS21PGPC04 | | On-Off-On | | 1571982-9 |
| **TSS Dual, Flush actuator** | | | | |
| TSS21NG1PC04 | DPST | On-None-Off | bulk | 1571982-6 |
| TSS21PG1PC04 | DPDT | On-None-On | | 1571982-8 |
| TSD21DDGPC04 | | On-Off-On | | 1825015-1 |

### MSS, MSSA Series

| Product key | Type | Contact material | Version | Part number |
|---|---|---|---|---|
| MSS120004 | SPDT | Ag | vertical | 1825257-1 |
| MSS1200G04 | | Au | | 1825257-2 |
| MSS1200R04 | | Ag | right angle | 1825258-1 |
| MSS1200RG04 | | Au | | 1825258-2 |
| MSS130004 | SP3T | Ag | vertical | 1825259-1 |
| MSS1300G04 | | Au | | 1825259-2 |
| MSS1300R04 | | Ag | right angle | 1825260-1 |
| MSS1300RG04 | | Au | | 1825260-2 |
| MSS140004 | SP4T | Ag | vertical | 1571423-2 |
| MSS222504 | DPDT | | | 1825262-1 |
| MSS2225G04 | | Au | | 1825262-2 |
| MSS420004 | 4PDT | Ag | | 1825264-1 |
| MSS4200G04 | | Au | | 1825264-2 |
| MSS4200R04 | | Ag | right angle | 1825265-1 |
| MSS4200RG04 | | Au | | 1825265-2 |
| MSS430004 | 4P3T | Ag | vertical | 1825267-1 |
| MSS4300G04 | | Au | | 1825267-2 |
| MSS4300R04 | | Ag | right angle | 1825268-1 |
| MSS4300RG04 | | Au | | 1825268-2 |
| MSS620004 | 6PDT | Ag | vertical | 1825271-1 |
| MSS6200G04 | | Au | | 1825271-2 |
| MSS635004 | 6P3T | Ag | | 1825273-1 |
| MSS6350R04 | | | right angle | 1825274-1 |

## Preferred Part Numbers - Slide Switches (Continued)

### MSSA-01/04

| Product key | Type | Contact material | Positions | Part number |
|---|---|---|---|---|
| MSSA111DG | SPDT | Au | On-None-On | 2-1437580-9 |
| MSSA111EG | | | On-Off-On | 3-1437580-0 |
| MSSA114D | | Ag | On-None-On | 3-1437580-1 |
| MSSA114E | | | On-Off-On | 3-1437580-2 |
| MSSA211NG | DPDT | Au | On-None-On | 4-1437580-9 |
| MSSA211N | | Ag | | 5-1437580-2 |

### MHS Series

| Product key | Type | Contact material | Positions | Part number |
|---|---|---|---|---|
| MHS | | | | |
| MHS12204 | SPDT | Ag | On-None-On | 1825255-1 |
| MHS122G04 | | Au | | 1825255-2 |
| MHS12304 | | Ag | On-Off-On | 1825255-5 |
| MHS13304 | SP3T | | On-On-On | 1825255-7 |
| MHS133G04 | | Au | | 1825255-8 |
| MHS22204 | DPDT | Ag | On-None-On | 1825289-1 |
| MHS222G04 | | Au | | 1825289-2 |
| MHS22304 | | Ag | On-Off-On | 1825289-5 |
| MHS223G04 | | Au | | 1825289-6 |
| MHS23304 | DP3T | Ag | On-On-On | 1825289-8 |
| MHS233G04 | | Au | | 1825289-9 |
| MHS Right Angle | | | | |
| MHS122GRA04 | SPDT | Au | On-None-On | 1825256-4 |
| MHS122RA04 | | Ag | | 1825256-1 |
| MHS123GRA04 | | Au | On-Off-On | 1825256-5 |
| MHS123RA04 | | Ag | | 1825256-2 |
| MHS133GRA04 | SP3T | Au | On-On-On | 1825256-6 |
| MHS133RA04 | | Ag | | 1825256-3 |
| MHS222GRA04 | DPDT | Au | On-None-On | 1825290-4 |
| MHS222RA04 | | Ag | | 1825290-1 |
| MHS223GRA04 | | Au | On-Off-On | 1825290-5 |
| MHS223RA04 | | Ag | | 1825290-2 |
| MHS233GRA04 | DP3T | Au | On-On-On | 1825290-6 |
| MHS233RA04 | | Ag | | 1825290-3 |

### SSJ Series

| Product key | Type | Contact material | Style | Part number |
|---|---|---|---|---|
| SSJ1204 | SPDT | Ag | vertical | 1825280-1 |
| SSJ12R04 | | | right angle | 1825282-1 |
| SSJ1304 | SP3T | | vertical | 1825283-1 |

### SSA Series

| Product key | Type | Contact material | Style | Part number |
|---|---|---|---|---|
| SSA1204 | SPDT | Ag | vertical | 1571981-1 |
| SSA12G04 | | Au | | 1571981-2 |
| SSA2204 | DPDT | Ag | | 1571981-3 |
| SSA22G04 | | Au | | 1571981-4 |

### SLS/SL/SLSA Series

| Product key | Type | Mounting | Style | Part number |
|---|---|---|---|---|
| SLS121PC04 | SPDT | THT | vertical | 1825115-1 |
| SLS121RA04 | | | right angle | 1825116-1 |
| SLS131PC04 | SP3T | | vertical | 1825117-1 |
| SLS131RA04 | | | right angle | 1825118-1 |
| SLS141PC04 | SP4T | | vertical | 1825119-1 |
| SLS141RA04 | | | right angle | 1825120-1 |
| SLS151PC04 | SP5T | | vertical | 1825121-1 |
| SLS151RA04 | | | right angle | 1825122-1 |
| SLS220PC04 | DPDT | | vertical | 1825080-1 |
| SLS230PC04 | DP3T | | | 1825080-2 |
| SLS240PC04 | DP4T | | | 1825080-3 |
| SLS250PC04 | DP5T | | | 1825080-4 |
| SLS260PC04 | DP6T | | | 1825080-5 |

### MLL Series

| Product key | Type | Mounting | Packaging | Part number |
|---|---|---|---|---|
| MLL1200S | SPDT | SMT | tube | 1437575-1 |
| MLL1200STR | | | tape and reel | 1437575-2 |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Preferred Part Numbers - Toggle Switches

## TST Series

| Product key | Type | Contact material | Positions | Part number |
|---|---|---|---|---|
| **TST** | | | | |
| TST11DGPC1D04 | 1 Pole, PCB | Ag | On-None-On | 1825455-1 |
| **TST, Right Angle** | | | | |
| TST11DGRA1D04 | 1 Pole | Ag | On-None-On | 1825455-3 |
| TST11DGVRA1D04 | 1 Pole Vertical r.a. | | | 1825455-4 |

## TT Series

| Product key | Type | Contact material | Positions | Part number |
|---|---|---|---|---|
| **TT** | | | | |
| TT13A2T04 | 1 Pole, Wire Lugs | Ag | On-None-Off | 1825222-2 |
| TT13D2T04 | | | On-None-On | 1825222-3 |
| TT13E2T04 | | | On-Off-On | 1825222-4 |
| TT23K2T04 | 2 Pole, Wire Lugs | | On-None-Off | 1825222-6 |
| TT23N2T04 | | | On-None-On | 1825222-7 |
| TT11AGPC104 | 1 Pole, PCB | | On-None-Off | 1825219-2 |
| TT11DGPC104 | | | On-None-On | 1825219-3 |
| TT11EGPC104 | | | On-Off-On | 1825219-6 |
| TT21KGPC104 | 2 Pole, PCB | | On-None-Off | 1-1825219-0 |
| TT21NGPC104 | | | On-None-On | 1-1825219-1 |
| **TT Right Angle** | | | | |
| TT11DGVRA104 | 1 Pole, PCB | Ag | On-None-On | 1825219-5 |
| TT11EGVRA104 | 2 Pole, PCB | | On-Off-On | 1825219-9 |

## Gemini Series A

| Product key | Type | Contact material | Positions | Part number |
|---|---|---|---|---|
| **Gemini A** | | | | |
| A101SYCB04 | 1 Pole, PCB | Au | On - On | 4-1825136-4 |
| A101SYCQ04 | | Ag | | 4-1825136-5 |
| A101SYZB04 | 1 Pole, Wire Lug | Au | | 4-1825136-8 |
| A101SYZQ04 | | Ag | | 4-1825136-9 |
| A103SYCB04 | 1 Pole, PCB | Au | On - Off - On | 1-1825137-5 |
| A103SYCQ04 | | Ag | | 1-1825137-6 |
| A103SYZB04 | 1 Pole, Wire Lug | Au | | 1-1825137-9 |
| A103SYZQ04 | | Ag | | 2-1825137-0 |
| A201SYCB04 | 2 Pole, PCB | Au | On - On | 2-1825138-4 |
| A201SYCQ04 | | Ag | | 2-1825138-5 |
| A201SYZB04 | 2 Pole, Wire Lug | Au | | 2-1825138-7 |
| A201SYZQ04 | | Ag | | 2-1825138-8 |
| A203SYCB04 | 2 Pole, PCB | Au | On - Off - On | 1825139-8 |
| A203SYCQ04 | | Ag | | 1825139-9 |
| A203SYZQ04 | 2 Pole, Wire Lug | | | 1-1825139-0 |
| A211SYCQ04 | 2 Pole, PCB | | On - On - On | 3-1825139-7 |
| A211SYZQ04 | 2 Pole, Wire Lug | | | 3-1825139-9 |
| **Gemini A, Right Angle** | | | | |
| A101SYAV2B04 | 1 Pole, PCB | Au | On - On | 1825136-8 |
| A103SYAV2B04 | | | On - Off - On | 2-1825136-5 |
| A103SYAV2Q04 | | Ag | | 1-1825137-4 |

## Gemini Series AE

| Product key | Type | Contact material | Positions | Part number |
|---|---|---|---|---|
| **Gemini AE** | | | | |
| AE101SD1CB04 | 1 Pole, PCB | Au | On-On | 2-1825142-0 |
| AE101SD1CQ04 | | Ag | | 2-1825142-1 |
| AE103SD1CB04 | | Au | On-Off-On | 3-1825142-0 |
| AE103SD1CQ04 | | Ag | | 3-1825142-1 |
| AE201SD1CB04 | 2 Pole, PCB | Au | On-On | 1-1825143-0 |
| AE201SD1CQ04 | | Ag | | 1-1825143-1 |
| AE203SD1CB04 | | Au | On-Off-On | 1-1825143-9 |
| **Gemini AE, Right Angle** | | | | |
| AE101SD1AV2B04 | 1 Pole, PCB | Au | On-On | 1-1825142-8 |
| AE101SD1AV2Q04 | | Ag | | 1-1825142-9 |
| AE103SD1AV2B04 | | Au | On-Off-On | 2-1825142-9 |
| AE201SD1AV2B04 | 2 Pole, PCB | | On-On | 1825143-9 |
| AE203SD1AV2B04 | | | On-Off-On | 1-1825143-7 |
| AE203SD1AV2Q04 | | Ag | | 1-1825143-8 |

# Preferred Part Numbers - Toggle Switches, Push Buttons

## MT Series

| Product key | Type | Contact material | Position | Part number |
|---|---|---|---|---|
| **MTA** | | | | |
| MTA306D04 | 3PDT, wire lug | Ag gold flash | On-None-On | 3-1571920-0 |
| MTA306DPC04 | 3PDT, THT | | | 3-1571920-1 |
| MTA306E04 | 3PDT, wire lug | | On-Off-On | 3-1571920-2 |
| MTA306EPC04 | 3PDT, THT | | | 3-1571920-3 |
| MTA406N04 | 4PDT, wire lug | | On-None-On | 3-1571920-8 |
| MTA406NPC04 | 4PDT, THT | | | 3-1571920-9 |
| MTA406P04 | 4PDT, wire lug | | On-Off-On | 4-1571920-0 |
| MTA406PPC04 | 4PDT, THT | | | 4-1571920-3 |
| **MTA Right Angle** | | | | |
| MTA8106DVRA04 | SPDT, THT | Ag gold flash | On-None-On | 1571922-4 |
| MTA8106EVRA04 | | | On-Off-On | 1571922-8 |
| **MTE (Sealed)** | | | | |
| MTE306D04 | 3PDT, wire lug | Ag gold flash | On-None-On | 1-1571924-6 |
| MTE306E04 | | | On-Off-On | 1-1571924-7 |
| MTE406N04 | 4PDT, wire lug | | On-None-On | 1-1571924-8 |
| MTE406P04 | | | On-Off-On | 1-1571924-9 |

## AW Series

| Product key | Type | Contact material | Position | Part number |
|---|---|---|---|---|
| AWTD1504 | 1 pole, tab | Ag | On-On | 7-6437630-0 |
| AWTN1504 | 2 pole, tab | | | 7-6437630-2 |
| AWTR1504 | | | On-(On) | 5-6437630-0 |
| AWTS1504 | | | (On)-Off-(On) | 1-6437630-1 |
| AWTT1504 | | | On-Off-(On) | 1-6437630-0 |

## F Series

| Product key | Type | Contact material | Position | Part number |
|---|---|---|---|---|
| FTD0904 | 1 pole, std. | Ag | On-On | 2-6437630-0 |
| FTD09G04 | | Au | | 3-6437630-4 |
| FTD5904 | 1 pole, locking | Ag | | 1-6437630-5 |
| FTD59G04 | | Au | | 4-6437630-0 |
| FTD7904 | 1 pole, Long | Ag | | 5-6437630-3 |
| FTE0904 | 1 pole, std. | | On-Off-On | 6-6437630-2 |
| FTH0904 | | | On-Off-(On) | 4-6437630-8 |
| FTN0904 | 2 pole, std. | | On-On | 4-6437630-2 |
| FTN5904 | 2 pole, locking | | | 3-6437630-9 |
| FTN59G04 | | Au | | 6-6437630-1 |
| FTP0904 | 2 pole, std. | Ag | On-Off-On | 4-6437630-6 |
| FTPA0904 | | | On-On-On | 4-6437630-5 |
| FTS0904 | | | (On)-Off-(On) | 4-6437630-3 |
| F4TN0904 | 4 pole, std. | | | 3-6437630-5 |

## TP Series

| Product key | Type | Contact material | Version | Part number |
|---|---|---|---|---|
| **TPA** | | | | |
| TPA11CGPC004 | SPST, THT | Au | Rnd. no bushing | 1825096-1 |
| TPA11FGPC004 | SPDT, THT | | | 1825096-7 |
| **TPA, Right Angle** | | | | |
| TPA11CGRA004 | SPST, THT | Au | Rnd. no bushing | 1825096-4 |
| TPA11FGRA004 | SPDT, THT | | | 1-1825096-0 |
| **TPB** | | | | |
| TPB11CGPC004 | SPST, THT | Au | Rnd. 0.188", | 1825097-1 |
| TPB11FGPC004 | SPDT, THT | | unthreaded | 1825097-9 |
| TPB21MGPC004 | DPST, THT | | | 1-1825097-7 |
| **TPB, Right Angle** | | | | |
| TPB11CGRA004 | SPST, THT | Au | Rnd. 0.188", | 1825097-6 |
| TPB11FGRA004 | SPDT, THT | | unthreaded | 1-1825097-1 |



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

# Preferred Part Numbers - Push Buttons

**MP Series**

| Product key | Type | Mounting | Function | Part number |
|---|---|---|---|---|
| **MPA** | | | | |
| MPA106D04 | SPDT | Wire Lug | Push On/ Push Off | 1825040-1 |
| MPA106DPC04 | | THT | | 1825040-3 |
| MPA106F04 | | Wire Lug | Momentary | 1825040-2 |
| MPA106FPC04 | | THT | | 1825040-4 |
| MPA206N04 | DPDT | Wire Lug | Push On/ Push Off | 1825040-5 |
| MPA206NPC04 | | THT | | 1825040-6 |
| MPA206R04 | | Wire Lug | Momentary | 1825040-7 |
| MPA206RPC04 | | THT | | 1825040-8 |
| MPA306D04 | 3PDT | Wire Lug | Push On/ Push Off | 1825040-9 |
| MPA306F04 | | | Momentary | 1-1825040-0 |
| MPA406N04 | 4PDT | | Push On/ Push Off | 1-1825040-1 |
| MPA406R04 | | | Momentary | 1-1825040-2 |
| **MPE (Splash proof)** | | | | |
| MPE106D04 | SPDT | Wire Lug | Push On/ Push Off | 1825041-1 |
| MPE106F04 | | | Momentary | 1825041-2 |
| MPE206N04 | DPDT | | Push On/ Push Off | 1825041-3 |
| MPE206R04 | | | Momentary | 1825041-4 |
| MPE306D04 | 3PDT | | Push On/ Push Off | 1825041-5 |
| MPE306F04 | | | Momentary | 1825041-6 |
| MPE406N04 | 4PDT | | Push On/ Push Off | 1825041-7 |
| MPE406R04 | | | Momentary | 1825041-8 |
| **MPG** | | | | |
| MPG106D04 | SPDT | Wire Lug | Push On/ Push Off | 1825042-1 |
| MPG106F04 | | | Momentary | 1825042-3 |
| MPG206N04 | DPDT | | Push On/ Push Off | 1825042-5 |
| MPG206NPC04 | | THT | | 1825042-6 |
| MPG206R04 | | Wire Lug | Momentary | 1825042-7 |
| MPG206RPC04 | | THT | | 1825042-8 |
| MPG306D04 | 3PDT | Wire Lug | Push On/ Push Off | 1825042-9 |
| MPG306F04 | | | Momentary | 1-1825042-0 |
| MPG406N04 | 4PDT | | Push On/ Push Off | 1-1825042-1 |
| MPG406R04 | | | Momentary | 1-1825042-2 |

## Preferred Part Numbers - Micro Switches

### MP Miniature Micro Switch

| Product key | Terminals | Contacts | Actuator | Operating/Release | Part number |
|---|---|---|---|---|---|
| MP16DTCOLG | spade terminal | SPDT 16 A | pin plunger | 2.0 N / 0.5 N | 1-1478607-1 |
| MP16DTCNLD | | | normal lever | | 1-1478607-3 |
| MP16DTCNRD | | | normal roller | | 1-1478607-6 |
| MP16DTCSMD | | | simulator lever | | 1-1478607-7 |

### SP Sub Miniature Micro Switch

| Product key | Terminals | Contacts | Actuator | Operating/Release | Part number |
|---|---|---|---|---|---|
| SP5DTBOLE | PCB | SPDT 5 A | pin plunger | 1.5 N / 0.2 N | 1-1478601-1 |
| SP5DTBNLC | | | normal lever | | 1-1478601-2 |
| SP5DTBNRD | | | normal roller | | 1-1478601-4 |
| SP5DTBSMA | | | simulator lever | | 1-1478601-5 |

### UP Ultra Miniature Micro Switch

| Product key | Terminals | Contacts | Actuator | Operating/Release | Part number |
|---|---|---|---|---|---|
| UP3DTANLA04 | PCB | SPDT | normal lever | 0.5 N / 0.08 N | 1-1825043-5 |
| UP3DTAOLA04 | | 3A | pin plunger | 1.5 N / 0.2 N | 1-1825043-3 |
| UP01DTANLA04 | | SPDT | normal lever | 0.5 N / 0.08 N | 1825043-3 |
| UP01DTAOLA04 | | 0.1A | pin plunger | 1.5 N / 0.2 N | 1825043-1 |

# Preferred Part Numbers - Power Rocker Switches

## PRA Series

| Product key | Switch function | Rocker color | Text pattern | Part number |
|---|---|---|---|---|
| PRA Series, 13.0x19.2mm panel cutout, 10A single pole | | | | |
| PRASA1-16F-BB000 | On-Off, opaque | black | not applicable | 1571076-9 |
| PRASA1-16F-BB0BW | | | 0 - , white printing | 1-1571076-0 |
| PRASA1-16F-BB0CW | | | 0 I , white printing | 1-1571076-1 |
| PRASA1-16F-BR000 | | red | not applicable | 6-1571076-5 |
| PRASA1-16F-BB0HW | | black | ON OFF, white pr. | 2-1571076-0 |
| PRASD1-16F-BB000 | | | not applicable | 1571079-4 |
| PRASD1-16F-BB0DW | | | - = , white printing | 1571079-5 |
| PRASD1-16F-BB0EW | | | I II , white printing | 1571079-6 |
| PRASD3-16F-BB000 | On-Off-On, opaque | | not applicable | 1571079-7 |
| PRASD3-16F-BB0FW | | | - 0 =, white printing | 1571079-8 |
| PRASD3-16F-BB0GW | | | I 0 II, white printing | 1571079-9 |
| PRASD2-16F-BB000 | On-(On), opaque | | not applicable | 1-1571079-0 |
| PRASD2-16F-BB0DW | | | - = , white printing | 1-1571079-1 |
| PRASD2-16F-BB0EW | | | I II , white printing | 1-1571079-2 |
| PRASD4-16F-BB000 | On-Off-(On), opaque | | not applicable | 1-1571079-3 |
| PRASD4-16F-BB0FW | | | - 0 =, white printing | 1-1571079-4 |
| PRASD4-16F-BB0GW | | | I 0 II, white printing | 1-1571079-5 |
| PRA Series, 13.0x19.2mm panel cutout, 6A double pole | | | | |
| PRADA1-12F-BB000 | On-Off, opaque | black | not applicable | 1977068-1 |
| PRADA1-12F-BB0BW | | | 0 - , white printing | 1977068-2 |
| PRADA1-12F-BB0CW | | | 0 I , white printing | 1977068-3 |
| PRADA1-12F-BR000 | | red | not applicable | 1977068-4 |
| PRADA1-12F-BR0BW | | | 0 - , white printing | 1977068-5 |
| PRADD1-12F-BB000 | | black | not applicable | 1977069-1 |
| PRADD1-12F-BB0DW | | | - = , white printing | 1977069-2 |
| PRADD1-12F-BB0EW | | | I II , white printing | 1977069-3 |
| PRADD3-12F-BB000 | On-Off-On, opaque | | not applicable | 1977069-4 |
| PRADD3-12F-BB0FW | | | - 0 =, white printing | 1977069-5 |
| PRADD3-12F-BB0GW | | | I 0 II, white printing | 1977069-6 |
| PRADD2-12F-BB000 | | | | 1977069-7 |
| PRADD2-12F-BB0DW | On-(On), opaque | | - = , white printing | 1977069-8 |
| PRADD2-12F-BB0EW | | | I II , white printing | 1977069-9 |
| PRADD4-12F-BB000 | On-Off-(On), opaque | | not applicable | 1-1977069-0 |
| PRADD4-12F-BB0FW | | | - 0 =, white printing | 1-1977069-1 |
| PRADD4-12F-BB0GW | | | I 0 II, white printing | 1-1977069-2 |

## PRC Series

| Product key | Switch function | Rocker color | Text pattern | Part number |
|---|---|---|---|---|
| PRCSA1-20F-BB0BW | On-Off, opaque | black | 0 - , white printing | 1571095-2 |
| PRCSD1-20F-BB0DW | On-On, opaque | | - = , white printing | 1571100-2 |
| PRCDA1-20F-BB0BW | On-Off, opaque | | 0 - , white printing | 1571102-2 |
| PRCDD1-20F-BB0DW | On-On, opaque | | - = , white printing | 1571099-2 |

## PRE Series

| Product key | Switch function | Rocker color | Text pattern | Part number |
|---|---|---|---|---|
| PREDA1-07F-BB000 | On-Off, opaque | black | not applicable | 1634200-1 |
| PREDA1-07F-BB0BW | | | 0 - , white printing | 1634200-2 |
| PREDA1-07F-BB0CW | | | 0 I , white printing | 1634200-3 |
| PREDB1-07F-BR000 | On-Off, illuminated | red | not applicable | 1634200-7 |
| PREDB1-07F-BG000 | | green | | 1634200-9 |
| PREDD1-07F-BB000 | On-On, opaque | black | | 1-1634200-1 |
| PREDD1-07F-BB0DW | | | I II , white printing | 1-1634200-2 |
| PREDD1-07F-BB0EW | | | - = , white printing | 1-1634200-3 |
| PREDD3-07F-BB0FW | On-Off-On, opaque | | I 0 II, white printing | 1-1634200-7 |
| PREDD3-07F-BB0GW | | | - 0 =, white printing | 1-1634200-8 |
| PREDD4-07F-BB000 | On-Off-(On), opaque | | not applicable | 2-1634200-1 |
| PREDD4-07F-BB0FW | | | I 0 II, white printing | 2-1634200-2 |
| PREDD4-07F-BB0GW | | | - 0 =, white printing | 2-1634200-3 |
| PREDD5-07F-BB000 | (On)-Off-(On), opaque | | not applicable | 2-1634200-4 |
| PREDD5-07F-BB0FW | | | I 0 II, white printing | 2-1634200-5 |
| PREDD5-07F-BB0GW | | | - 0 =, white printing | 2-1634200-6 |

## Preferred Part Numbers - Power Rocker Switches (Continued)

### PRF Series

| Product key | Switch function | Rocker color | Text pattern | Part number |
|---|---|---|---|---|
| PRFDA1-16F-BB000 | On-Off, opaque | black | not applicable | 1634201-1 |
| PRFDA1-16F-BB0BW | | | 0 - , white printing | 1634201-2 |
| PRFDA1-16F-BB0CW | | | 0 I , white printing | 1634201-3 |
| PRFDB1-16F-BR000 | On-Off, illuminated | red | not applicable | 1634201-4 |
| PRFDB1-16F-BG000 | | green | | 1634201-5 |
| PRFDB1-16F-BY000 | | yellow | | 1634201-6 |
| PRFDD1-16F-BB000 | On-On, opaque | black | | 1634201-7 |
| PRFDD1-16F-BB0DW | | | I II , white printing | 1634201-8 |
| PRFDD1-16F-BB0EW | | | - = , white printing | 1634201-9 |
| PRFDD3-16F-BB000 | On-Off-On, opaque | | not applicable | 1-1634201-0 |
| PRFDD3-16F-BB0FW | | | I 0 II, white printing | 1-1634201-1 |
| PRFDD3-16F-BB0GW | | | - 0 =, white printing | 1-1634201-2 |

### PRG Series

| Product key | Switch function | Rocker color | Text pattern | Part number |
|---|---|---|---|---|
| PRGSB1-16F-BG000 | On-Off, illuminated | green | not applicable | 1634202-6 |
| PRGSB1-16F-BR000 | | red | | 1634202-5 |
| PRGSA1-16F-BR000 | On-Off, opaque | | | 1634202-4 |
| PRGSA1-16F-BB0BW | | black | 0 - , white printing | 1634202-3 |
| PRGSA1-16F-BB0AW | | | • , white printing | 1634202-2 |
| PRGSA1-16F-BB000 | | | not applicable | 1634202-1 |

© Tyco Electronics Austria GmbH 2008. All Rights Reserved.

All technical data listed is for description purposes only and does not guarantee characteristics. All drawings, photos and descriptions are subject to change without prior notice.

We are not able to guarantee that the specified circuits, descriptions and tables are not covered by rights of third parties. Terms of delivery and rights to change design reserved.

## Preferred Part Numbers (Continued)

### Americas

**Argentina** - Buenos Aires
Phone: +54-11-4733-2200
Fax: +54-11-4733-2211

**Brasil** - São Paulo
Phone: +55-11-2103-6000
Fax: +55-11-2103-6210

**Canada** - Toronto
Phone: +905-475-6222
Fax: +905-474-5520

**Product Information Center:**
Phone: +905-470-4425
Fax: +905-474-5525

**Chile** - Santiago
Phone: +56-2-345-0300
Fax: +56-2-223-1477

**Colombia** - Bogota
Phone: +57-1-231-9398
Fax: +57-1-660-0206

**Mexico** - Mexico City
Phone: +52-55-1106-0800
+01-800-733-8926
Fax: +52-55-1106-0901

**For Latin/South American Countries not shown**
Phone: +54-11-4733-2015
Fax: +54-11-4733-2083

**United States** - Harrisburg, PA
Phone: +1-717-564-0100
Fax: +1-717-986-7575
**Product Information Center:**
Phone: +1-800-522-6752
Fax: +1-717-986-7575

### Asia/Pacific

**Australia** - Sydney
Phone: +61-2-9554-2600
Fax: +61-2-9502-2556

**Product Information Center:**
Phone: +61-2-9840-8200
Fax: +61-2-9634-6188

**India** - Bangalore
Phone: +91-80-285-40800
Fax: +91-80-285-40820

**Indonesia** - Jakarta
Phone: +65-6482-0311
Fax: +65-6482-1012

**Japan** - Kawasaki, Kanagawa
Phone: +81-44-844-8111
Fax: +81-44-812-3207

**Product Information Center:**
Phone: +81-44-844-8013
Fax: +81-44-812-3200

**Korea** - Seoul
Phone: +82-2-3415-4500
Fax: +82-2-3486-3810

**Malaysia** - Selangor
Phone: +60-3-7805-3055
Fax: +60-3-7805-3066

**New Zealand** - Auckland
Phone: +64-9-634-4580
Fax: +64-9-634-4586

**Philippines** - Makati City
Phone: +632-848-0171
Fax: +632-867-8661

**People's Republic of China** - Hong Kong
Phone: +852-2735-1628
Fax: +852-2735-0243

Shanghai
Phone: +86-21-2407-1588
Fax: +86-21-2407-1599

**Singapore** - Singapore
Phone: +65-6482-0311
Fax: +65-6482-1012

**Taiwan** - Taipei
Phone: +886-2-8768-2788
Fax: +886-2-8768-2268

**Thailand** - Bangkok
Phone: +66-2-955-0500
Fax: +66-2-955-0505

**Vietnam** - Ho Chi Minh City
Phone: +84-8-930-5546
Fax: +84-8-930-3443

### Europe/Middle East/Africa

**Austria** - Vienna
Phone: +43-1-90-560-0
Fax: +43-1-90-560-1333
office.vienna@tycoelectronics.com
**Product Information Center:**
Phone: +43-1-90-560-1249
Fax: +43-1-90-560-1251

**Belgium** - Kessel-Lo
Phone: +32-16-352-300
Fax: +32-16-352-352
beneluxsales@tycoelectronics.com

**Bulgaria** - Sofia
Phone: +359-2-971-2152
Fax: +359-2-971-2153
ampbg@internet-bg-net

**Czech Republic** - Kurim
Phone: +420-5-41-162-111
Fax: +420-5-41-162-223
amp@tycoelectronics.cz
**Product Information Center:**
Phone: +420-541-162-113
Fax: +420-541-162-132

**Denmark** - Glostrup
Phone: +45-43-48-04-00
Fax: +45-43-44-14-14
info.dk@tycoelectronics.com

**Egypt** - Cairo
Phone: +20-2-419-2334
Fax: +20-2-417-7647

**Estonia** - Tartu
Phone: +372-5138-274
Fax: +372-7400-779

**Finland** - Helsinki
Phone: +358-95-12-34-20
Fax: +358-95-12-34-250
info.fi@tycoelectronics.com

**France** - Cergy-Pontoise Cedex
Phone: +33-1-3420-8888
Fax: +33-1-3420-8600
**Product Information Center:**
Phone: +33-1-3420-8686
Fax: +33-1-3420-8623

**France Export Divisions** - Cergy-Pontoise Cedex
Phone: +33-1-3420-8804
Fax: +33-1-3420-8699

**Germany** - Bensheim
Tyco Electronics AMP GmbH
Phone: +49-6251-133-0
Fax: +49-6251-133-1600
tyco-sales@tycoelectronics.com
**Product Information Center:**
Phone: +49-6251-133-1999
Fax: +49-6251-133-1988

**Greece** - Athens
Phone: +30-210-9370-396/397
Fax: +30-210-9370-655

**Hungary** - Budapest
Phone: +36-1-289-1000
Fax: +36-1-289-1010
**Product Information Center:**
Phone: +36-1-289-1016
Fax: +36-1-289-1017

**Ireland** - Dublin
Phone: +353-1-820-3000
Fax: +353-1-820-9790

**Israel** - Yokneam
Phone: +972-4-959-0508
Fax: +972-4-959-0506

**Italy** - Collegno (Torino)
Phone: +39-011-4012-111
Fax: +39-011-4031-116
**Product Information Center:**
Phone: +39-011-4012-360
Fax: +39-011-4028-7360

**Lithuania & Latvia** - Vilnius
Phone: +370-5-213-1402
Fax: +370-5-213-1403
**Product Information Center:**
Phone: +370-5-211-3016
Fax: +370-5-213-1403

**Netherlands** - 'sHertogenbosch
Phone: +31-73-6246-246
Fax: +31-73-6212-365
beneluxsales@tycoelectronics.com
**Product Information Center:**
Phone: +31-73-6246-999
Fax: +31-73-6246-998

**Norway** - Nesbru
Phone: +47-66-77-88-50
Fax: +47-66-77-88-55
info.no@tycoelectronics.com

**Poland** - Warsaw
Phone: +48-22-4576-700
Fax: +48-22-4576-720
poland.info@tycoelectronics.com
**Product Information Center:**
Phone: +48-22-4576-704
Fax: +48-22-4576-720

**Romania** - Bucharest
Phone: +40-21-311-3479 + 3596
Fax: +40-21-312-0574

**Russia** - Moscow
Phone: +7-495-790-7902
Fax: +7-495-721-1893
**Product Information Center:**
Phone: +7-495-790-7902-404
Fax: +7-495-790-7902-401

**Russia** - St. Petersburg
Phone: +7-812-718-8192
Fax: +7-812-718-8193

**Slovenia** - Ljubljana
Phone: +386-1561-3270
Fax: +386-1561-3240

**South Africa** - Port Elizabeth
Phone: +27-41-503-4500
Fax: +27-41-581-0440

**Spain** - Barcelona
Phone: +34-93-291-0330
Fax: +34-93-201-7879

**Sweden** - Upplands Väsby
Phone: +46-8-50-72-50-00
Fax: +46-8-50-72-50-01
info.se@tycoelectronics.com

**Switzerland** - Steinach
Phone: +41-71-447-0447
Fax: +41-71-447-0444
info.ch@tycoelectronics.com

**Turkey** - Istanbul
Phone: +90-212-281-8181…3
+90-212-282-5130/5430
Fax: +90-212-281-8184
ProductInfo.Turkey@tycoelectronics.com

**Ukraine** - Kiev
Phone: +380-44-206-2265
Fax: +380-44-206-2264

**United Kingdom** - Stanmore Middlesex
Phone: +44-8706-080208
Fax: +44-208-954-6234
**Product Information Center:**
Freephone GB: +0800-267-666
Phone: +44-8706-080208
Fax: +44-208-420-8081



Catalogue No. 1308111
Issued 03/2008

Dimensions are in mm and are shown for reference purposes only.

Specifications subject to change.

Tyco Electronics offers a comprehensive range of switches including DIP switches, slide switches, toggle switches, push buttons, micro switches, rotary switches, and industrial control switches. Accessories as knobs, caps, boot seals and the respective hardware round off our extensive range.

Our switches cover the widest range of applications, from white goods, building automation, office equipment, communications, test & measurement, remote control devices up to machinery and heating and air-conditioning systems.

Tyco Electronics does not only offer standard switches, but also customized switching solutions for customer applications from the mA range up to 25 A.

**Tyco Electronics Austria GmbH**
Pilzgasse 33
1210 Vienna
Austria
Phone: +43 1 90560-0
Fax: +43 1 90560-1333

www.tycoelectronics.com

© Tyco Electronics Corporation
Catalogue No. 1308111, Issued 03-2008

Tyco Electronics
Our commitment. Your advantage.