HAT2165H

Silicon N Channel Power MOS FET
Power Switching

REJ03G0004-0600
Rev.6.00
Sep 20, 2005

Features

- High speed switching
- Capable of 7 V gate drive
- Low drive current
- High density mounting
- Low on-resistance
  $R_{DS(on)}$ = 2.5 mΩ typ. (at V_{GS} = 10 V)

Outline

RENESAS Package code: PTZZ0005DA-A)
(Package name: LFPAK)





1, 2, 3	Source
4	Gate
5	Drain

Absolute Maximum Ratings

(Ta = 25°C)

Item	Symbol	Ratings	Unit
Drain to source voltage	V_{DSS}	30	V
Gate to source voltage	V_{GSS}	±20	V
Drain current	I_D	55	A
Drain peak current	$I_{D(pulse)}$ Note1	220	A
Body-drain diode reverse drain current	I_{DR}	55	A
Avalanche current	I_{AP} Note 2	30	A
Avalanche energy	E_{AR} Note 2	90	mJ
Channel dissipation	Pch Note3	30	W
Channel to Case Thermal Resistance	θch-C	4.17	°C/W
Channel temperature	Tch	150	°C
Storage temperature	Tstg	–55 to +150	°C

Notes: 1. PW ≤ 10 µs, duty cycle ≤ 1%
2. Value at Tch = 25°C, Rg ≥ 50 Ω
3. Tc = 25°C

Electrical Characteristics

(Ta = 25°C)

Item	Symbol	Min	Typ	Max	Unit	Test Conditions
Drain to source breakdown voltage	$V_{(BR)DSS}$	30	—	—	V	I_D = 10 mA, V_{GS} = 0
Gate to source breakdown voltage	$V_{(BR)GSS}$	±20	—	—	V	I_G = ±100 µA, V_{DS} = 0
Gate to source leak current	I_{GSS}	—	—	±10	µA	V_{GS} = ±16 V, V_{DS} = 0
Zero gate voltage drain current	I_{DSS}	—	—	1	µA	V_{DS} = 30 V, V_{GS} = 0
Gate to source cutoff voltage	$V_{GS(off)}$	1.0	—	2.5	V	V_{DS} = 10 V, I_D = 1 mA
Static drain to source on state resistance	$R_{DS(on)}$	—	2.5	3.3	mΩ	I_D = 27.5 A, V_{GS} = 10 V [Note4]
	$R_{DS(on)}$	—	3.4	5.3	mΩ	I_D = 27.5 A, V_{GS} = 4.5 V [Note4]
Forward transfer admittance	$\|y_{fs}\|$	60	100	—	S	I_D = 27.5 A, V_{DS} = 10 V [Note4]
Input capacitance	Ciss	—	5180	—	pF	V_{DS} = 10 V, V_{GS} = 0, f = 1 MHz
Output capacitance	Coss	—	1200	—	pF	
Reverse transfer capacitance	Crss	—	380	—	pF	
Gate Resistance	Rg	—	0.5	—	Ω	
Total gate charge	Qg	—	33	—	nC	V_{DD} = 10 V, V_{GS} = 4.5 V, I_D = 55 A
Gate to source charge	Qgs	—	15	—	nC	
Gate to drain charge	Qgd	—	7.1	—	nC	
Turn-on delay time	$t_{d(on)}$	—	13	—	ns	V_{GS} = 10 V, I_D = 27.5 A, V_{DD} ≅ 10 V, R_L = 0.36 Ω, Rg = 4.7 Ω
Rise time	t_r	—	65	—	ns	
Turn-off delay time	$t_{d(off)}$	—	60	—	ns	
Fall time	t_f	—	9.5	—	ns	
Body–drain diode forward voltage	V_{DF}	—	0.81	1.06	V	IF = 55 A, V_{GS} = 0 [Note4]
Body–drain diode reverse recovery time	t_{rr}	—	40	—	ns	IF = 55 A, V_{GS} = 0, di_F/dt = 100 A/µs

Notes: 4. Pulse test

Main Characteristics

Power vs. Temperature Derating



Maximum Safe Operation Area



Typical Output Characteristics



Typical Transfer Characteristics



Drain to Source Saturation Voltage vs. Gate to Source Voltage



Static Drain to Source on State Resistance vs. Drain Current



Static Drain to Source on State Resistance vs. Temperature



Forward Transfer Admittance vs. Drain Current



Body-Drain Diode Reverse Recovery Time



Typical Capacitance vs. Drain to Source Voltage



Dynamic Input Characteristics



Switching Characteristics



Reverse Drain Current vs. Source to Drain Voltage



Maximum Avalanche Energy vs. Channel Temperature Derating



Normalized Transient Thermal Impedance vs. Pulse Width



Avalanche Test Circuit



Avalanche Waveform

$$E_{AR} = \frac{1}{2} L \bullet I_{AP}^2 \bullet \frac{V_{DSS}}{V_{DSS} - V_{DD}}$$



Switching Time Test Circuit



Switching Time Waveform



Package Dimensions

JEITA Package Code	RENESAS Code	Package Name	MASS[Typ.]
SC-100	PTZZ0005DA-A	LFPAK	0.080g

Unit: mm



(Ni/Pd/Au plating)

Ordering Information

Part Name	Quantity	Shipping Container
HAT2165H-EL-E	2500 pcs	Taping

Note: For some grades, production may be terminated. Please contact the Renesas sales office to check the state of production before ordering the product.

Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

RENESAS SALES OFFICES

http://www.renesas.com

Refer to "**http://www.renesas.com/en/network**" for the latest and detailed information.

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology Hong Kong Ltd.
7th Floor, North Tower, World Finance Centre, Harbour City, 1 Canton Road, Tsimshatsui, Kowloon, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2730-6071

Renesas Technology Taiwan Co., Ltd.
10th Floor, No.99, Fushing North Road, Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd.
Unit2607 Ruijing Building, No.205 Maoming Road (S), Shanghai 200020, China
Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd.
Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea
Tel: <82> 2-796-3115, Fax: <82> 2-796-2145

Renesas Technology Malaysia Sdn. Bhd.
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jalan Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: <603> 7955-9390, Fax: <603> 7955-9510

Colophon .3.0