



# Extension Cable 25 Pin Male to Female

172-2525

KOBI CONN

Extension Cable 25 Pin Male to Female



Dimensions: mm (In.)

Sec: A-A	
DB 25M	DB 25F
1	1
2	2
3	3
4	4
5	5
8	6
.....	.....
22	22
23	23
24	24
25	25
Shell	Shell

## MECHANICAL SPECIFICATIONS

Molding PVC color:	beige
Screw:	4-40
Cable:	28 AWG

## ELECTRICAL SPECIFICATIONS

Max current:	500mA
--------------	-------

## MATERIAL SPECIFICATIONS

Insulator:	PBT with 30% glass fiber
Housing:	nickel plated steel
Pin:	brass contact 1μ" gold plated

Date Last Revised: 6/21/12

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300106

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

172-2525

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-2525](#)