





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P		REVISED PER ECO-15-015252	12NOV15	BJ	FY



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. K. SEIFRIED CHK F. KIBLER APVD —	03/26/90 8-18-92 —	TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± -		1 PLC ± -		PRODUCT SPEC	
2 PLC ± -		3 PLC ± 0.13 [.005]		APPLICATION SPEC	
4 PLC ± -		ANGLES ± -		—	
MATERIAL		FINISH		WEIGHT	
1 2		3		A1 00779 532432	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2	
				REV P	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—BLACK.

2

CONTACT MATERIAL: PHOSPHOR BRONZE.

3

FINISH:

MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108—9063; BASED ON TELCORDIA DR—1217—CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.

SOLDER TAILS AREA: TIN—LEAD PLATED.

4

ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK P.C. BOARD. RECOMMENDED P.C. BOARD HOLES ARE 1.151 [.0453] DIA PLATED THRU WITH 0.025—0.076 [.001—0.003] COPPER, WITH 0.0076 [.0003] MIN TIN—LEAD PLATING; FINISHED HOLE AFTER PLATING 0.94—1.09 [.037—0.43] DIA.

5.

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

HOUSINGS WITH CENTER MOUNTING IS RECOMMENDED FOR ASSEMBLIES HAVING 75 CONTACTS PER ROW OR MORE.

7

PART NUMBER IS OBSOLETE.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

6	7	—	—	—	—	—	—	2—532432—0
6	7	—	—	—	—	—	—	1—532432—9
6	7	—	—	—	—	—	—	1—532432—8
6	7	—	—	—	—	—	—	1—532432—7
6	7	—	—	—	—	—	—	1—532432—6
6	7	—	—	—	—	—	—	1—532432—5
6	7	—	—	—	—	—	—	1—532432—4
6	7	—	—	—	—	—	—	1—532432—3
7	7	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	225	1—532432—2
7	7	175.26 [6.900]	69	179.07 [7.050]	189.23 [7.450]	196.85 [7.750]	210	1—532432—1
7	7	—	—	—	—	—	—	1—532432—0
7	7	149.86 [5.900]	59	153.67 [6.050]	163.83 [6.450]	171.45 [6.750]	180	532432—9
7	7	137.16 [5.400]	54	140.97 [5.550]	151.13 [5.950]	158.75 [6.250]	165	532432—8
7	7	—	—	—	—	—	—	532432—7
7	7	—	—	—	—	—	—	532432—6
7	7	99.06 [3.900]	39	102.87 [4.050]	113.03 [4.450]	120.65 [4.750]	120	532432—5
7	7	—	—	—	—	—	—	532432—4
7	7	78.74 [3.100]	31	82.55 [3.250]	92.71 [3.650]	100.33 [3.950]	96	532432—3
7	7	—	—	—	—	—	—	532432—2
7	7	—	—	—	—	—	—	532432—1
E	D	C	B	A	POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± —
± —
± —
± 0.13 [.005]
± — ± —

ANGLES

FINISH

MATERIAL

1

2

DWN
R. K. SEIFRIED

CHK
F. KIBLER

APVD
—

03/26/90

8—18—92

—

PRODUCT SPEC

APPLICATION SPEC

—

WEIGHT

0

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV P

DWN
R. K. SEIFRIED

CHK
F. KIBLER

APVD
—

03/26/90

8—18—92

—

NAME

HDI, 3 ROW, PIN ASSEMBLY,
18.62 [.733] LONG ACTION PINS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

00779

532432

—

4805 (1/15)