


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	WRITE-ON AREA in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs/100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)													
PLF1MC	.06 (1.5)	.87 (22.0)	.045 (1.1)	.098 (2.5)	.177 (4.5)	.154 (3.9)	.180 (4.6)	4.3 (109)	.315 (8.0)	.290 (7.4)	.038 (.96)	.064 (1.626)	18 (80)	MINIATURE	.07 (31.8)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PLF1MC CABLE TIE

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .01 (.25) (.XXX) ± .020 (.50)
(.XX) ± .02 (.5) ANGLES ± _____

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RAMA

MAT'L:

SCALE
NONE

DATE
6/23/05

NYLON 6.6

DRAWING NO.
SS-27445

DWG
A
SIZE

3 5/02/06 FAB CHANGED DIM. J FROM .028" TO .038"

27445 3

CHK'D
BOBK

DESCRIPTION

ECN - R

CUST

SUP

REV

DATE

BY

CHK