

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,2007.


© COPYRIGHT 2007 By --

ALL RIGHTS RESERVED.



LOC
JDIST
/

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED PER ECR-12-004002	01MAR2012	W.W	C.W



HOW TO MATE AND UNMATE

MATE: ① → ④
UNMATE: ⑤ → ⑦

(APPLIED TO SHEET 1-2)

1. MATERIAL ; HOUSING: HIGH TEMPERATURE THERMO PLASTIC UL94V-0
COLOR: SEE TABLE

CONTACT: COPPER ARROY

LOCK LEVER: STAINLESS STEEL


PEG: COPPER ARROY

2-1. FINISH ; CONTACT AREA: GOLD FLASH
ALL OVER NICKEL.SOLDERING AREA: GOLD FLASH PLATING
PEG: TIN PLATING.2-2. FINISH ; CONTACT AREA: 0.000254MIN GOLD
ALL OVER NICKEL.SOLDERING AREA: GOLD FLASH PLATING
PEG: TIN PLATING.2-3. FINISH ; CONTACT AREA: 0.00076MIN GOLD
ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLATING
PEG: TIN PLATING.

△ COPLANARITY: 0.1 MAX. (BEFORE SOLDERING)

△ THE FLOATING VALUE BY SOLDERING IS NOT INCLUDED.

△ NOT MATING CONDITION.

6. IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY,
OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE
INSERTED AND LOCKED IN THE LATCH.GENERAL TOLERANCE
 $10 \geq : \pm 0.2$
 $30 \geq > 10 : \pm 0.25$
 $100 \geq > 30 : \pm 0.3$
ANGLES: $\pm 3^\circ$

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC $\pm$
1 PLC $\pm$
2 PLC $\pm$
3 PLC $\pm$
4 PLC $\pm$
ANGLES $\pm$
FINISH

MATERIAL

DWN 18SEP2007

CHK 18SEP2007

K.IKEGAMI

APVD 18SEP2007

K.IKEGAMI

PRODUCT SPEC

108-78493

APPLICATION SPEC

WEIGHT

6.2g

CUSTOMER DRAWING

STE

TE Connectivity

NAME

DDR3 SODIMM SOCKET
0.6mm PITCH 204POS
9.2mm HEIGHT STANDARD TYPE

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-2013310

SCALE 2:1

SHEET 1 OF 6

REV D

4

3

2


1

LOC	DIST	REVISIONS					
J	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

AVAILABLE	ENBOSS (SEE SHEET 6)	WITHBOSS	BLACK	NOTE 2-3	1.5V	204	2-2013310-3
AVAILABLE	ENBOSS (SEE SHEET 6)	WITHBOSS	BLACK	NOTE 2-2	1.5V	204	2-2013310-2
AVAILABLE	ENBOSS (SEE SHEET 6)	WITHBOSS	BLACK	NOTE 2-1	1.5V	204	2-2013310-1
AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-3	1.5V	204	2013310-3
AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-2	1.5V	204	2013310-2
AVAILABLE	SEMI-HARD TRAY (SEE SHEET 5)	WITH BOSS	BLACK	NOTE 2-1	1.5V	204	2013310-1
TOOLING STATUS	PACKAGING TYPE	REMARK	HOUSING COLOR	FINISH	POWER SUPPLY	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

DWN
CHK
APVD
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

NAME
DDR3 SODIMM SOCKET
0.6mm PITCH 204POS
9.2mm HEIGHT STANDARD TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2013310

RESTRICTED TO
—

SCALE
2:1

SHEET
2 OF 6

REV
D


TE Connectivity

REV D



LOC	DIST
J	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





- (APPLIED TO SHEET 4)
1. TOLERANCES ON ALL DIMENSIONS ± 0.15 UNLESS OTHERWISE SPECIFIED.
 2. P.C. BOARD THICKNESS APPLIES ACROSS TABS AND INCLUDES PLATING AND/OR METALIZATION.
 3. FINISH OF PAD : GOLD PLATING 0.00076 MIN. OVER Ni PLATING 0.002MIN.
- ④ NO BURR
- ⑤ CHAMFER 0.25 MAX x 45° IF EXIST.





30	CA
31.75	BA
25.4	AA
H	SDRAM VARIATIONS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity	
DIMENSIONS: MM		CHK		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		DDR3 SODIMM SOCKET	
0 PLC ±		PRODUCT SPEC		0.6mm PITCH 204POS	
1 PLC ±		APPLICATION SPEC		9.2mm HEIGHT STANDARD TYPE	
2 PLC ±		WEIGHT		SIZE	RESTRICTED
3 PLC ±		CUSTOMER DRAWING		CAGE CODE	
4 PLC ±		SCALE		DRAWING NO	
ANGLES ±		SHEET			
FINISH		REV			
MATERIAL		4 OF 6			
A3		2.1			
00779		D			
C-2013310					

1. THE DIRECTION OF EACH CONNECTOR ON A TRAY IS REFERRED TO THIS DRAWING.
2. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$



B-B
SCALE 1:1



A-A
SCALE 1:1
(180DEG. ROTATE)

CUSTOMER DRAWING

REV	D
-----	---

