

EC Safety Data Sheet according to Directive 1907/2006

Trade name: Solder-wire Kristall 400; S-Sn62Pb36Ag2

Date of issue: 06.05.2003

Revised on: 19.01.2009

Date of print: 12.02.2009

Page: 1(3)

1. Name of product, characterization and company name

Information on the product

Trade name:

Solder-wire Kristall 400 S-Sn62Pb36Ag2

Usage of the product / preparation

Solder wire for soft soldering

Identification of the manufacturer / supplier

Address:

Stannol GmbH

Oskarstr. 3 -7

42283 Wuppertal

Phone: 0202 585 0

Fax: 0202 585 155

0202 585 119

Emergency call:

E-mail:

werner.kruppa@stannol.de

2. Possible hazards:

Not a composition for the purposes of the Dangerous Substances Regulations, but nevertheless observe items 4-16

3. Composition/Information on the components

Chemical characterization: Tin/Lead/Silver – alloy with flux max.3,5 % modified resin (halidefree)

Composition according to EC 1907/2006:

Contents	CAS No.	EINECS No.	Symbols	R-phrases:	Substance
61,5-62,5%	7440-31-5	231-141-8			Tin
Remainder	7439-92-1	231-131-3			Lead
1,8-2,2%	7440-22-4	231-131-3			Silver

The wording of the R-phrases stated is indicated in Section 16

4. First Aid measures

General information:

If casualty is unconscious but breathing, place in the recovery position. If breathing has stopped apply artificial resuscitation or give oxygen by mask

After inhalation:

Remove patient to fresh air. If irritation persists, obtain medical attention.

After skin contact:

If any skin irritation develops seek medical attention

After eye contact:

Flush **immediately** with plenty of water. In cases where spitting flux has entered the eye seek medical attention.

After ingestion:

Rinse mouth immediately and drink plenty of water. Seek medical advice.

Hints for doctors.

Inhalation of the flux fumes given off at soldering temperatures will irritate the nose, throat and respiratory system. Repeated or prolonged exposure to flux fumes may cause shortness of breath and cough..

Physician's information

Treatment:

Decontamination, treatment of symptoms.

5. Fire fighting measures

Suitable extinguishing media:

Use extinguishing media appropriate to surrounding fire conditions

Special protective equipment for fire fighting

Wear self-contained breathing apparatus and protective clothing to prevent contact with skin and eyes.

6. Accidental release measures

Pick up and place in appropriate container

7. Handling and storage

The fumes produced during soldering should be extracted away from the breathing zone of the operators. Ensure the area is well ventilated. Wash hands with soap and warm water after handling, particularly before eating, drinking or smoking.

The product should be stored in a cool, dry area.

EC Safety Data Sheet according to Directive 1907/2006

Trade name: Solder-wire Kristall 400; S-Sn62Pb36Ag2

Date of issue: 06.05.2003

Revised on: 19.01.2009

Date of print: 12.02.2009

Page: 2(3)

8. Exposure controls and personal protection

Additional information on system design:

Local exhaust or dilution ventilation and control of process conditions are suitable methods..

Substances with limit values to be monitored at the working place:

Danger to health at the working place:

Peak limit category:

Working place limit values according to TRGS 900 from Section 2 for Germany:

Product name	CAS No.	ml/m ³ (ppm)	mg/m ³	Type	Category	Remarks
Tin	7440-31-5		2	MAK (NL)		
Lead	7439-92-1		0,1	MAK (TLV)		
Silber	7440-50-8		0,1	MAK (DFG)		

BAT-Value Lead/blood level: 700µg/l,
Women below 45 years: 300µg/l

Skin resorption / Sensitization: Skin resorption ----

Sensitization: ----

General protection and hygiene measures

Avoid direct contact with eyes, the skin and clothing.

Personal protection

Respiratory protection:

If concentrations are over the exposure limit, use a supplied air respirator.

Hand protection:

Use heat resistant gloves if required.

Eye protection:

Operators should wear goggles

Personal protection:

Light protective clothing

9. Physical and chemical properties

Form: Form: Tin-Lead Silver Solder

Colour: silver

Melting Point: 179°C

Vapour Pressure: n.a.

Density(20°C): 7-8 g/cm³

10. Stability and reactivity

Reaction with substances: Possible with oxidising agents.

Hazardous combustion or decomposition products: Lead-oxides possible

11. Toxicological information

The toxicological classification of the product is based on the results of the calculation procedure of the general preparation directive 1999/45/EC.

Acute Effects:

Acute intoxication by ingestion of skin contact with lead is improbable. High doses nevertheless lead to symptoms of poisoning. Inhalation of fumes can irritate the respiratory tract and eyes..

Contamination through skin contact and inhalation:

All following items refer to pure lead

Acute Toxicity

Type	Value in mg/Kg	Form	Species
LD.LO	160	oral	pigeon
LD.LO	1000	ip	rat

LD.LO (oral, pigeon): 160 mg/kg; TD.LO (oral, woman): 450 mg/kg (damage to nervous system); LD.LO (ip., Rat): 1000 mg/kg; TC.LO (inhal., human): 10 mg/m³ ;

12. Ecological information

General information: Lead and combinations of lead are not biological reducible.

EC Safety Data Sheet according to Directive 1907/2006

Trade name: Solder-wire Kristall 400; S-Sn62Pb36Ag2

Date of issue: 06.05.2003

Revised on: 19.01.2009

Date of print: 12.02.2009

Page: 3(3)

13. Disposal considerations

Disposal information

Product:

Contact a licensed professional waste disposal service to dispose of this material.

Further information:

Observe all federal, state and local environmental regulations. Collect metal for recycling

Waste identity number:

Waste identity number EAK-code: 120104

14. Transport information

GGVS/ADR/RID:

The product is not classified as hazardous for transport

15. Legal regulations:

Labelling information:

The product is classified and labelled according to the EC Directives.

Water hazard class:

Not subject to current legislation

Classification according to the TA Luft:

WGK 1 (weakly water-endangering)

Organic materials class III; whole-carbon-concentration: Max. acceptable

Emission 50 mg/m³ (mass-flow-rate \geq 0,5 kg/h)

Ingredients:

Tin, Lead, Silver; resin

16. Further information

R-phrases point 3: -----

German regulations:

See TRGS 505 "Lead and leaded dangerous compounds"

This statement is based on our current knowledge and offers no assurance of product properties.

Department issuing the data sheet

Stannol GmbH/Quality Assurance/Laboratory

Contact person

Dr. Kruppa