

# 84

## 64 Electronics End Cutting Nippers



64 01 115  
Style 0: End Cutter,  
with bevel



64 02 115  
Style 0: End Cutter,  
with bevel



64 12 115  
Style 1: End Cutter,  
with small bevel



64 22 115  
Style 2: End Cutter, mini-blade  
with small bevel




64 32 120  
Style 3: Oblique End Cutter,  
short head, with small bevel,  
 $\alpha = 15^\circ$




64 42 115  
Style 4: Oblique End Cutter,  
short head, with small bevel,  
 $\alpha = 27^\circ$

DIN ISO 9654


- precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- precision box joint
- low-friction double spring for gentle and even opening
- the polish or mirror polish (only finish 2) together with a fine film of oil offer the best possible rust protection - no circuit faults caused by peeling chrome from plated tools
- cutting edge hardness at least 56 HRC
- special tool steel, oil-hardened and tempered




64 12 115




64 22 115




64 62 120  
differently shaped jaws and  
mini-blades for flush cutting  
in confined areas



64 32/42/52 115



64 72 120



64 62 120

Article-No.	EAN-	Style	Head	Handles	Dimensions				Cutting capacities				
					B	A	D	C	Ø mm	Ø mm	Ø mm	g	
Length mm	Code	all pliers with			mm	mm	mm	mm	Ø mm	Ø mm	Ø mm	g	
64 01 115	017745	0		polished	plastic coated	6.0	11.0	7.5	16.0	2.0	1.0	0.6	80
64 02 115	035343			mirror polished	with two-colour dual component handles	6.0	11.0	7.5	16.0	2.0	1.0	0.6	90
64 11 115	017769	1		polished	plastic coated	6.0	11.0	7.0	16.0	1.4	0.8	-	80
64 12 115	040743			mirror polished	with two-colour dual component handles	6.0	11.0	7.0	16.0	2.0	0.8	0.5	90
64 22 115	017806	2		polished	plastic coated	20.0	10.0	6.0	3.0	0.8	-	-	70
64 32 120	017820	3		mirror polished	with two-colour dual component handles	10.0	11.0	7.0	17.0	1.5	1.0	0.5	90
64 42 115	017844	4		polished	plastic coated	10.3	10.0	7.0	12.0	1.5	1.0	0.5	70
64 52 115	040439	5		mirror polished	with two-colour dual component handles	10.0	10.0	7.0	12.0	1.3	-	-	70
64 62 120	046998	6		polished	plastic coated	18.5	9.5	6.0	5.0	0.6	-	-	70
64 72 120	017882	7		mirror polished	with two-colour dual component handles	19.5	12.0	7.0	5.0	1.5	-	-	90
Pliers sets see page 157													