


## AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

### 070 MULTILOCK PLUG HSG. 8 POS

AMP

282366-1

TE Internal Number: 282366-1

EU RoHS Compliant

EU ELV Compliant

**Connector Style** Housing for female terminals

**Mating Tab Width** 1.8 mm [.071 in]

**Connector System** Wire-to-Wire

**Number of Positions** 8

**Centerline (Pitch) (mm)** 3.5, 5.5

**Centerline (Pitch) (in)** .138, .211

#### PRODUCT DRAWING

English

#### 3D PDF

## DOCUMENTATION

Product Drawings

### 070 SERIES MULTILOCK CONN. PLUG HOUSING 8 POSITION DOUBLE ROW

PDF [\(TIFF AVAILABLE\)](#)

English

CAD Files

#### Customer View Model

2D\_DXF.ZIP

English

#### 3D PDF

PDF

3D

#### **Customer View Model**

3D\_IGS.ZIP

English

#### **Customer View Model**

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

#### **070 Series Multilock Conns.**

TIF

English

#### **070 Series Multilock Conns.**

PDF

English

#### **070 SERIES MULTILOCK CONNECTOR FOR W.T.W. APPLICATION**

PDF

English

#### **070 SERIES MULTILOCK CONNECTOR FOR W.T.W. APPLICATION**

TIF

English

---

Instruction Sheets

Instruction Sheet (non U.S.)

#### **070 Sr MULTILOCK\* Connector (Wire To Wire Version)**

TIF

English

#### **070 Sr MULTILOCK\* Connector (Wire To Wire Version)**

PDF

English

---

#### **FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Connector Style** Housing for female terminals

**Connector System** Wire-to-Wire

**Sealable** No

**Hybrid Connector** No

**Primary Locking Feature** On the terminal

**Strain Relief** No

**Row-to-Row Spacing** 5.6 mm [ .22 in ]

## Configuration Features

**Number of Positions** 8

**Number of Rows** 2

---

## Electrical Characteristics

**Nominal Voltage Architecture (V)** 12, 24

**Operating Voltage (VDC)** 24

---

## Body Features

**Color** Natural

**Cable Exit Angle** 180°

**Body Material** PBT

---

## Contact Features

**Mating Tab Width** 1.8 mm [.071 in]

---

## Mechanical Attachment

**Mounting Feature** No

**Terminal Position Assurance** No

**Polarized** Yes

---

## Housing Features

**Centerline (Pitch) (mm)** 3.5, 5.5

**Centerline (Pitch) (in)** .138, .217

---

## Dimensions

**Width** 26.1 mm [ 1.028 in ]

**Height** 21.6 mm [ .85 in ]

**Length** 24.8 mm [ .976 in ]

---

## Usage Conditions

**Operating Temperature Range** -30 – 105 °C [ -22 – 221 °F ]

---

## Operation/Application

**Circuit Application** Signal

---

## Industry Standards

**Degree of Protection** Other

---

## Packaging Features

**Packaging Method** Box

**Packaging Quantity** 2000

---

## Other

Connector Position Assurance Capable No

Customer GEN

Serviceable Yes

## PRODUCT COMPLIANCE



Statement of Compliance

### **Statement of Compliance**

PDF