



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		G	REVISED PER ECR-13-008204	10DEC2013	KH	TM

D

C

B

A




1 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN THE TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.

2 WIRE RANGE: 0.5-2mm² [20-14] AWG. INSULATION RANGE: 1.52-3.30[.060-.130] DIA.


3 DIMENSIONS IN BRACKETS ARE IN INCHES.

4 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN MATTE TIN IN MATTE TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.

5 SUPERSEDED BY 1-770254-0




SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

5	GOLD 4	0.30[.012]	BRASS	1-770254-0
	GOLD 1	0.30[.012]	BRASS	770254-2
	PRE-TIN	0.30[.012]	BRASS	770254-1
	FINISH	MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.CARPENTER 11AUG03	 TE Connectivity							
		CHK C.JONES 11AUG03								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN, GROUNDING, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II —						
		APVD C.JONES 11AUG03								
		PRODUCT SPEC —								
		APPLICATION SPEC —								
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
SEE TABLE		SEE TABLE		WEIGHT —	A2	00779	C=770254	—		
CUSTOMER DRAWING					SCALE	5:1	SHEET	1 of 1	REV	G