

SLE 76CX482P

48 Kbyte EEPROM

196 Kbytes ROM, 7100 bytes RAM,

1100-Bit Advanced Crypto Engine

certified RSA 2048-bit library available

Dual Key Triple DES

8/16-Bit Security Controller with enhanced instruction set
for large memories in 0.22 μm CMOS Technology

Short Product Overview

May 2010

SLE 66CX482PE Short Product Overview		Ref.: Chip_Card_Product_Overview_11/09
Revision History: Current Version 05.10		
Previous Releases:		
Page		

Important: Further information is confidential and on request. Please contact:
Infineon Technologies AG in Munich, Germany,
Chip Card & Security
E-Mail: security.chipcard.ics@infineon.com

Edition 2010

**Published by Infineon Technologies AG,
Chip Card & Security
81726 Munich, Germany
© Infineon Technologies AG 2010
All Rights Reserved.**

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Product name	SLE 66CX482PE Secure μSlim EEPROM
Product description	Security cryptocontroller
User-ROM	196 kByte
EEPROM	48 kByte
RAM	6,400 Byte + 700 Byte crypto
CPU	8-bit/16-bit
Crypto coprocessors	
Symmetrical Cryptography	3DES
Asymmetrical Cryptography	RSA up to 2048 bit, ECC up to 521 bit
Clock (int.)	1 - 33 MHz
Clock (ext.)	1 - 7.5 MHz
Operating voltage	1.62 V - 5.5 V
Max. supply current (at 5 MHz, 5 V)	10 mA
Max. sleep mode current (typical)	100 μ A
Ambient temperature	-25 to +85°
Write / erase time	2 ms (typ.)
EEPROM page programming	1 to 64 Byte
Security features	EEPROM Error Detection, Memory-, Bus- and SFR-Encryption, Active Shield, MMU, DPA/SPA, DEMA/SEMA Countermeasures, Security Sensors: V, f, Light, Temperature, Glitch, Tamperproof Design, Chip ID, True RNG (AIS31, FIPS-140)
Peripherals	CRC, PLL, UART DF 16
Delivery forms	Module M5.1, MFC5.x, DSO-8, VQFN-8, die
Typical applications	Payment, EMV DDA, ePurse, Loyalty, Access Control, Health / Social Security, Digital Signature, ID-Card, Pay-TV
Certifications	CC EAL5+ high, EMVCo

www.infineon.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infiniteon:

[SLE 66CX482PE DSO8](#) [SLE 66CX482PE M5.1](#) [SLE 66CX482PE MFC5.6](#) [SLE 66CX482PE MFC5.8](#) [SLE](#)
[66CX80PE DSO8](#)