



## ABM2S-AT-D0






- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

|                             |                                                              |
|-----------------------------|--------------------------------------------------------------|
| ▪ Part Number               | ABM2S-AT-D0                                                  |
| ▪ RoHS Compliancy Status    | Compliant                                                    |
| ▪ Part Description          | 4-Way Adhesive Backed Cable Tie Mount                        |
| ▪ Product Type              | Cable Tie Mounts - Adhesive Backed                           |
| ▪ Material                  | Weather Resistant ABS                                        |
| ▪ Color                     | Black                                                        |
| ▪ UL Recognized             | E136577                                                      |
| ▪ Height (In.)              | .16                                                          |
| ▪ Height (mm)               | 4.2                                                          |
| ▪ Length (In.)              | 1.00                                                         |
| ▪ Length (mm)               | 25.4                                                         |
| ▪ Width (In.)               | 1.00                                                         |
| ▪ Width (mm)                | 25.4                                                         |
| ▪ Adhesive Type             | Acrylic                                                      |
| ▪ CE Compliant              | CT-ACC1 / 10.96                                              |
| ▪ Environment               | Outdoors/High Temp                                           |
| ▪ Max. Bundle Diameter (mm) | 4.8                                                          |
| ▪ Mounting Method           | Adhesive Backed                                              |
| ▪ Pricing Description       | Cable Tie Mount, Hi Tmp. Adh., 1"x1" (25.4mm x 25.4mm), WRBL |
| ▪ Screw Size                | #6 (M3)                                                      |
| ▪ Screw Size Metric         | M3                                                           |
| ▪ Used With Cable Ties      | M, I, S, SGM, SGI                                            |
| ▪ Min. Order UOM            | PC                                                           |
| ▪ Min. Order Qty.           | 500                                                          |
| ▪ BOM Qty. (# of Pkgs.)     |                                                              |

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

| PANDUIT<br>PART<br>NUMBER* | REC'M<br>FASTENER | USE WITH THESE<br>CABLE TIE<br>CROSS SECTIONS | WEIGHT<br>lbs/100 pcs<br>[ g ]/100 pcs |
|----------------------------|-------------------|-----------------------------------------------|----------------------------------------|
| ABM2S-AT                   | #6 (M3)<br>SCREW  | MINIATURE<br>INTERMEDIATE<br>STANDARD         | 0.26<br>[ 119 ]                        |



ADHESIVE BACKING:  
PRESSURE SENSITIVE FOAM TAPE  
0.040(1.0) THICK WITH PROTECTIVE  
LINER. MOUNT IS DESIGNED TO  
SUPPORT 0.5lbs.(227g) MAX. WEIGHT  
ON A CLEAN, DRY, SMOOTH, GREASE-  
FREE SURFACE.

#### TO APPLY MOUNTS:

- 1) REMOVE MOUNT FROM PROTECTIVE LINER.
- 2) PLACE IN DESIRED LOCATION.
- 3) APPLY PRESSURE TO TOP SURFACE OF MOUNT.

#### NOTES:

- \*1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.
2. MOUNTS PROVIDED IN STRIPS OF TWO FOR EASY REMOVAL FROM LINER.
3. MOUNT HAS A CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C).

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYER#

G00239BY\_PB\_ABM2S-AT\_05

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

ABM2S-AT  
ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±0.05 (1.3) (..XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CJB

MAT'L:

SCALE 1:1

DATE

5/15/98

ABS

DRAWING NO.

G00239BY

CAD

A  
SIZE

| REV | DATE     | BY   | CHK | DESCRIPTION                                                                   | ECN      | R | CUST | SUP |
|-----|----------|------|-----|-------------------------------------------------------------------------------|----------|---|------|-----|
| 5   | 3/3/05   | JAD  |     | REMOVE ABM2S8                                                                 | G80239BY | 5 |      |     |
| 4   | 7/10/03  | L66  |     | CHANGED TOLERANCE ON .203 AND .087<br>DIMENSION FROM .010 (.25) TO .015 (.38) | G80239BY | 4 |      |     |
| 3   | 12-1-00  | C6SM |     | ADDED NEW PART# ABM2S8 FOR JAPAN PARTS                                        | G80239BY | 3 |      |     |
| 2   | 10-28-00 | C6SM |     | CHANGED .158 AND .167 DIMS TO REF                                             | G80239BY | 2 |      |     |
| 1   | 12/18/98 | AJV  |     | UPDATED PART GEOMETRY AND DIMENSIONS                                          | G80239BY | 1 |      |     |
|     |          |      |     | AND UPDATED NOTES.                                                            |          |   |      |     |
| R   | 5/15/98  | CJB  |     | INITIAL RELEASE                                                               | G80239BY | R |      |     |