








1. RECOMMENDED P.C.B THICKNESS 1.60 MM
2. HOUSING MAT'L: NYLON 66, 25% GLASS REINFORCED,
UL94V-0, COLOR: BLACK
3. CONTACTS: PHOS BRONZE ALLOY UNS-C51000,
Ø0.460 DIA, ROUND WIRE, PLATING: SEE TABLE.
4. METAL SHELL MATERIAL:
COPPER ALLOY, 0.20MM THICK.
FOR -XXX: FINISH: TIN-LEAD, 100 u" THICK MIN.
FOR -XXXLF: FINISH: PURE BRIGHT TIN 80u THICK MIN.
5. PACKAGING PER GES-14-361, USING TUBE.
6. IF LF P/N THE PRODUCT MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION WITH A 1.60mm MINIMUM THICK
CIRCUIT BOARD.
8. IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.



PRODUCT NO.	NO. OF POSITION	LOADED POSITION	CONTACTS PLATING
91125-002/-002LF	8	1,2,3,6	30u" GXT
91125-004/-004LF	8	ALL POS.	2u" GOLD

mat'l. code				surface ☒		tolerance		projection 		product family MOD JACK											
ltr		ecn no		dr		date		tolerances unless otherwise specified													
C		T70163		C L		04/30/97		angles linear		.0 ± 0.25				MODIFIED LOW PROFILE PCB III 8-POS SHIELDED MOD JACK, WITHOUT PANEL STOP							
D		T80306		C L		07/15/98				.00 ± 0.13											
E		T80321		CATHY L		07/23/98		± 2'		.000± 0.05		scale 2.5/1									
F		T03-0443		WL		10/06/03		dr		C L FENG		02/22/95									
G		N05-0019		YS		01/27/05		engr		TONY CHIEN		02/22/95		FCI 		dwg no		sheet 1 of 1		size	
								chr		TONY CHIEN		02/22/95				91125		A3			
								appd		JENN TSAO		02/22/95									
sheet index		revision		G																	
sheet		sheet		1																	