



25W Single Output LED Power Supply

PLD-25 series



■ Features :

- Universal AC input / Full range (up to 295VAC)
- Built-in active PFC function
- Constant current design
- Protections: Short circuit / Overload / Over temperature
- Cooling by free air convection
- Fully isolated plastic case
- Class II power unit, no FG
- 100% full load burn-in test
- Low cost
- High reliability
- Suitable for dry / damp locations
- 3 years warranty

SPECIFICATION




MODEL	PLD-25-350	PLD-25-700	PLD-25-1050	PLD-25-1400
OUTPUT	RATED CURRENT	350mA	700mA	1050mA
	OPERATING VOLTAGE RANGE	36 ~ 58V	24 ~ 36V	16 ~ 24V
	CURRENT RANGE	0 ~ 350mA	0 ~ 700mA	0 ~ 1050mA
	CURRENT ACCURACY	±5.0%		
	RATED POWER	20.3W	25.2W	25.2W
	RIPPLE & NOISE (max.) Note.1	4.6Vp-p	2.7Vp-p	2Vp-p
	NO LOAD OUTPUT VOLTAGE (max.)	63V	50V	35V
INPUT	SETUP TIME	1500ms / 230VAC	3000ms / 115VAC at full load	
	VOLTAGE RANGE	90 ~ 295VAC	127 ~ 417VDC	
	FREQUENCY RANGE	47 ~ 63Hz		
	POWER FACTOR (Typ.)	PF>0.98/115VAC, PF>0.92/230VAC, PF>0.91/277VAC at full load (Please refer to "Power Factor Characteristic" curve)		
	EFFICIENCY (Typ.)	85%	86%	85%
	AC CURRENT (Typ.)	0.6A/115VAC	0.3A/230VAC	
	INRUSH CURRENT(max.)	40A/230VAC		
PROTECTION	LEAKAGE CURRENT	<0.5mA / 240VAC		
	OVER CURRENT	95 ~ 110%		
	SHORT CIRCUIT	Protection type : Constant current limiting, recovers automatically after fault condition is removed		
ENVIRONMENT	OVER TEMPERATURE	95°C ±10°C (RTH1)		
	WORKING TEMP.	-30 ~ +60°C (Refer to "Derating Curve")		
	WORKING HUMIDITY	20 ~ 95% RH non-condensing		
SAFETY & EMC	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH		
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)		
	VIBRATION	10 ~ 500Hz, 2G 12min./1cycle, period for 72min. each along X, Y, Z axes		
OTHERS	SAFETY STANDARDS	Design refer to UL8750, TUV EN61347-1, EN61347-2-13		
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC		
	ISOLATION RESISTANCE	I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH		
	EMC EMISSION	Compliance to EN55015, EN61000-3-2 Class C (≥ 75% load) ; EN61000-3-3, FCC part18 Class A		
NOTE	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024,EN61547, light industry level, criteria A		
	MTBF	968.6Khrs min. MIL-HDBK-217F (25°C)		
	DIMENSION	84*57*29.5mm (L*W*H)		
	PACKING	0.19Kg; 72pcs/14.7Kg/0.75CUFT		


1. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.
2. Direct connecting to LEDs is not using additional drivers is highly recommended.

Mechanical Specification


Case No. PCD16A Unit: mm




Block Diagram




Derating Curve



Static Characteristics




Power Factor Characteristic




EFFICIENCY vs LOAD (PLD-25-700)

PLD-25 series possess superior working efficiency that up to 86% can be reached in field applications.



DRIVING METHODS OF LED MODULE

LED power supply may either work in constant current mode (CC) to drive the LEDs.



Typical LED power supply I-V curve