

## SMT15C Series

5 Vin and 12 Vin  
single output

Total Power: 50W  
Input Voltage: 4.5-5.5 Vdc  
# of Outputs: Single



### Special Features

- 15 A current rating
- Input voltage range: 4.5 Vdc - 5.5 Vdc or 10.2 Vdc - 13.8 Vdc
- Output voltage range: 0.9 Vdc - 3.3/5.0 Vdc
- Industry leading value
  - Cost optimized design
- Excellent transient response
- Output voltage adjustability
  - Pathway for future upgrades
  - Supports silicon voltage migration
  - Resulting in reduced design-in and qualification time
- Designed in reliability: MTBF of >7 million hours per Telcordia SR-332
- Available RoHS compliant
- 2 year warranty

### Safety

UL/cUL CAN/CSA 22.2 No. 60950  
UL 60950 File No. E139421

TÜV Product Service  
(EN60950:2000)  
Certificate No. B 04 08 19870 228  
CB report and certificate to  
US/6415C/UL

The SMT15C series is a new high density open-frame, non-isolated converter for space sensitive applications. Each model has a wide input range (4.5 Vdc to 5.5 Vdc or 10.2 Vdc to 13.8Vdc) and offers a wide 0.9 Vdc to 5.0 Vdc output voltage range with a 15 A load. An external resistor adjusts the output voltage from its pre-set value of 0.9 V to any value up to the 5 V maximum. Typical efficiencies for the models are 89% for the 5 V input version and 91% for the 12 V input version. The series offers remote ON/OFF and overcurrent protection as standard. With full international safety approvals including EN60950 and UL/cUL60950, the SMT15C reduces compliance costs and time to market.

# Specifications

All specifications are typical at nominal input, full load at 25°C unless otherwise stated.

OUTPUT SPECIFICATIONS		
Voltage adjustability (See Note 7)	5 Vin 12 Vin	0.9-3.3 Vdc 0.9-5.0 Vdc
Output setpoint accuracy	1.0% trim resistors	±2.5%
Line regulation	Low line to high line	±0.2%
Load regulation	Full load to min. load	±0.5%
Min/max load		0 A/15 A
Overshoot (at turn-on)	5 Vin 12 Vin	3.0% max. 1.0% max.
Undershoot	At turn-off	100 mV max.
Ripple and noise 5 Hz to 20 MHz	(See Note 6)	See Table on page 2
Transient response (See Note 1)		100 mV max. deviation 200 µs recovery to within regulation band
INPUT SPECIFICATIONS		
Input voltage range	5 Vin 12 Vin	4.5-5.5 Vdc 10.2-13.8 Vdc
Input current	Minimum load Remote ON/OFF	65 mA 20 mA
Input current (max.) (See Note 9)	5 Vin 12 Vin	11.5 A max. @ Io max. 8.1 A @ Io max.
Input reflected ripple (See Note 2)	5 Vin 12 Vin	200 mA (pk-pk) 200 mA (pk-pk)
Remote ON/OFF Logic compatibility ON OFF		Positive logic ≥2.4 Vdc ≤0.8 Vdc
Start-up time (See Note 3)	Power-up Remote ON/OFF	<20 ms <20 ms

INPUT SPECIFICATIONS (CONT'D.)		
Turn ON threshold	5 Vin 12 Vin	4.5 Vdc typ. 9.3 Vdc typ.
Turn OFF threshold	5 Vin 12 Vin	4.3 Vdc typ. 7.8 Vdc typ.
GENERAL SPECIFICATIONS		
Efficiency	See Table on page 2	
Switching frequency	Fixed	200 kHz
Approvals and standards	(See Note 4)	TÜV Product Services IEC60950, UL/cUL60950
Material flammability	UL94V-0	
Weight	14.2 g (0.5 oz)	
Coplanarity	150 µm	
MTBF	Telcordia SR-332	7,817,294 hours
ENVIRONMENTAL SPECIFICATIONS		
Thermal performance (See Note 10)	Operating ambient, temperature	0 °C to +80 °C
	Non-operating	-40 °C to +125 °C
PROTECTION		
Short-circuit	Hiccup, non-latching	
RECOMMENDED SYSTEM CAPACITANCE		
Input capacitance (See Note 11)	(See Note 11)	270 µF/20 mW ESR max.
Output capacitance (See Note 11)	(See Note 11)	680 µF/10 mW ESR max.


# Specifications

All specifications are typical at nominal input  $V_{in} = 12$  V, full load at  $25^\circ C$  unless otherwise stated.

OUTPUT POWER (MAX.)	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT (MIN.)	OUTPUT CURRENT (MAX.)	EFFICIENCY (TYP.)	REGULATION		MODEL NUMBER <sup>(12,13)</sup>
						LINE	LOAD	
50 W	4.5-5.5 Vdc	0.9-3.3 Vdc	0 A	15 A	89%	$\pm 0.2\%$	$\pm 0.5\%$	SMT15C-05SADJJ
75 W	10.2-13.8 Vdc	0.9-5.0 Vdc	0 A	15 A	91%	$\pm 0.2\%$	$\pm 0.5\%$	SMT15C-12SADJJ

## Part Number System with Options

### SMT15C-12SADJJ



## Output Voltage Adjustment of the SMT15C Series


The ultra-wide output voltage trim range offers major advantages to users who select the SMT15C series. It is no longer necessary to purchase a variety of modules in order to cover different output voltages. The output voltage can be trimmed in a range of 0.9 Vdc to 5.0 Vdc. When the SMT15C series converter leaves the factory the output has been adjusted to the default voltage of 0.9 V.

## Notes

- 1  $di/dt = 10$  A/ $\mu$ s,  $V_{in} = \text{Nom}$ ,  $T_c = 25^\circ C$ , load change = 0.50 lo max. to 0.75 lo max, and vice versa.
- 2 Measured with external filter. See Application Note 169 for details.
- 3 Power up is the time from application of dc input to POWER GOOD high. Remote ON/OFF asserted high to POWER GOOD high.
- 4 This product is only for inclusion by professional installers within other equipment and must not be operated as a stand alone product.
- 5 Reserved.
- 6 Measured as per recommended set-up.  $C_{in} = 270 \mu\text{F}$  (20mW ESR max.),  $C_{out} = 680 \mu\text{F}$  (10 mW ESR max.).
- 7 Uses external resistor from TRIM to ground. See Application Note 169 for details. Minimum value 485  $\mu\text{F}$  for 5 V model, 280  $\mu\text{F}$  for 12 V model.
- 8 Signal line assumed  $<3$  m in length.
- 9 External input fusing recommended.
- 10 See Application Note 169 for operation above 50  $^\circ C$ .
- 11 See Application Note 169 for more details.
- 12 TSE RoHS 5/6 (non Pb-free) compliant versions may be available on special request, please contact your local sales representative for details.
- 13 NOTICE: Some models do not support all options. Please contact your local Artesyn representative or use the on-line model number search tool at <http://www.artesyn.com/powergroup/products.htm> to find a suitable alternative.

## Ripple and Noise Specification

Model	Output Voltage	Pk - Pk	RMS
5 V input models	0.9 Vdc to 2.5 Vdc	30 mV	15 mV
	3.3 Vdc	40 mV	15 mV
12 V input models	0.9 Vdc to 2.5 Vdc	50 mV	25 mV
	3.3 Vdc to 5 Vdc	50 mV	25 mV



PIN CONNECTIONS	
PIN NUMBER	FUNCTION
1	Vout
2	Vout
3	Power Good
4	GND
5	GND
6	Vin
7	Trim
8	Remote ON/OFF

## Americas

5810 Van Allen Way  
Carlsbad, CA 92008  
USA  
Telephone: +1 760 930 4600  
Facsimile: +1 760 930 0698

## Europe (UK)

Waterfront Business Park  
Merry Hill, Dudley  
West Midlands, DY5 1LX  
United Kingdom  
Telephone: +44 (0) 1384 842 211  
Facsimile: +44 (0) 1384 843 355

## Asia (HK)

16th - 17th Floors, Lu Plaza  
2 Wing Yip Street, Kwun Tong  
Kowloon, Hong Kong  
Telephone: +852 2176 3333  
Facsimile: +852 2176 3888

For global contact, visit:

[www.powerconversion.com](http://www.powerconversion.com)

[technicalsupport@powerconversion.com](mailto:technicalsupport@powerconversion.com)

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

**Emerson Network Power.**  
The global leader in enabling  
business-critical continuity.

- AC Power
- Connectivity
- DC Power
- **Embedded Power**
- Inbound Power
- Integrated Cabinet Solutions
- Outside Plant
- Precision Cooling
- Site Monitoring and Services

**EmersonNetworkPower. com**

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.  
©2007 Emerson Electric Co.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Artesyn Embedded Technologies](#):

[SMT15C-05SADJJ](#) [SMT15C-12SADJJ](#)