



## Specification:

### Material:

Insulator: PBT, rated UL94V-0

Contacts: Copper Alloy

Shell: Steel

### Contact Plating

Underplate: 40u" Nickel

Contact Area: 1u"~30u" selective gold

Solder Tails Area: 100u" Tin/Lead

### Shell Plating

N=Nickel over copper alloy

### Electrical:

Operation Voltage: 25

Operating Temperature: -5°C to +105°C

### 1.Series No.

2.Type: A=Standard

3.Contact Number: 14.24.36.50

4.Contact Type: F=Female

5.Contact Plating: G=Gold Flash

S=Selective Gold

A=5u" Gold (Selective)

B=10u" Gold (Selective)

C=15u" Gold (Selective)

D=30u" Gold (Selective)

6.Shell Plating: N=Nickel

7.Process Option: A=Standard Type  
(Male+Metal Cover)

8.Fill it with "0"

9.Fill it with "0"

10. Insulator Color: 2=Blue

3=Black

## Description

Name :

A57-XXF

Centronic Solder

**ASSMANN**  
Electronic Components

Position	A	B	C	D
14F	25.20	36.00	43.90	22.70
24F	36.00	46.80	54.70	33.50
36F	48.90	59.70	67.70	46.60
50F	64.10	74.90	82.80	61.70

**RoHS**  
Compliant

THIS DRAWING IS UNPUBLISHED

© Copyright 2005 by Assmann Electronic Components All International Rights Reserved

This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.