

General Description

The AHK432 is a low voltage adjustable shunt reference with thermal stability guaranteed over the full industrial temperature range. This 3-terminal regulator has an output voltage range that extends from V_{REF} (1.24V) to 20V, giving designers outstanding flexibility in the development of power supplies and instrumentation. With a low operating current of 60 μ A, the AHK432 is well suited for battery-powered portable electronic applications. It also has a sharp turn-on characteristic and a dynamic resistance of only 50m Ω making it an excellent replacement for zener diodes in low tempco designs.

The AHK432 is available in the surface-mount 3 or 5 pin SOT-23, as well as the through hole TO-92. Three voltage tolerance options are offered in each package: $\pm 0.5\%$, $\pm 1\%$, and $\pm 2\%$.

Features


- Wide output voltage range (1.24 to 20V)
- Operating current from 60 μ A to 100mA
- Low dynamic output resistance of 50m Ω
- $\pm 0.5\%$ trimmed voltage reference
- 10mV typ. V_{REF} deviation, from -40 to $+105^\circ\text{C}$
- Surface mount 3 or 5 pin SOT-23 or through-hole 3 pin TO-92 packages

Applications

- Notebook computers
- Isolated feedback in switching power supplies
- Adjustable and programmable supplies
- Linear regulators (External Reference)
- Instrumentation
- Medical Electronics*
- Global voltage reference for multiple power supplies

Preliminary Information

Typical Application



Adjustable regulator:

$$OUT = V_{REF} \left(\frac{R1 + R2}{R2} \right)$$

Advanced Analogic Technologies, Inc.

1250 Oakmead Pkwy, Suite 310, Sunnyvale, CA 94086
(408)524-9684 Fax (408)524-9689

Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise noted)

Symbol	Description	Value	Units
V_Z	Cathode Voltage	20	V
I_Z	Continuous Cathode Current	100	mA
I_{REF}	Reference Current	3	mA
T_J	Operating Junction Temperature Range	-40 to 150	$^\circ\text{C}$
Θ_{JA}	Maximum Thermal Resistance	TO-92	160
		SOT-23-3, SOT-23-5	410
P_D	Maximum Power Dissipation	TO-92	780
		SOT-23-3, SOT-23-5	300
T_{LEAD}	Maximum Soldering Temperature (at Leads)	260	$^\circ\text{C}$

Note: Stresses above those listed in Absolute Maximum Ratings may cause permanent damage to the device. Functional operation at conditions other than the operating conditions specified is not implied. Only one Absolute Maximum rating should be applied at any one time.

Electrical Characteristics ($T_J=25^\circ\text{C}$ unless otherwise noted)


				AHK432 0.5%			AHK432 1.0%			AHK432 2.0%			
Symbol	Description	Conditions		min	typ	max	min	typ	Max	min	typ	max	Units
V _{REF}	Reference Voltage	V _Z =V _{REF} I _Z =10mA (test circuit 1)	T _A =25°C	1.234	1.240	1.246	1.228	1.240	1.252	1.215	1.240	1.265	V
			T _A =-40 to +105°C	1.222		1.258	1.215		1.265	1.200		1.280	
V _{DEV}	V _{REF} Temp Deviation	T _A =-40 to +105°C, V _Z =V _{REF} , I _Z =10mA (test circuit 1)			10	25		10	25		10	25	mV
ΔV _{REF} /ΔV _Z	Ratio of Change in V _{REF} to Change in Cathode Voltage	I _Z =10mA, ΔV _Z =16V to V _{REF} (test circuit 2)			-1.0	-2.7		-1.0	-2.7		-1.0	-2.7	mV/V
I _{REF}	Reference Input Current	R1=10kΩ, R2=∞, I _Z =10mA (test circuit 2)			0.15	0.5		0.15	0.5		0.15	0.5	μA
I _{REF(DEV)}	I _{REF} Temp Deviation	T _A =-40 to +105°C R1=10kΩ, R2=∞, I _Z =10mA (test circuit 2)			0.1	0.4		0.1	0.4		0.1	0.4	μA
I _{Z(OFF)}	Off State Cathode Current	V _{REF} =0V (test circuit 3)	V _Z =6V		0.04	0.1		0.04	0.1		0.04	0.1	μA
			V _Z =16V		0.04	0.5		0.04	0.5		0.04	0.5	

Advanced Analogic Technologies, Inc.


1250 Oakmead Pkwy, Suite 310, Sunnyvale, CA 94086
(408)524-9684 Fax (408)524-9689

			AHK432 0.5%			AHK432 1.0%			AHK432 2.0%			
Symbol	Description	Conditions	min	typ	max	min	typ	Max	min	typ	max	Units
R_Z	Dynamic Output Impedance	$f < 1\text{kHz}$, $V_Z = V_{REF}$, $I_Z = 100\mu\text{A}$ to 100mA (test circuit 1)		0.05	0.2		0.05	0.2		0.05	0.2	Ω
$I_{Z(MIN)}$	Minimum Operating Current	$V_Z = V_{REF}$ (test circuit 1)		60	80		60	80		60	80	μA


Test Circuits



Test Circuit 1



Test Circuit 2




Test Circuit 3


Typical Characteristics

(Unless otherwise noted, $T_A = 25^\circ\text{C}$, $I_Z = 10\text{mA}$)


Cathode Current v. Cathode Voltage




Cathode Current v. Cathode Voltage




Reference Voltage v. Temperature




Reference Current v. Temperature



Cathode Current v. Temperature




Ratio of $\Delta V_{REF} / \Delta V_Z$ v. Temperature




(Unless otherwise noted, $T_A = 25^\circ\text{C}$, $I_Z = 10\text{mA}$)



Cathode Impedance v. Temperature



Impedance v. Frequency





Gain and Phase v. Frequency




Test Circuit for Voltage Gain and Phase

Stability Boundary




Test Circuit for Stability

Functional Block Diagram



Symbol Diagram



Ordering Information

Package	Bulk or Tape and Reel	Tolerance		
		0.5%	1.0%	2.0%
SOT-23-3	Bulk	N/A	N/A	N/A
SOT-23-5		N/A	N/A	N/A
TO-92		AHK432ILY-.5-B1	AHK432ILY-1-B1	AHK432ILY-2-B1
SOT-23-3	Tape and Reel	AHK432IGY-.5-T1	AHK432IGY-1-T1	AHK432IGY-2-T1
SOT-23-5		AHK432IGV-.5-T1	AHK432IGV-1-T1	AHK432IGV-2-T1
TO-92	Ammo	AHK432-.5-A1	AHK432EBR-1-A1	AHK432EBR-2-A1

* LIFE SUPPORT POLICY




AnalogicTech's PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF Advanced Analogic Technologies Inc. As used herein: 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.


Advanced Analogic Technologies, Inc.

1250 Oakmead Pkwy, Suite 310, Sunnyvale, CA 94086
(408)524-9684 Fax (408)524-9689

Pin Configuration



Package Information




Dim	Millimeters		Inches	
	Min	Max	Min	Max
A	2.40	2.60	0.094	0.102
A1	0.70	0.90	0.028	0.036
b	0.35	0.55	0.014	0.022
C	0.00	0.00	0.000	0.000
D	2.80	3.20	0.110	0.126
E	3.80	4.20	0.149	0.165
e	0.00	0.00	0.000	0.000
F	1.91	2.31	0.075	0.091
G	3.35	3.75	0.132	0.148
H	0.00	0.15	0.000	0.006
L	13.80	14.20	0.543	0.559
θ1	2°		2°	
θ2	5°		5°	

Note: PACKAGE OUTLINE EXCLUSIVE OF ANY MOLD FLASHES AND BURR DIMENSION

Advanced Analogic Technologies, Inc.


1250 Oakmead Pkwy, Suite 310, Sunnyvale, CA 94086
(408)524-9684 Fax (408)524-9689

SOT-23-3


Dim	Millimeters		Inches	
	Min	Max	Min	Max
A	.887	1.02	0.034	.040
A1	.013	0.10	0.0005	.004
A2	-	-	-	-
b	0.37	0.51	0.015	0.020
C	0.085	0.180	0.003	0.007
D	2.80	3.04	0.110	0.120
E	1.20	1.40	0.047	0.055
e	1.78	2.05	0.070	0.080
H	2.10	2.64	0.083	0.104
L	-	0.69	-	0.027
S	0.45	0.60	0.018	0.024
S1	0.89	1.03	0.035	0.040
θ1	0°	8°	0°	8°

Note:

1. PACKAGE BODY SIZE EXCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.
2. TOLERANCE ± 0.1000 mm (4mi) UNLESS OTHERWISE SPECIFIED
3. COPLANRITY: 0.1000
4. DIMENSION L IS MEASURED IN GAGE PLANE

SOT-23-5


Dim	Millimeters		Inches	
	Min	Max	Min	Max
A	0.95	1.45	0.037	0.057
A1	0.05	0.15	0.002	0.006
A2	0.90	1.30	0.035	0.051
b	0.35	0.50	0.014	0.019
c	0.08	0.20	0.003	0.078
D	2.84	3.00	0.112	0.112
E	1.50	1.70	0.059	0.067
e	1.90		0.0748	
H	2.60	3.00	0.102	0.118
L	0.35	0.55	.0137	.0216
S	0.47	0.55	0.019	.0216
S1	.95		0.037	
θ	0°	10°	0°	10°

Advanced Analogic Technologies, Inc.

1250 Oakmead Pkwy, Suite 310, Sunnyvale, CA 94086
(408)524-9684 Fax (408)524-9689