

## IH-series

Reverse conducting IGBT with monolithic body diode

# IHW20N135R3



Datasheet

Industrial & Multimarket

## Reverse conducting IGBT with monolithic body diode

### Features:

- Offers new higher breakdown voltage to 1350V for improved reliability
- Powerful monolithic body diode with low forward voltage designed for soft commutation only
- TRENCHSTOP™ technology offering:
  - very tight parameter distribution
  - high ruggedness, temperature stable behavior
  - low  $V_{CEsat}$
  - easy parallel switching capability due to positive temperature coefficient in  $V_{CEsat}$
- Low EMI
- Qualified according to JESD-022 for target applications
- Pb-free lead plating; RoHS compliant
- Halogen free (according to IEC 61249-2-21)
- Complete product spectrum and PSpice Models:  
<http://www.infineon.com/igbt/>



### Applications:

- Inductive cooking

### Package pin definition:

- Pin 1 - gate
- Pin 2 & backside - collector
- Pin 3 - emitter



### Key Performance and Package Parameters

| Type        | $V_{CE}$ | $I_C$ | $V_{CEsat}$ , $T_{vj}=25^{\circ}C$ | $T_{vjmax}$ | Marking  | Package    |
|-------------|----------|-------|------------------------------------|-------------|----------|------------|
| IHW20N135R3 | 1350V    | 20A   | 1.6V                               | 175°C       | H20R1353 | PG-TO247-3 |

**Table of Contents**

|                                           |    |
|-------------------------------------------|----|
| Description .....                         | 2  |
| Table of Contents .....                   | 3  |
| Maximum ratings .....                     | 4  |
| Thermal Resistance .....                  | 4  |
| Electrical Characteristics .....          | 5  |
| Electrical Characteristics diagrams ..... | 7  |
| Package Drawing .....                     | 13 |
| Testing Conditions .....                  | 14 |
| Revision History .....                    | 15 |
| Disclaimer .....                          | 15 |

### Maximum ratings

| Parameter                                                                                    | Symbol      | Value                | Unit        |
|----------------------------------------------------------------------------------------------|-------------|----------------------|-------------|
| Collector-emitter voltage                                                                    | $V_{CE}$    | 1350                 | V           |
| DC collector current, limited by $T_{vjmax}$<br>$T_C = 25^{\circ}C$<br>$T_C = 100^{\circ}C$  | $I_C$       | 40.0<br>20.0         | A           |
| Pulsed collector current, $t_p$ limited by $T_{vjmax}$                                       | $I_{Cpuls}$ | 60.0                 | A           |
| Turn off safe operating area $V_{CE} \leq 1350V$ , $T_{vj} \leq 175^{\circ}C$                | -           | 60.0                 | A           |
| Diode forward current, limited by $T_{vjmax}$<br>$T_C = 25^{\circ}C$<br>$T_C = 100^{\circ}C$ | $I_F$       | 40.0<br>20.0         | A           |
| Diode pulsed current, $t_p$ limited by $T_{vjmax}$                                           | $I_{Fpuls}$ | 60.0                 | A           |
| Gate-emitter voltage<br>Transient Gate-emitter voltage ( $t_p \leq 10\mu s$ , $D < 0.010$ )  | $V_{GE}$    | $\pm 20$<br>$\pm 25$ | V           |
| Power dissipation $T_C = 25^{\circ}C$<br>Power dissipation $T_C = 100^{\circ}C$              | $P_{tot}$   | 310.0<br>155.0       | W           |
| Operating junction temperature                                                               | $T_{vj}$    | -40...+175           | $^{\circ}C$ |
| Storage temperature                                                                          | $T_{stg}$   | -55...+175           | $^{\circ}C$ |
| Soldering temperature,<br>wave soldering 1.6 mm (0.063 in.) from case for 10s                |             | 260                  | $^{\circ}C$ |
| Mounting torque, M3 screw<br>Maximum of mounting processes: 3                                | $M$         | 0.6                  | Nm          |

### Thermal Resistance

| Parameter                                    | Symbol        | Conditions | Max. Value | Unit |
|----------------------------------------------|---------------|------------|------------|------|
| <b>Characteristic</b>                        |               |            |            |      |
| IGBT thermal resistance,<br>junction - case  | $R_{th(j-c)}$ |            | 0.48       | K/W  |
| Diode thermal resistance,<br>junction - case | $R_{th(j-c)}$ |            | 0.48       | K/W  |
| Thermal resistance<br>junction - ambient     | $R_{th(j-a)}$ |            | 40         | K/W  |

**Electrical Characteristic, at  $T_{vj} = 25^{\circ}\text{C}$ , unless otherwise specified**

| Parameter                            | Symbol        | Conditions                                                                                                    | Value       |                      |                 | Unit     |
|--------------------------------------|---------------|---------------------------------------------------------------------------------------------------------------|-------------|----------------------|-----------------|----------|
|                                      |               |                                                                                                               | min.        | typ.                 | max.            |          |
| Static Characteristic                |               |                                                                                                               |             |                      |                 |          |
| Collector-emitter breakdown voltage  | $V_{(BR)CES}$ | $V_{GE} = 0V, I_C = 0.50mA$                                                                                   | 1350        | -                    | -               | V        |
| Collector-emitter saturation voltage | $V_{CESat}$   | $V_{GE} = 15.0V, I_C = 20.0A$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 125^{\circ}C$<br>$T_{vj} = 175^{\circ}C$ | -<br>-<br>- | 1.60<br>1.80<br>1.90 | 1.80<br>-<br>-  | V        |
| Diode forward voltage                | $V_F$         | $V_{GE} = 0V, I_F = 20.0A$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 125^{\circ}C$<br>$T_{vj} = 175^{\circ}C$    | -<br>-<br>- | 1.60<br>1.73<br>1.80 | 1.80<br>-<br>-  | V        |
| Gate-emitter threshold voltage       | $V_{GE(th)}$  | $I_C = 0.50mA, V_{CE} = V_{GE}$                                                                               | 5.1         | 5.8                  | 6.4             | V        |
| Zero gate voltage collector current  | $I_{CES}$     | $V_{CE} = 1350V, V_{GE} = 0V$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 175^{\circ}C$                            | -<br>-      | -<br>-               | 100.0<br>2500.0 | $\mu A$  |
| Gate-emitter leakage current         | $I_{GES}$     | $V_{CE} = 0V, V_{GE} = 20V$                                                                                   | -           | -                    | 100             | nA       |
| Transconductance                     | $g_{fs}$      | $V_{CE} = 20V, I_C = 20.0A$                                                                                   | -           | 14.8                 | -               | S        |
| Integrated gate resistor             | $r_G$         |                                                                                                               |             | none                 |                 | $\Omega$ |

**Electrical Characteristic, at  $T_{vj} = 25^{\circ}\text{C}$ , unless otherwise specified**

| Parameter                    | Symbol           | Conditions                                                             | Value |       |      | Unit |
|------------------------------|------------------|------------------------------------------------------------------------|-------|-------|------|------|
|                              |                  |                                                                        | min.  | typ.  | max. |      |
| Dynamic Characteristic       |                  |                                                                        |       |       |      |      |
| Input capacitance            | C <sub>ies</sub> | V <sub>CE</sub> = 25V, V <sub>GE</sub> = 0V, f = 1MHz                  | -     | 1500  | -    | pF   |
| Output capacitance           | C <sub>oes</sub> |                                                                        | -     | 55    | -    |      |
| Reverse transfer capacitance | C <sub>res</sub> |                                                                        | -     | 45    | -    |      |
| Gate charge                  | Q <sub>G</sub>   | V <sub>CC</sub> = 1080V, I <sub>C</sub> = 20.0A, V <sub>GE</sub> = 15V | -     | 195.0 | -    | nC   |

**Switching Characteristic, Inductive Load**

| Parameter           | Symbol       | Conditions                                                                                                                                                                                                                                                                            | Value |      |      | Unit |
|---------------------|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|------|------|
|                     |              |                                                                                                                                                                                                                                                                                       | min.  | typ. | max. |      |
| Turn-off delay time | $t_{d(off)}$ | $T_{vj} = 25^{\circ}\text{C},$<br>$V_{CC} = 600\text{V}, I_C = 20.0\text{A},$<br>$V_{GE} = 0.0/15.0\text{V},$<br>$r_G = 15.0\Omega, L\sigma = 175\text{nH},$<br>$C\sigma = 40\text{pF}$<br>$L\sigma, C\sigma$ from Fig. E<br>Energy losses include "tail" and diode reverse recovery. | -     | 335  | -    | ns   |
| Fall time           | $t_f$        |                                                                                                                                                                                                                                                                                       | -     | 50   | -    | ns   |
| Turn-off energy     | $E_{off}$    |                                                                                                                                                                                                                                                                                       | -     | 1.30 | -    | mJ   |

**Switching Characteristic, Inductive Load**

| Parameter                                              | Symbol              | Conditions                                                                                                                                                                                                                                                                                          | Value |      |      | Unit |
|--------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|------|------|
|                                                        |                     |                                                                                                                                                                                                                                                                                                     | min.  | typ. | max. |      |
| IGBT Characteristic, at $T_{vj} = 175^{\circ}\text{C}$ |                     |                                                                                                                                                                                                                                                                                                     |       |      |      |      |
| Turn-off delay time                                    | $t_{d(\text{off})}$ | $T_{vj} = 175^{\circ}\text{C}$ ,<br>$V_{CC} = 600\text{V}$ , $I_C = 20.0\text{A}$ ,<br>$V_{GE} = 0.0/15.0\text{V}$ ,<br>$r_G = 15.0\Omega$ , $L\sigma = 175\text{nH}$ ,<br>$C\sigma = 40\text{pF}$<br>$L\sigma$ , $C\sigma$ from Fig. E<br>Energy losses include “tail” and diode reverse recovery. | -     | 405  | -    | ns   |
| Fall time                                              | $t_f$               |                                                                                                                                                                                                                                                                                                     | -     | 100  | -    | ns   |
| Turn-off energy                                        | $E_{\text{off}}$    |                                                                                                                                                                                                                                                                                                     | -     | 2.25 | -    | mJ   |




Figure 1. **Collector current as a function of switching frequency**  
( $T_{vj} \leq 175^\circ\text{C}$ ,  $D=0.5$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $r_G=15\Omega$ )




Figure 2. **Forward bias safe operating area**  
( $D=0$ ,  $T_C=25^\circ\text{C}$ ,  $T_{vj} \leq 175^\circ\text{C}$ ;  $V_{GE}=15\text{V}$ )




Figure 3. **Power dissipation as a function of case temperature**  
( $T_{vj} \leq 175^\circ\text{C}$ )




Figure 4. **Collector current as a function of case temperature**  
( $V_{GE} \geq 15\text{V}$ ,  $T_{vj} \leq 175^\circ\text{C}$ )




Figure 5. **Typical output characteristic**  
( $T_{vj}=25^{\circ}\text{C}$ )




Figure 6. **Typical output characteristic**  
( $T_{vj}=175^{\circ}\text{C}$ )




Figure 7. **Typical transfer characteristic**  
( $V_{CE}=20\text{V}$ )




Figure 8. **Typical collector-emitter saturation voltage as a function of junction temperature**  
( $V_{GE}=15\text{V}$ )




Figure 9. **Typical switching times as a function of collector current**  
(inductive load,  $T_{vj}=175^{\circ}\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $r_G=15\Omega$ , Dynamic test circuit in Figure E)




Figure 10. **Typical switching times as a function of gate resistor**  
(inductive load,  $T_{vj}=175^{\circ}\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=20\text{A}$ , Dynamic test circuit in Figure E)




Figure 11. **Typical switching times as a function of junction temperature**  
(inductive load,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=20\text{A}$ ,  $r_G=15\Omega$ , Dynamic test circuit in Figure E)




Figure 12. **Gate-emitter threshold voltage as a function of junction temperature**  
( $I_C=0.5\text{mA}$ )




Figure 13. **Typical switching energy losses as a function of collector current**  
(inductive load,  $T_{vj}=175^{\circ}\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $r_G=15\Omega$ , Dynamic test circuit in Figure E)




Figure 14. **Typical switching energy losses as a function of gate resistor**  
(inductive load,  $T_{vj}=175^{\circ}\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=20\text{A}$ , Dynamic test circuit in Figure E)




Figure 15. **Typical switching energy losses as a function of junction temperature**  
(inductive load,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=20\text{A}$ ,  $r_G=15\Omega$ , Dynamic test circuit in Figure E)




Figure 16. **Typical switching energy losses as a function of collector emitter voltage**  
(inductive load,  $T_{vj}=175^{\circ}\text{C}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=20\text{A}$ ,  $r_G=15\Omega$ , Dynamic test circuit in Figure E)




Figure 17. **Typical turn off switching energy loss for soft switching**  
(inductive load,  $T_{vj}=175^{\circ}\text{C}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=20\text{A}$ ,  $r_G=15\Omega$ , Dynamic test circuit in Figure E)




Figure 18. **Typical gate charge**  
( $I_C=20\text{A}$ )




Figure 19. **Typical capacitance as a function of collector-emitter voltage**  
( $V_{GE}=0\text{V}$ ,  $f=1\text{MHz}$ )




Figure 20. **IGBT transient thermal resistance**  
( $D=t_p/T$ )




Figure 21. Diode transient thermal impedance as a function of pulse width ( $D = t_p / T$ )




Figure 22. Typical diode forward current as a function of forward voltage





Figure 23. Typical diode forward voltage as a function of junction temperature

## PG-TO247-3



| DIM | MILLIMETERS |       | INCHES      |       |
|-----|-------------|-------|-------------|-------|
|     | MIN         | MAX   | MIN         | MAX   |
| A   | 4.83        | 5.21  | 0.190       | 0.205 |
| A1  | 2.27        | 2.54  | 0.089       | 0.100 |
| A2  | 1.85        | 2.16  | 0.073       | 0.085 |
| b   | 1.07        | 1.33  | 0.042       | 0.052 |
| b1  | 1.90        | 2.41  | 0.075       | 0.095 |
| b2  | 1.90        | 2.16  | 0.075       | 0.085 |
| b3  | 2.87        | 3.38  | 0.113       | 0.133 |
| b4  | 2.87        | 3.13  | 0.113       | 0.123 |
| c   | 0.55        | 0.68  | 0.022       | 0.027 |
| D   | 20.80       | 21.10 | 0.819       | 0.831 |
| D1  | 16.25       | 17.65 | 0.640       | 0.695 |
| D2  | 0.95        | 1.35  | 0.037       | 0.053 |
| E   | 15.70       | 16.13 | 0.618       | 0.635 |
| E1  | 13.10       | 14.15 | 0.516       | 0.557 |
| E2  | 3.68        | 5.10  | 0.145       | 0.201 |
| E3  | 1.00        | 2.60  | 0.039       | 0.102 |
| e   | 5.44 (BSC)  |       | 0.214 (BSC) |       |
| N   | 3           |       | 3           |       |
| L   | 19.80       | 20.32 | 0.780       | 0.800 |
| L1  | 4.10        | 4.47  | 0.161       | 0.176 |
| øP  | 3.50        | 3.70  | 0.138       | 0.146 |
| Q   | 5.49        | 6.00  | 0.216       | 0.236 |
| S   | 6.04        | 6.30  | 0.238       | 0.248 |

|                                                                                                                     |
|---------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NO.</b><br>Z8B00003327                                                                                  |
| <b>SCALE</b><br>0 5 7.5mm                                                                                           |
| <b>EUROPEAN PROJECTION</b><br> |
| <b>ISSUE DATE</b><br>09-07-2010                                                                                     |
| <b>REVISION</b><br>05                                                                                               |




Figure A. Definition of switching times




Figure B. Definition of switching losses




Figure C. Definition of diodes switching characteristics





Figure D. Thermal equivalent circuit


Figure E. Dynamic test circuit  
Parasitic inductance  $L_\sigma$ ,  
Parasitic capacitor  $C_\sigma$ ,  
Relief capacitor  $C_r$   
(only for ZVT switching)

**Revision History**

IHW20N135R3

**Revision: 2011-05-03, Rev. 2.1**

Previous Revision

| Revision | Date       | Subjects (major changes since last revision) |
|----------|------------|----------------------------------------------|
| 2.1      | 2011-05-03 | Final data sheet                             |

**We Listen to Your Comments**

Any information within this document that you feel is wrong, unclear or missing at all ?

Your feedback will help us to continuously improve the quality of this document.

Please send your proposal (including a reference to this document) to: [erratum@infineon.com](mailto:erratum@infineon.com)

**Published by****Infineon Technologies AG****81726 Munich, Germany****81726 München, Germany****© 2013 Infineon Technologies AG****All Rights Reserved.****Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics.

With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

**Information**

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

**Warnings**

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.