


PRINT



Where To Buy

Enter Zip Code:

Enter Quantity:

GO

Locking Fork Terminal

T&B Catalog Number: B225
UPC Number: 78621080989
Status: Active

Description:
Non-Insulated Locking Fork Terminal For Wire Range 18-14 Stud Size #10, Metallic

ROHSSUBMITTAL
PACKAGE

Features

- Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.

General

Insulation Type	Non-Insulated
Terminal Series	B
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	18-14
Stud Size	#10

Dimension Information

Stock Thickness	.03
A (inches)	.75
B (inches)	.29
C (inches)	.27
M (inches)	.59

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Click Here
Application Tools	WT110M, WT111M, WT112M, WT2000, ERG4002
Recommended Tool	ERG4002, ERG4005

Packaging

Order Multiple	1000
Inner Package	1000
Outer Package	10000
Package Type	Bulk
Package Height	3.5
Package Length	16.4
Package Width	7.5
T&B Sold in UOM	Each
T&B Weight Per UOM	0.18 lbs. per 100
Alternate Package Qty	B14-10FL

Application Support

Overview	Click Here
Wire Guide Tables	Click Here

Notes

- Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

Certifications

RoHS ComplianceYes [Generate Compliance Certificate](#)

Certifications



File Nbr:
E9809

HOME

Global Site

Report Issue

LOGIN

T&B Access (Dist only)

Suppliers

MyTNB

RESOURCES

Catalog PDFs

End User Toolkit

Solution Set Brochures

Vertical Market Brochures

Where To Buy

SUPPORT

Contact Us

Global Locations

Product Support

Tool Services

Terms

COMPANY

About Us

Careers

Employees

News

© 2013 Thomas & Betts Corporation