


**FEATURES**

- 12 dB Gain
- Balanced Design
- High Linearity
- Low Noise Figure
- Single Supply Operation
- Wide Bandwidth
- -40 to +85 °C


**APPLICATIONS**

- Driver Amplifier
- CATV - Distribution / Drop Amplifiers
- Set Top Boxes
- Home Gateway

**PRODUCT DESCRIPTION**

The ABA3100 is a monolithic IC intended for use in applications requiring high linearity, such as Cellular Telephone Base Station Driver Amplifiers, CATV Fiber Receiver and Distribution Amplifiers, CATV Drop Amplifiers, CATV Set Top Boxes and Home Gateways.

Offered in a modified 16 lead surface mount SOIC package, it is well suited for use in amplifiers where small size, reduced component count, and high reliability are important.



**Figure 1: Block Diagram**




Figure 2: Pin Out

Table 1: Pin Description

PIN	NAME	DESCRIPTION	PIN	NAME	DESCRIPTION
1	FB1	Feedback for Amplifier A1	9	I <sub>ADJ</sub>	Current Adjust
2	RF <sub>IN1</sub>	RF Input of Amplifier A1	10	GND	Ground
3	RF <sub>IN1</sub>	RF Input of Amplifier A1	11	RF <sub>OUT2</sub>	RF Output of Amplifier A2
4	GND	Ground	12	GND	Ground
5	GND	Ground	13	GND	Ground
6	RF <sub>IN2</sub>	RF Input of Amplifier A2	14	RF <sub>OUT1</sub>	RF Output of Amplifier A1
7	RF <sub>IN2</sub>	RF Input of Amplifier A2	15	GND	Ground
8	FB2	Feedback for Amplifier A2	16	GND	Ground

## ELECTRICAL CHARACTERISTICS

Table 2: Absolute Minimum and Maximum Ratings

PARAMETER	MIN	MAX	UNIT
Analog Supply (pins 11, 14)	0	+12	VDC
RF Power at Inputs (pins 2, 3, 6, 7)	-	+10	dBm
Storage Temperature	- 65	+150	°C
Soldering Temperature	-	260	°C
Soldering Time	-	5	sec

Stresses in excess of the absolute ratings may cause permanent damage. Functional operation is not implied under these conditions. Exposure to absolute ratings for extended periods of time may adversely affect reliability.

## Notes:

1. Pins 1, 2, 3, 6, 7 and 8 should be AC-coupled. No external DC bias should be applied.
2. Pin 9 should be AC-grounded. No external DC bias should be applied.

Table 3: Operating Ranges

PARAMETER	MIN	TYP	MAX	UNIT
RF Input / Output Frequency	50	-	1000	MHz
Analog Supply: V <sub>DD</sub> (pins 11, 14)	+4.5	+5	+9	VDC
Case Temperature: T <sub>A</sub>	-40	-	+85	°C

The device may be operated safely over these conditions; however, parametric performance is guaranteed only over the conditions defined in the electrical specifications.

**Table 4: Electrical Specifications**  
 (TA = +25 °C, VDD = + 5 VDC, Test System = 75Ω)

PARAMETER	MIN	TYP	MAX	UNIT	COMMENTS
Gain	11	12	14	dB	
Noise Figure	-	2.5	3.0	dB	50 - 350 MHz
	-	2.7	3.5		350 - 550 MHz
	-	3.2	4.0		550 - 860 MHz
Input / Output Return Loss	10	18	-	dB	
CSO <sup>(1)</sup>	-	-72	-70	dBc	
CTB <sup>(1)</sup>	-	-75	-73	dBc	
2nd Order output Intercept Point (OIP2) <sup>(2)</sup>	-	+60	-	dBm	
3rd Order Output Intercept Point (OIP3) <sup>(2)</sup>	-	+35	-	dBm	
Thermal Resistance	-	-	10	°C/W	
Current Consumption	120	150	170	mA	

Notes:

(1) 132 channels, +25dBmV per channel (measured at the output), 6MHz channel spacing

(2) Two tones: 397 MHz and 403 MHz, +4dBm per tone

## PERFORMANCE DATA

Figure 3: Typical Gain (S21) vs. Frequency







Figure 4: Typical Input and Output Return Loss (S11 and S22) vs. Frequency



**Figure 5: Typical Isolation (S12) vs. Frequency****Figure 6: Typical Noise Figure vs. Frequency**

## APPLICATION INFORMATION




Figure 7: Evaluation Board Layout




Figure 8: Evaluation Board Schematic


Table 5: Evaluation Board Parts List

ITEM	DESCRIPTION	QTY	VENDOR	VENDOR PART NUMBER
C1-C4, C6, C9	0.01uF CHIP CAP.	6	MURATA	GRM39X7R1103K25V
C7, C8	470 pF CHIP CAP.	2	MURATA	GRM39COG471J25V
C10	47 uF ELEC. CAP.	1	DIGI-KEY CORP	P5275-ND
C5, C11	(not installed)			
L1, L2	390 nH CHIP INDUCTOR	2	COILCRAFT	1008CS-391XKBC
CONNECTORS	75 OHMS N MALE PANEL MOUNT	2	PASTERNAK ENTERPRISES	PE4504
T1, T2	BALUN	2	PULSE ENGINEERING	CX2024
	PCB	1	STANDARD PRINTED CIRCUITS, INC.	EBSTA-111899

*Notes:*

1. "N" Connector center pin should be approximately 80 mils in length.
2. Connector tabs must be reduced by 150 mils.
3. Device must be soldered on PC board.

## PACKAGE OUTLINE



S <sub>M<sub>B<sub>0</sub></sub></sub>	INCHES		MILLIMETERS		NOTE
	MIN.	MAX.	MIN.	MAX.	
A	0.058	0.068	1.47	1.73	
A <sub>1</sub>	0.004	0.010	0.10	0.25	
A <sub>2</sub>	0.055	0.065	1.40	1.65	
B	0.013	0.020	0.33	0.50	
B <sub>1</sub>	0.062	0.070	1.58	1.78	
C	0.008	0.010	0.20	0.25	4
D	0.380	0.400	9.66	10.16	2
E	0.150	0.160	3.81	4.06	3
e	0.050	BSC	1.27	BSC	
H	0.226	0.244	5.74	6.20	
L	0.016	0.040	0.41	1.02	
LE	0.030	—	0.76	—	
α	0°	8°	0°	8°	

## NOTES:

1. CONTROLLING DIMENSION: INCHES
2. DIMENSION "D" DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH, PROTRUSIONS AND GATE BURRS SHALL NOT EXCEED 0.006 [0.15mm] PER SIDE.
3. DIMENSION "E" DOES NOT INCLUDE INTER-LEAD FLASH OR PROTRUSIONS. INTER-LEAD FLASH AND PROTRUSIONS SHALL NOT EXCEED 0.010 [0.25mm] PER SIDE.
4. MAXIMUM LEAD TWIST/SKew TO BE  $\pm 0.005$  [0.13mm].
5. LEAD THICKNESS AFTER PLATING TO BE 0.013 [0.33mm] MAXIMUM.

Figure 9: S3 Package Outline - Modified 16 Pin SOIC



**NOTES**

## ORDERING INFORMATION

ORDER NUMBER	TEMPERATURE RANGE	PACKAGE DESCRIPTION	COMPONENT PACKAGING
ABA3100S3P1	-40 to +85 °C	Modified 16 Pin SOIC	3,500 piece Tape and Reel
ABA3100S3P0	-40 to +85 °C	Modified 16 Pin SOIC	Plastic tubes (50 pieces per tube)

**ANADIGICS, Inc.**

141 Mount Bethel Road  
 Warren, New Jersey 07059, U.S.A  
 Tel: +1 (908) 668-5000  
 Fax: +1 (908) 668-5132

<http://www.anadigics.com>

[Mktg@anadigics.com](mailto:Mktg@anadigics.com)

**IMPORTANT NOTICE**

ANADIGICS, Inc. reserves the right to make changes to its products or to discontinue any product at any time without notice. The product specifications contained in Advanced Product Information sheets and Preliminary Data Sheets are subject to change prior to a product's formal introduction. Information in Data Sheets have been carefully checked and are assumed to be reliable; however, ANADIGICS assumes no responsibilities for inaccuracies. ANADIGICS strongly urges customers to verify that the information they are using is current before placing orders.

**WARNING**

ANADIGICS products are not intended for use in life support appliances, devices, or systems. Use of an ANADIGICS product in any such application without written consent is prohibited.