




PRODUCT NUMBER
73305-XXXLF

PLATING OPTION
1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm

PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED
2= POS 2,3,4,5
3= POS 1,2,5,6


WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.



REFERENCE PLAN
DEFINED BY THE
2 HOLD DOWN
BEARING SURFACE

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.



VIEW ACCORDING "V"

SEE NOTE 3






CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		MOD JACK
lfr	ecr no	dr	date	tolerances unless otherwise specified			title
H	F06-0240	DLE	06.07.18	angles	linear	mm	SMT RA JACK
J	F09-0070	LSA	09.07.23	±2'		scale 2:1	6 POS OUTSIDE
K	B-15798	JFA	13.09.09	dr	D LEGRAND	04.10.18	dwg no
L	F-21888	AMA	15.09.09	enr	P NIZZI	04.10.18	sheet 1 of 3
F	F04-0363	DLE	04.10.18	chr	D LEGRAND	04.10.18	73305
G	F05-0247	DLE	05.09.12	appd	P.NZ	04.10.18	A3
sheet	revision	L	E	B			type
index	sheet	1	2	3			CUSTOMER Drawing



PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3


CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406 ISO 1101		mm		MOD-JACK	
litr		ecr no	dr	date		tolerances unless otherwise specified		title	
D		F80620	DLE	98.11.26		angles		SMT RA JACK	
E		F06-0240	DLE	06.07.18		linear		6 POS. OUTSIDE	
						scale 1:1		dwg no	
						FCJ		73305	
								sheet 2 of 3	
								A3	
								type	
								CUSTOMER Drawing	
sheet index		revision sheet							



FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family	
				ISO 1302	ISO 406 ISO 1101		MOD JACK	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
A	F04-0363	DLE	04.10.18	angles	±0.13	mm	SMT RA JACK	
B	F06-0240	DLE	06.07.18	linear		scale 2:1	6 POS OUTSIDE	
				±2°				
		dr	D LEGRAND	04.10.18			dwg no	
		engr	P NIZZI	04.10.18			sheet 3 of - size	
		chr	D LEGRAND	04.10.18			73305 A4	
		appd	P NZ	04.10.18			type	
							CUSTOMER Drawing	

form: A4