



- SMD COLLAPSIBLE BOXES
- SMD BOXES
- SMD CABINETS
- SMD SPOOL STANDS
- CONDUCTIVE CABINETS
- CONDUCTIVE BOXES
- CONDUCTIVE CASES




SMD boxes – non-conductive

		Art. No.	Lid	Bottom part	Inside dimensions	Characteristics
N 1		SMD-Box N 1-2-3-2-1	transparent		16 x 12 x 15	non-conductive
		SMD-Box N 1-2-3-4-1	transparent		16 x 12 x 15	non-conductive
		SMD-Box N 1-2-3-6-1	transparent		16 x 12 x 15	non-conductive
		SMD-Box N 1-2-3-7-1	transparent		16 x 12 x 15	non-conductive
		SMD-Box N 1-2-3-8-1	transparent		16 x 12 x 15	non-conductive
		SMD-Box N 1-2-2-2-2			16 x 12 x 15	non-conductive
		SMD-Box N 1-2-2-4-4			16 x 12 x 15	non-conductive
		SMD-Box N 1-2-2-6-6			16 x 12 x 15	non-conductive
		SMD-Box N 1-2-2-7-7			16 x 12 x 15	non-conductive
		SMD-Box N 1-2-2-8-8			16 x 12 x 15	non-conductive
N 2		SMD-Box N 2-2-3-2-1	transparent		37 x 12 x 15	non-conductive
		SMD-Box N 2-2-3-4-1	transparent		37 x 12 x 15	non-conductive
		SMD-Box N 2-2-3-6-1	transparent		37 x 12 x 15	non-conductive
		SMD-Box N 2-2-3-7-1	transparent		37 x 12 x 15	non-conductive
		SMD-Box N 2-2-3-8-1	transparent		37 x 12 x 15	non-conductive
		SMD-Box N 2-2-2-2-2			37 x 12 x 15	non-conductive
		SMD-Box N 2-2-2-4-4			37 x 12 x 15	non-conductive
		SMD-Box N 2-2-2-6-6			37 x 12 x 15	non-conductive
		SMD-Box N 2-2-2-7-7			37 x 12 x 15	non-conductive
		SMD-Box N 2-2-2-8-8			37 x 12 x 15	non-conductive
N 3		SMD-Box N 3-2-3-2-1	transparent		41 x 37 x 15	non-conductive
		SMD-Box N 3-2-3-4-1	transparent		41 x 37 x 15	non-conductive
		SMD-Box N 3-2-3-6-1	transparent		41 x 37 x 15	non-conductive
		SMD-Box N 3-2-3-7-1	transparent		41 x 37 x 15	non-conductive
		SMD-Box N 3-2-3-8-1	transparent		41 x 37 x 15	non-conductive
		SMD-Box N 3-2-2-2-2			41 x 37 x 15	non-conductive
		SMD-Box N 3-2-2-4-4			41 x 37 x 15	non-conductive
		SMD-Box N 3-2-2-6-6			41 x 37 x 15	non-conductive
		SMD-Box N 3-2-2-7-7			41 x 37 x 15	non-conductive
		SMD-Box N 3-2-2-8-8			41 x 37 x 15	non-conductive
N 4		SMD-Box N 4-2-3-2-1	transparent		68 x 57 x 15	non-conductive
		SMD-Box N 4-2-3-4-1	transparent		68 x 57 x 15	non-conductive
		SMD-Box N 4-2-3-6-1	transparent		68 x 57 x 15	non-conductive
		SMD-Box N 4-2-3-7-1	transparent		68 x 57 x 15	non-conductive
		SMD-Box N 4-2-3-8-1	transparent		68 x 57 x 15	non-conductive
		SMD-Box N 4-2-2-2-2			68 x 57 x 15	non-conductive
		SMD-Box N 4-2-2-4-4			68 x 57 x 15	non-conductive
		SMD-Box N 4-2-2-6-6			68 x 57 x 15	non-conductive
		SMD-Box N 4-2-2-7-7			68 x 57 x 15	non-conductive
		SMD-Box N 4-2-2-8-8			68 x 57 x 15	non-conductive
N 5		SMD-Box N 5-2-3-2-1	transparent		180 x 68 x 15	non-conductive
		SMD-Box N 5-2-3-4-1	transparent		180 x 68 x 15	non-conductive
		SMD-Box N 5-2-3-6-1	transparent		180 x 68 x 15	non-conductive
		SMD-Box N 5-2-3-7-1	transparent		180 x 68 x 15	non-conductive
		SMD-Box N 5-2-3-8-1	transparent		180 x 68 x 15	non-conductive
		SMD-Box N 5-2-2-2-2			180 x 68 x 15	non-conductive
		SMD-Box N 5-2-2-4-4			180 x 68 x 15	non-conductive
		SMD-Box N 5-2-2-6-6			180 x 68 x 15	non-conductive
		SMD-Box N 5-2-2-7-7			180 x 68 x 15	non-conductive
		SMD-Box N 5-2-2-8-8			180 x 68 x 15	non-conductive

SMD boxes – conductive – dissipative


		Art. No.	Lid	Bottom part	Inside dimensions	Characteristics
N 1		SMD-Box N 1-6-6-10-10	●	●	16 x 12 x 15	
		SMD-Box N 1-6-6-1 LS	transparent*	●	16 x 12 x 15	
		SMD-Box N 1-11-6-4-1 LS	transparent*	●	16 x 12 x 15	 
		SMD-Box N 1-11-6-6-1 LS	transparent*	●	16 x 12 x 15	 
		SMD-Box N 1-11-6-8-1 LS	transparent*	●	16 x 12 x 15	 
		Diss-SMD-Box N1-11-11-4-4	●	●	16 x 12 x 15	
		Diss-SMD-Box N1-11-11-6-6	●	●	16 x 12 x 15	
		Diss-SMD-Box N1-11-11-8-8	●	●	16 x 12 x 15	
N 2		SMD-Box N 2-6-6-10-10	●	●	37 x 12 x 15	
		SMD-Box N 2-6-6-10-1 LS	transparent*	●	37 x 12 x 15	
		SMD-Box N 2-11-6-4-1 LS	transparent*	●	37 x 12 x 15	 
		SMD-Box N 2-11-6-6-1 LS	transparent*	●	37 x 12 x 15	 
		SMD-Box N 2-11-6-8-1 LS	transparent*	●	37 x 12 x 15	 
		Diss-SMD-Box N2-11-11-4-4	●	●	37 x 12 x 15	
		Diss-SMD-Box N2-11-11-6-6	●	●	37 x 12 x 15	
		Diss-SMD-Box N2-11-11-8-8	●	●	37 x 12 x 15	
N 3		SMD-Box N 3-6-6-10-10	●	●	41 x 37 x 15	
		SMD-Box N 3-6-6-10-1 LS	transparent*	●	41 x 37 x 15	
		SMD-Box N 3-11-6-4-1 LS	transparent*	●	41 x 37 x 15	 
		SMD-Box N 3-11-6-6-1 LS	transparent*	●	41 x 37 x 15	 
		SMD-Box N 3-11-6-8-1 LS	transparent*	●	41 x 37 x 15	 
		Diss-SMD-Box N3-11-11-4-4	●	●	41 x 37 x 15	
		Diss-SMD-Box N3-11-11-6-6	●	●	41 x 37 x 15	
		Diss-SMD-Box N3-11-11-8-8	●	●	41 x 37 x 15	
N 4		SMD-Box N 4-6-6-10-10	●	●	68 x 57 x 15	
		SMD-Box N 4-6-6-10-1 LS	transparent*	●	68 x 57 x 15	
		SMD-Box N 4-11-6-4-1 LS	transparent*	●	68 x 57 x 15	 
		SMD-Box N 4-11-6-6-1 LS	transparent*	●	68 x 57 x 15	 
		SMD-Box N 4-11-6-8-1 LS	transparent*	●	68 x 57 x 15	 
		Diss-SMD-Box N4-11-11-4-4	●	●	68 x 57 x 15	
		Diss-SMD-Box N4-11-11-6-6	●	●	68 x 57 x 15	
		Diss-SMD-Box N4-11-11-8-8	●	●	68 x 57 x 15	
N 5						
		SMD-Box N 5-6-6-10-10	●	●	180 x 68 x 15	
		SMD-Box N 5-6-6-10-1 LS	transparent*	●	180 x 68 x 15	

SMD CABINETS WITH CHIP CONTAINERS



Art. No. **144 SMD-Boxen N1**
fitting exactly into **A 1-4/16-6-10**

Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 144**

Cabinet with 3 drawers incl.


3 x 144 = 432 pcs



Art. No. SMD cabinet **A 1-4 ESD 144**

Cabinet with 3 drawers incl.

3 x 144 = 432 pcs



Art. No. **72 SMD-Boxen N2**
fitting exactly into **A 1-4/16-6-10**


Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 72**

Cabinet with 3 drawers incl.


3 x 72 = 216 pcs



Art. No. SMD cabinet **A 1-4 ESD 72**


Cabinet with 3 drawers incl.

3 x 72 = 216 pcs



Art. No. **36 SMD-Boxen N3**
fitting exactly into **A 1-4/16-6-10**


Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 36**

Cabinet with 3 drawers incl.


3 x 36 = 108 pcs



Art. No. SMD cabinet **A 1-4 ESD 36**


Cabinet with 3 drawers incl.

3 x 36 = 108 pcs



Art. No. **16 SMD-Boxen N4**
fitting exactly into **A 1-4/16-6-10**


Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 16**

Cabinet with 3 drawers incl.


3 x 16 = 48 pcs




Art. No. SMD cabinet **A 1-4 ESD 16**

Cabinet with 3 drawers incl.


3 x 16 = 48 pcs



Art. No. **A 1-4/4 Bunt MIX**
 Multicoloured cabinet (not ESD) with 4 drawers
 various SMD collapsible boxes per drawer, sizes N1-N4
 (cf. page 60)



Art. No. **A 1-4/4 ESD MIX**
 Conductive cabinet with 4 drawers
 various SMD collapsible boxes per drawer, sizes N1-N4
 (cf. page 75)



Art. No. **144 SMD-Boxen N1** **72 SMD-Boxen N2** **36 SMD-Boxen N3** **16 SMD-Boxen N4**



Art. No. **SMD-Rollboy Single N1**
 Art. No. **SMD-Rollboy Single N2**
 Art. No. **SMD-Rollboy Single N3**
 Art. No. **SMD-Rollboy Single N4**
 Art. No. **SMD-Rollboy Single Mix** (on request)



Art. No. **SMD-EGB-Rollboy Single N1**
 Art. No. **SMD-EGB-Rollboy Single N2**
 Art. No. **SMD-EGB-Rollboy Single N3**
 Art. No. **SMD-EGB-Rollboy Single N4**
 Art. No. **SMD-EGB-Rollboy Single Mix** (on request)

SMD SPOOL RACK



Art. No. **V 11-4** (not conductive)
with 25 variable partitions and
continuous identification rail
(for spools up to 250 mm Ø)

Basic dimensions 450 x 240

Colours



Art. No. **V 11-7**
with 25 variable partitions and
continuous identification rail
(for spools up to 330 mm Ø)

Basic dimensions 455 x 315

Colours



Art. No. **V 11-14**
with 10 variable partitions and
continuous identification rail
(for spools up to 380 mm Ø)

Basic dimensions 455 x 360

Colours



Art. No. **V 11-4-6-10** (conductive)
with 25 variable partitions and
continuous identification rail
(for spools up to 250 mm Ø)

Basic dimensions 450 x 240

Colours



Art. No. **V 11-7-6-10** (conductive)
with 25 variable partitions and
continuous identification rail
(for spools up to 330 mm Ø)

Basic dimensions 455 x 315

Colours



Art. No. **V 11-14-6-10** (conductive)
with 10 variable partitions and
continuous identification rail
(for spools up to 380 mm Ø)

Basic dimensions 455 x 360

Colours



Art. No. **V 11-8-6-10** (conductive)
Spool stands for horizontal storage
of SMD spools up to 180 mm Ø
(First in/first out)

Outside dimensions 186 x 173 x 210

Inside dimensions 182 x 169 x 190



Art. No. **V 11-9-6-10** (conductive)
Spool stands for horizontal storage
of SMD spools up to 330 mm Ø
(First in/first out)

Outside dimensions 339 x 319 x 210

Inside dimensions 335 x 315 x 190



Art. No. **V 11-15-6-10** (conductive)
Spool stands for horizontal storage
of SMD spools up to 380 mm Ø
(First in/first out)

Outside dimensions 380 x 370 x 250

Inside dimensions 375 x 365 x 230

SMD CABINETS WITH ROUND BOXES FOR CHIPS




Art. No. **V 11-5**
SMD packing set with 32 cavities
18 Ø x 12 mm with individual
top cover (non-conductive)



Art. No. **A 1-3 SMD**
for 6 pcs **V 11-5** (without top cover)


Art. No. **A 1-3 SMD NORMAL**
non conductive




Art. No. SMD cabinet **A 1-1 SMD** Liastat
6-fold cabinets with inserts and
6 x 42 round boxes **V 1-12-6-10**
27 Ø x 13




Art. No. SMD cabinet **A 1-1 SMD white**



Art. No. SMD cabinet **A 1-1 SMD yellow**



Art. No. SMD cabinet **A 1-1 SMD green**




Art. No. SMD cabinet **A 1-1 SMD red**



Art. No. SMD cabinet **A 1-1 SMD blue**



Art. No. SMD cabinet **A 1-1 SMD/5 bunt**



Art. No. **V 11-3**
SMD packing set with 60 boxes
and foam grid

Art. No. **V 4-1**
6 x 6 x 19 mm
(non conductive)




Art. No. **V 11-1**
SMD packing set with 130 boxes
and foam grid

Art. No. **V 4-1**
6 x 6 x 19 mm
(non conductive)



SERIES A 1-1 DRAWER FORMAT

Art. No. **A 1-1 S** 6-fold Liastat

Drawer 261 x 238 x 20 (inside)


Characteristics conductive

Art. No. **SK 730-6-10**

Drawer 261 x 238 x 20 (inside)

Characteristics conductive


Note Please order inserts and identification labels separately

Art. No. **A 1-1 SMD** complete with round boxes

Drawer 261 x 238 x 20 (inside)


Characteristics conductive

Note Please order identification labels separately, further designs (clear boxes with conducting layer) see page 73

Art. No. **A 1-1/16-6-10** as stackable box

Inside dimensions 261 x 238 x 20

Characteristics conductive

Art. No. **A 1-1/16-6-10** bottom partArt. No. **+ A 1-1/4-6-10** lid
as flat box

Inside dimensions 261 x 238 x 20

Characteristics conductive


Art. No. **A 1-1/16-6-10** bottom partArt. No. **+ A 1-1/4-6-10** lidArt. No. **+ TE ... W-6-10** insert

see below as assortment case


Inside dimensions 261 x 238 x 20

Characteristics conductive


VACUM FORMED STANDARD DRAWER INSERTS Conductive version Liastat *) black, inside dimension of compartments, inside depth 16 mm




TE 4 W-6-10




TE 5 W-6-10




TE 6 W-6-10




TE 16 AW-6-10




TE 16 W-6-10




TE 18 W-6-10




TE 24 W-6-10



TE 36 W-6-10




TE 42 W-6-10



TE 56 W-6-10

SERIES A 1-1 DRAWER FORMAT




Art. No.	A 1-4 9-fold Liastat
Drawer	340 x 250 x 22 (inside)
Characteristics	conductive
Note	Please order inserts and identification labels separately




Art. No.	SK 734-6-10
Drawer	340 x 250 x 22 (inside)
Characteristics	conductive
Note	Please order inserts and identification labels separately, lateral hinge



Art. No.	A 1-4 Liacarry
Drawer	340 x 250 x 22 (inside)
Characteristics	conductive
Note	Inserts, identification labels and declaration form pockets to be ordered separately, lateral hinge



Art. No.	Drawer A 1-4/16-6-10
	as stackable box
Inside dimensions	340 x 250 x 22
Characteristics	conductive
Note	




Art. No.	A 1-4/6 ESD insert spare parts cabinet
Inside dimensions	340 x 250 x 22
Characteristics	conductive /antistatic
	3 drawers, insert with 42 subdivisions each
	2 drawers, insert with 25 subdivisions each
	1 drawer, insert with 16 subdivisions each




Art. No.	A 1-4/16-6-10 bottom part
Art. No.	+ A 1-2/4-6-10 lid
Art. No.	+ TE ... 4-6-10 insert
	see below as assortment cases
Inside dimensions	340 x 250 x 22
Characteristics	conductive

VACUM FORMED STANDARD DRAWER INSERTS Inside dimensionsof compartments, conductive type Liastat *) black



SERIES A 1-2 DRAWER FORMAT

Art. No. **A 1-2 S 6-fold Liastat**

Drawer 340 x 250 x 40 (inside)

Characteristics conductive


Note Please order inserts and identification labels separately

Art. No. **SK 731-6-10**

Drawer 340 x 250 x 40 (inside)

Characteristics conductive

Note Please order inserts and identification labels separately, lateral hinge

Art. No. **A 1-2 Liacarry**




Drawer 340 x 250 x 40 (inside)

Characteristics conductive


Note Inserts, identification labels and declaration form pockets to be ordered separately, lateral hinge

DETACHABLE DRAWER INSERTS, conductive type Liastat *) black, standard type grey and white

	24	12	6
grey	SE 24-2-2-9	SE 12-2-2-9	SE 6-2-2-9
white	SE 24-2-2-2	SE 12-2-2-2	SE 6-2-2-2
EGB	SE 24-2-6-10	SE 12-2-6-10	SE 6-2-6-10
outside	62 x 56 x 33 mm	112 x 62 x 33 mm	124 x 112 x 33 mm
inside	59 x 53 x 31 mm	109 x 59 x 31 mm	121 x 109 x 31 mm

Special size **V 6-28/2**; 110 x 42 x 35 mm outside 18 pcs per box

Drawers **A 1-2/16-6-10** with lid, **A 1-2/4-6-10** as flat box or with inserts as assortment boxArt. No. **A 1-2/ESD selective cups Service cabinet**









with 2 drawers with 24, 2 drawers with

12 and 2 drawers with 6 selective cups each


Inside dimensions 340 x 250 x 40

Characteristics conductive /antistatic

VACUM FORMED STANDARD DRAWER INSERTS Conductive version Liastat *) black, inside dimension of compartments, inside depth 16 mm

	 TE 3 S-6-10	 TE 6 S-6-10	 TE 9 S-6-10	 TE 12 S-6-10
	 TE 16 S-6-10	 TE 22 S-6-10 Compartments rounded at the bottom	 TE 25 S-6-10	 TE 30 S-6-10 Compartments rounded at the bottom


SERIES A 1-60 DRAWER FORMAT



Art. No.	A 1-60 4-fold Liastat
Drawer	340 x 250 x 62 (inside)
Characteristics	conductive
Note	Please order inserts and identification labels separately



Art. No.	SK 732-6-10
Drawer	340 x 250 x 62 (inside)
Characteristics	conductive
Note	Please order inserts and identification labels separately, lateral hinge



Art. No.	A 1-60 Liacarry
Drawer	340 x 250 x 62 (inside)
Characteristics	conductive
Note	Inserts, identification labels and declaration form pockets to be ordered separately, lateral hinge

LOOSE DRAWER INSERTS CONDUCTIVE, standard version, white

	58	30	15	6
white	SE 58-60-1-2	SE 30-60-1-2	SE 15-60-1-2	SE 6-60-1-2
conductive	SE 58-60-6-10	SE 30-60-6-10	SE 15-60-6-10	SE 6-60-6-10
outside	59 x 23 x 60 mm	56 x 50 x 54 mm	113 x 50 x 54 mm	125 x 113 x 54 mm
inside	54 x 18 x 58 mm	53 x 47 x 52 mm	109 x 47 x 52 mm	121 x 109 x 52 mm

VACUM FORMED STANDARD DRAWER INSERTS Conductive version Liastat *) black, inside height 53 mm

	TE 4-60-6-10	TE 6-60-6-10	TE 9-60-6-10	TE 12 K 6-10	TE 24 K 6-10
--	----------------------------	----------------------------	----------------------------	----------------------------	----------------------------

Dimensions in mm.

Dimensions subject to errors and corrections!

* Material Liastat = conductive/antistatic material, black. Surface resistance according to fabrication criteria 10^5 – 10^8 Ohm.

EGB-ROLLBOYS + EGB-DRAWER CABINETS



Art. No. **EGB-Rollboy Single 4**
with 18 drawers
(cf. inside dimensions drawers page 75)
Outside dimensions 318 x 365 x 806
Note Please order inserts separately
conductive pad on request



Art. No. **EGB-Rollboy Single 1**
with 12 drawers
(cf. inside dimensions drawers page 78)
Outside dimensions 318 x 365 x 806
Note Please order inserts separately
conductive pad on request



Art. No. **EGB-Rollboy Single 2**
with 8 drawers
(cf. inside dimensions drawers page 79)
Outside dimensions 318 x 365 x 806
Note Please order inserts separately
conductive pad on request



Art. No. **Spiral cable** extremely flexible
2.4 m x 2 x 1 MOhm safety resistance
Earth connection: 10 mm push-button



Art. No. **Wrist band** adjustable, flexible,
interlaced, silver-plated synthetic fabrics,
antiallergenic



Art. No. **EGB-Rollboy 4 with 36 drawers**
with pad 585 x 365
(cf. inside dimensions drawers page 75)
Outside dimensions 585 x 365 x 806
Note Please order inserts separately




Art. No. **EGB-Rollboy 1 with 24 drawers**
with pad 585 x 365
(cf. inside dimensions drawers page 78)
Outside dimensions 585 x 365 x 806
Note Please order inserts separately



Art. No. **EGB-Rollboy 2 with 16 drawers**
with pad 585 x 365
(cf. inside dimensions drawers page 79)
Outside dimensions 585 x 365 x 806
Note Please order inserts separately

CONDUCTIVE BOXES + SUBDIVISIONS



Printed boards packings


Art. No.	V 11-20*	175 x 100 x 26 inside
Art. No.	V 11-21*	175 x 100 x 47 inside
Art. No.	V 11-22*	175 x 100 x 67 inside
Art. No.	V 11-23*	220 x 100 x 26 inside
Art. No.	V 11-24*	220 x 100 x 47 inside
Art. No.	V 11-25*	220 x 100 x 67 inside

Characteristics non-conductive, white bottom part, crystal clear lid

*) conductive version i.e. bottom part conductive/antistatic, lid conductive, black, vapour-deposited

Order instructions e.g. **V 11 - 20 - 6 - 7 - 10 - 1**

conductive version



Art. No. **ET-1-6-10** Insert tray for Euro boxes

EK 1-2/LWB (400 x 300) stackable,

Inside dimensions 310 x 250 x 20



Art. No. **ET-3-6-10**

Insert tray for Euro boxes

EK 3-4/LWB stackable,

Inside dimensions 520 x 345 x 60

EURO boxes (conductive)						
Art. No.	EK 1-6-10	EK 2-6-10	D 1-2-6-10	EK 3-6-10	EK 4-6-10	D 3-4-6-10
Outside dimensions	400 x 300 x 120	400 x 300 x 220	Top cover	600 x 400 x 120	600 x 400 x 270	Top cover



Pallets for small printed boards

Art. No. **TL 1** for 16 printed boards 105 x 50


Dimensions 350 x 225 x 30

Art. No. **TL 2** for 15 printed boards 100 x 40

Dimensions 350 x 250 x 30

Art. No. **TL 3** for 45 printed boards 50 x 30

Dimensions 350 x 250 x 23



Printed boards L-profile

Art. No. **LP 1**

Dimensions 200 x 274 x 93

Art. No. **LP 2**

Dimensions 350 x 263 x 125

25 slots for printed boards

Transport/storage Service workshop

Dimensions in mm.

Dimensions subject to errors and corrections!

CONDUCTIVE BOXES + SUBDIVISIONS

Art. No. **A 4-1-6-10**

Base area 175 x 100

Top edge 250 x 125

Height inside 34 mm

Colours ●

Art. No. **A 4-2-6-10**

Base area 190 x 120

Height inside 50 mm

Colours ●

Note can be stacked nested, when turned even with content

Art. No. **A 4-3-6-10**

Base area 210 x 150

Top edge 260 x 200

Height inside 40 mm

Colours ●

Art. No. **A 4-4 N-6-10**

Outside dimensions 260 x 165

Height outside 45 mm

Colours ●

Art. No. **A 4-16-6-10**

Outside dimensions 240 x 210 x 82

Inside dimensions 208 x 178 x 79


Colours ●

Art. No. **EGB Papierkorb 14 l**


Outside dimensions 300 Ø x 320

Inside dimensions 255 Ø x 310

Colours ●

Note Volume approx. 14 l, conductive
Polypropylene with EGB warning symbol

ESD boxes (conductive/antistatic)

Art. No. **A 3-1/2-6-10** 282 x 130 x 70 insideArt. No. **A 3-1/4-6-10** Top coverArt. No. **A 3-1/11** RackArt. No. **A 3-1/10-6-10** Cross partitions optional


ESD boxes (conductive/antistatic)

Art. No. **A 3-3/2-6-10** 282 x 130 x 90 insideArt. No. **A 3-1/4-6-10** Top coverArt. No. **A 3-1/11** RackArt. No. **A 3-1/10-6-10** Cross partitions optional


EGB PACKINGS FOR ELECTRONIC PARTS (LIASTAT*)



Art. No.	V 3-12-6-6-10-10	V 3-18-6-6-10-10	V 3-30-6-6-10-10	V 3-40-6-6-10-10
Inside dimensions	50 x 30 x 16	57 x 36 x 17	73 x 42 x 17	80 x 50 x 27
Art. No.	V 3-12/9-6-10	V 3-18/9-6-10	V 3-30/9-6-10	V 3-40/9-6-10
Foam fit for insertion	8 mm	8 mm	8 mm	8 mm
Colours	●	●	●	●



Art. No.	V 8-14 SCH + V-6-6-10-10	V 9-40 SCH + V-6-6-10-10	V 8-12 SCH + V-6-6-10-10
Outside dimensions	295 x 175 x 20	295 x 175 x 20	
Inside dimensions	292 x 160 x 16	73 x 42 x 17	80 x 50 x 27
Colours	●	●	●
Note	various compartment inserts s. p. 29-30, conductive versions on request 54 compartments		various comp. inserts s. p. 28-29, conductive versions on request



Art. No.	V 8-8-6-6-10-10	V 8-9 SCH + V-6-6-10-10	V 8-15-6-6-10-10
Inside dimensions	183 x 108 x 30	196 x 136 x 49 (Outside dimensions 203 x 152 x 53)	220 x 130 x 35
Art. No.	V 8-8/9-6-10		
Foam fit for insertion	8 mm		
Colours	●	●	



Stackable boxes, slip lid	
EGB foam inlays on request	
Art. No.	V 3-16-6-6-10-10 55 x 55 x 25/16 inside
Art. No.	V 3-17-6-6-10-10 55 x 55 x 35/26 inside
Art. No.	V 3-59-6-6-10-10 115 x 55 x 35/26 inside
Art. No.	V 3-60-6-6-10-10 115 x 55 x 55/46 inside
Art. No.	V 3-61-6-6-10-10 115 x 115 x 55/46 inside



Stackable boxes, slip lid	
EGB foam inlays on request	
Art. No.	V 8-1-6-6-10-10 75 x 50 x 33 inside
Art. No.	V 8-2-6-6-10-10 75 x 50 x 45 inside
Art. No.	V 8-5-6-6-10-10 106 x 75 x 46 inside
Art. No.	V 8-7-6-6-10-10 56 x 106 x 46 inside



LiaStat hinged boxes	
Art. No.	V 20-29-6-10 130 x 80 x 14 inside
Art. No.	V 20-30-6-10 130 x 80 x 30 inside
Art. No.	V 20-31-6-10 130 x 80 x 50 inside
Art. No.	V 20-32-6-10 178 x 133 x 78 inside
Art. No.	V 20-33-6-10 221 x 121 x 55 inside

CONDUCTIVE ROUND BOXES, COMPARTMENT BOXES, RECTANGULAR BOXES AND CASES with foam inlays, soft or fit for insertion, on request



Liastat round boxes


Art. No. **V 1-11-6-6-10-10** 26 Ø x 17,5 slip lid

Art. No. **V 1-12-6-10** 26 Ø x 13 slip lid

Art. No. **V 2-101-6-6-10-10** 52 Ø x 40 screw cap

Art. No. **V 2-102-6-6-10-10** 52 Ø x 67 screw cap

Colours ●




Liastat compartment box

Art. No. **V 6-4-6-6-10-10**

6 comp. je 19 x 15 x 5 mm inside

Art. No. **V 6-5-6-6-10-10**

12 comp. je 25 x 10 x 10 mm inside



Liastat rectangular box

Art. No. **V 3-37-6-6-10-10**

Inside dimensions 75 x 75 x 27

Art. No. **V 3-54-6-6-10-10**

Inside dimensions 102 x 85 x 47

Note further sizes see pages 12-15 on request



Art. No.	K 2005 ESD	K 2001 ESD	K 2004 ESD	K 2000 ESD
Inside dimensions	170 x 130 x 37	240 x 170 x 42	270 x 185 x 76	340 x 250 x 53
Colours	●	●	●	●
Equipment	① ② ③ ④	① ② ③ ④ ⑤	① ② ③ ④	① ② ③ ④ ⑤ ⑥

VACUUM FORMED INSERTS Please specify art. no. separately!



Art. No. ① **Noppe** ② **Raster** ③ **TE 6** ④ **TE 9** ⑤ **TE 12** ⑥ **TE 24**