


# Medium-high Voltage Multilayer Ceramic Capacitors

## SMK316B7472KF-T



### ■ Features

- Item Summary  
630V, X7R, 0.0047  $\mu$ F,  $\pm 10\%$ , 1206
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping Embossed 3000pcs

### ■ Products characteristics table

CaseSize (EIA/JIS)	1206/3216
Rated Voltage (max)	630V
Capacitance	0.0047 $\mu$ F
Capacitance Tolerance	$\pm 10\%$
Resistance	10,000 M $\Omega$ min.
Dielectric Loss Tangent	2.5%MAX
Temperature Characteristics (EIA/JIS)	X7R/-
Temperature Range (EIA/JIS)	-55 to +125°C/-
Capacitance Change (EIA/JIS)	$\pm 15\%/-$
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

### ■ External Dimensions

L	3.2mm $\pm 0.15$
W	1.6mm $\pm 0.15$
T	1.15mm $\pm 0.10$
e	0.5mm $+0.35\%/-0.25$

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
Before making final selection, please check product specification.

2014.06.06