





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H2	REVISED PER ECR-16-014469	17OCT2016	BW	RS



1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.5 - 0.15mm² (30-26 AWG).
3. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

3	0.20 [.008] BRASS	1-770835-0
1	0.20 [.008] BRASS	770835-3
PRE-TIN	0.20 [.008] BRASS	770835-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 05MAR03	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C. JONES 05MAR03				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		APVD C. JONES 05MAR03			
	1 PLC ± -		PRODUCT SPEC			
		2 PLC ± 0.13 [.005]	APPLICATION SPEC			
		3 PLC ± -				
		4 PLC ± -				
		ANGLES ± -				
MATERIAL -		FINISH -	WEIGHT 0.000000			
			CUSTOMER DRAWING			
			SIZE A2	CAGE CODE 00779	DRAWING NO C=770835	RESTRICTED TO -
			SCALE 10:1	SHEET 1 of 1	REV H2	