

9808	9101	5650	8679
9808-0-15-XX-16-XX-04-0 Press-fit in 1,70 mounting hole	9101-0-15-XX-16-XX-10-0 Press-fit in 1,70 mounting hole	5650-0-19-XX-16-XX-10-0 Press-fit in 1,70 mounting hole	8679-0-15-XX-16-XX-10-0 Solder mount in 1,80 min. mounting hole
8827	6021	1873	
8827-0-15-XX-16-XX-04-0 Press-fit in 1,55 mounting hole	6021-0-15-XX-16-XX-10-0 Solder mount in 1,57 min. mounting hole	1873-0-15-XX-16-XX-04-0 Press-fit in 1,68 mounting hole	
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: $\pm 0,13$ DIAMETERS: $\pm 0,05$ ANGLES: $\pm 2^\circ$	ORDER CODE: XXXX - X - 1X - XX - 16 - XX - XX - 0 BASIC PART # _____ SPECIFY SHELL FINISH: _____ 01 5,08μm TIN/LEAD OVER NICKEL ◇ 80 5,08μm TIN OVER NICKEL (RoHS) ◇ 15 0,25μm GOLD OVER NICKEL (RoHS) SPECIFY CONTACT FINISH: _____ 01 5,08μm TIN/LEAD OVER NICKEL ◇ 80 5,08μm TIN OVER NICKEL (RoHS) ◇ 27 0,76μm GOLD OVER NICKEL (RoHS) CONTACT #16 CONTACT (DATA ON PAGE 222) RoHS 2002/95/EC		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[9101-0-15-01-16-01-10-0](#) [9101-0-15-01-16-27-10-0](#) [5660-0-15-01-30-02-10-0](#) [5660-0-15-01-30-27-10-0](#) [5650-0-19-01-16-27-10-0](#) [9101-0-15-80-16-80-10-0](#) [9101-0-15-80-16-27-10-0](#) [5660-0-15-80-30-84-10-0](#) [5660-0-15-80-30-27-10-0](#) [5650-0-19-80-16-80-10-0](#) [5650-0-19-80-16-27-10-0](#) [5650-0-19-15-16-27-10-0](#) [5660-0-15-00-00-00-10-0](#) [5660-0-15-15-30-27-10-0](#)