







PCB LAYOUT



SECTION C-C

	Dim A	Dim B
2-6p	±0.20	±0.15
7-12p	±0.30	±0.25
13-16p	±0.40	±0.35

N = Number of poles
 Dim A = N x 6.35
 Dim B = (N-1) x 6.35

SIGN	DATE	DESCRIPTION	APPROVER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Insulator(housing):Thermoplastic (UL 94V-0)
- Metal housing: Brass
- Contacts:Brass
- Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 30A
- Wire range:
Solid wire(AWG): 10-24
Stranded wire(AWG): 10-24
- Torque(Lb-In): 8.9
- Screw: M3.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

RoHS Compliant

PART NUMBER:

OSTKPXX0151

No. of Poles
 02 2 Poles
 03 3 Poles

 12 12 Poles

COLOR
 0: Black
 5: Green (Standard)
 6: Blue
 8: Grey

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

OST ON-SHORE TECHNOLOGY, INC.

TITLE		OSTKP 6.35 series - back single row (without cover)						
PART NO.		OSTKPXX0151		DWG NO.	OSTKPXX0151.DWG			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
Marvin 2009.04.07	Marvin 2009.04.07	Jacke 2008.12.17	Jacke 2008.12.17			UNIT: mm	X.	±0.50
						SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV: B	X.XX	±0.10	
						X°	±1°	

SHEET: 01/01