




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
XX	XX	XXXX	XXXX	06-10-08	XXXX	06-10-08	XXXX	06-10-08
XXXX	XXXX		XXXX	06-10-08	XXXX	06-10-08	XXXX	06-10-08



Key Specifications / Special Features:

- Type : Condenser
- Directivity : Super cardioid
- Impedance : 130 ohms $\pm$ 20%
- Frequency response : 50Hz to 18kHz
- Sensitivity : -70dB $\pm$ 3dB at 1kHz (0dB = 1V/g bar)
- Output : Balance
- Standard operating voltage : DC 48V
- Weight : 220g $\pm$ 10g (with cable)



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
XXXX	06-10-08
CHECKED BY:	DATE:
XXXX	06-10-08
APPROVED BY:	DATE:
XXXX	06-10-08

DRAWING TITLE:

Condenser Microphone

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	CT-03	01P0752	XX
SCALE: NTS		U.O.M.: INCHES [MM]	SHEET: 1 OF 1