



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		D1	REVISED PER ECO-11-004587	11MAR11	RK	HMR


D




44 POS.



52 POS.



68 POS.




84 POS.

RECOMMENDED HOLE LAYOUT
TOLERANCE: ±0.05[.002] UNLESS OTHERWISE NOTED

NOTES:


- 1 MATERIALS:
CONTACT: COPPER ALLOY, 0.004572[.000180] MIN TIN PLATE
OVER 0.00127[.000050] MIN NICKEL.
INSULATOR: PPS, 40% GLASS FILLED, UL 94V-O

- 2 DATE CODE (PER BELOW) TO BE LASER CODED
AND CENTERED ON THIS SURFACE.



3. UL RECOGNITION E320916.

C



B

A

PART NO.	POS.	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"
1571541-1	44	22.61 [.890]	16.76 [.660]	12.70 [.500]	17.78 [.700]
1571541-2	52	25.15 [.990]	19.30 [.760]	15.24 [.600]	20.32 [.800]
1571541-3	68	30.23 [1.190]	24.38 [.960]	20.32 [.800]	25.40 [1.000]
1571541-4	84	35.31 [1.390]	29.46 [1.160]	25.40 [1.000]	30.48 [1.200]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MURREN 26AUG2003	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK K. WRIGHT 24APR03				
		APVD K. WRIGHT 24APR03	NAME OUTLINE DRAWING PLCC SOCKET			
		PRODUCT SPEC 108-38000				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=1571541	RESTRICTED TO -
MATERIAL 1		FINISH 1	WEIGHT	SCALE 2:1	SHEET 1 of 1	REV D1
CUSTOMER DRAWING						