


Capacitor, film, 2.2 uF, +/-5% Tol, -55/+125C, General Purpose, 50VDC@85C, Lead Spacing=5 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.2	+0.3
H	11	+0.1
T	6	+0.2
S	5	+/-0.4
F	0.6	+/-0.05
H0	18.5	+/-0.5

Notes:

-L,H,T are nominal dimensions and do not imply a minimum.

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	2.2 uF
Rated Temperature:	85C
Voltage @ rated temp:	50VDC
Voltage AC:	30VAC
Tolerance:	+/-5%
Body Type:	Radial Box
Dielectric:	Metallized Polyester (Stacked)
Application:	General Purpose
Sub Application:	AEC-Q200
Temperature Range:	-55/+125C
Dissipation Factor @ 1 kHz:	0.8%
Dissipation Factor @ 10 kHz:	1.2%
Insulation Resistance:	454.54 MOhm
Inductance:	7 nH
Maximum dVdT:	200 v/us

Packaging Specifications	
Package Kind:	Ammo
Package Size:	360x340x59
Package Quantity:	1400