


MBRF2535CT THRU MBRF2560CT

SCHOTTKY ISOLATED PLASTIC RECTIFIER

Reverse Voltage - 35 to 60 Volts Forward Current - 30.0 Amperes


ITO-220AB



Dimensions in inches and (millimeters)

FEATURES

- ◆ Isolated plastic package has Underwriters Laboratory Flammability Classifications 94V-0
- ◆ Dual rectifier construction, positive center-tap
- ◆ Metal silicon junction, majority carrier conduction
- ◆ Low power loss, high efficiency
- ◆ High current capability, low forward voltage drop
- ◆ High surge capability
- ◆ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- ◆ Guardring for overvoltage protection
- ◆ High temperature soldering guaranteed: 250°C/10 seconds, 0.25" (6.35mm) from case



MECHANICAL DATA

Case: ITO-220AB fully overmolded plastic body

Terminals: Lead solderable per MIL-STD-750, Method 2026

Polarity: As marked

Mounting Position: Any

Weight: 0.08 ounce, 2.24 grams

Mounting Torque: 5 in. - lbs. max.

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

	SYMBOLS	MBRF2535CT	MBRF2545CT	MBRF2550CT	MBRF2560CT	UNITS
Maximum repetitive peak reverse voltage	VRRM	35	45	50	60	Volts
Maximum working peak reverse voltage	VRWM	35	45	50	60	Volts
Maximum DC blocking voltage	VDC	35	45	50	60	Volts
Maximum average forward rectified current at TC=130°C	l(AV)	30.0				Amps
Peak repetitive forward current per leg at TC=130°C (rated VR, square wave, 20 KHz)	lFRM	30.0				Amps
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	lFSM	150.0				Amps
Peak repetitive reverse surge current (NOTE 1)	IRRM	1.0		0.5		Amps
Maximum instantaneous forward voltage IF=15.0A ,TC=25°C per leg at: (NOTE 2)	VF	-		0.75		Volts
IF=15.0A ,TC=25°C		-		0.65		
IF= 30A, TC=25°C		0.82		-		
IF= 30A, TC=125°C		0.73		-		
Maximum instantaneous reverse current at rated DC blocking voltage per leg (NOTE 2)	IR	TC=25°C 0.2		1.0		mA
TC=125°C		40.0		50.0		
Maximum thermal resistance (NOTE 3)	ReJC	4.5				°C/W
Voltage rate of change (rated VR)	dv/dt	10,000				V/μs
Operating junction temperature range	TJ	-65 to +150				°C
Storage temperature range	TSTG	-65 to +175				°C
RMS Isolation voltage from terminals to heatsink with RH ≤ 30%	VISOL	4500 (NOTE 4) 3500 (NOTE 5) 1500 (NOTE 6)				Volts

NOTES: (1) 2.0μs pulse width, $f=1.0\text{ KHz}$

(2) Pulse test: 300μs pulse width, 1% duty cycle

(3) Thermal resistance from junction to case per leg

(4) Clip mounting (on case), where lead does not overlap heatsink with 0.110" offset.

(5) Clip mounting (on case), where leads do overlap heatsink.

(6) Screw mounting with 4-40 screw, where washer diameter is $\leq 4.9\text{ mm}$ (0.19").

RATINGS AND CHARACTERISTIC CURVES MBRF2535CT THRU MBRF2560CT

FIG. 1 - FORWARD CURRENT DERATING CURVE




FIG. 3 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 5 - TYPICAL JUNCTION CAPACITANCE PER LEG




FIG. 2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 4 - TYPICAL REVERSE CHARACTERISTICS PER LEG




FIG. 6 - TYPICAL TRANSIENT THERMAL IMPEDANCE PER LEG

