





Copyright FCI.



NOTES:

- 1-Material:phosphor bronze,thickness 0.20
- 2-Finish on contact area:see table
finish on termination:bright tin over nickel
- 3-Wire range:20 to 24 AWG
- 4-Max outer dia of wire insulator:1.73 mm
- 5-Current carrying capacity per contact:
5.Amps max when crimped to #20 AWG
5 Amps max when crimped to #22 AWG
3 Amps max when crimped to #24 AWG
- 6-After 5 insertions into connector,
contact retention must be 5 pounds axial load min
- 7-When contact is crimped to 20 AWG,the insulation
support crimped height must be 1.78 mm max to ensure
a proper insertion into housing
- 8-Reel should be continuous without any contacts
missing in between
- 9-Packaging:Reel of 400 contacts

NOTE : ROHS INFORMATION


The LF products meet European union directives and other
country regulations as described in GS-22-008

Terminations plating spec : 2um Nickel min + 2um Sn min

Packaging Spec : see GS-14-920

PULL PART	
86563006067LF	0.4μ Au / GXT
86563006067	0.4μ Au / GXT
86563006065LF	0.76μ Au / GXT
86563006065	0.76μ Au / GXT
PART NUMBER	Plating

rev	ecn no	dr	date
C	LS06-196	MPE	27/11/2006
D	LS08-0127	MPE	2008/05/13
E	109-0152	AMR	2009-07-27
F	110-0070	AMR	2010-03-09
G	111-0003	AMR	2011-01-06
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		 mm			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	C JARRY	28/01/97	ANGULAR LINEAR		0.X		±0.3		size A3		Scale 10:1	
Eng					0.XX		±0.1					
Chr					0° ±2°		0.XXX		±0.05		ECN 111-0003	
Appr			Product family 8656					Spec ref				
			title CRIMP CONTACTS				dwg no C01-8656-1532				Rev. G	
			catalog no -				CUSTOMER			sheet 1 of 1		