




4

3

2


1

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER 0G3B-0119-01	06FEB2002	EZ	DB



284515-3 AS SHOWN

87.5	25	2-284515-5
84.0	24	2-284515-4
80.5	23	2-284515-3
77.0	22	2-284515-2
73.5	21	2-284515-1
70.0	20	2-284515-0
66.5	19	1-284515-9
63.0	18	1-284515-8
59.5	17	1-284515-7
56.0	16	1-284515-6
52.5	15	1-284515-5
49.0	14	1-284515-4
45.5	13	1-284515-3
42.0	12	1-284515-2
38.5	11	1-284515-1
35.0	10	1-284515-0
31.5	9	284515-9
28.0	8	284515-8
24.5	7	284515-7
21.0	6	284515-6
17.5	5	284515-5
14.0	4	284515-4
10.5	3	284515-3
7.0	2	284515-2
DIM A	NO OF POS	PART NUMBER



- 1


MATERIALS AND FINISH
HOUSING : PA 6.6, UL 94-V0, COLOR GREEN
TERMINAL : PHOSPHOR BRONZE, TIN PLATED
- 2

END-TO-END STACKABLE W/INTERLOCK WITHOUT
LOSS OF CENTERLINE SPACING
- 3

SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS
- 4

NOT CUMULATIVE TOLERANCE

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.3
1 PLC ±.3
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±2

FINISH

DWN 06FEB2002
E. ZANOLINI
CHK 06FEB2002
E. ZANOLINI
APVD 06FEB2002
D. BIEVENOUR

PRODUCT SPEC
108-20166
APPLICATION SPEC
114-20079
WEIGHT
-

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608

NAME
TERMINAL BLOCK, HEADER ASSEMBLY
STRAIGHT, OPEN ENDS
STACKING W/INTERLOCK, 3.5mm PITCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-284515

RESTRICTED TO
-

SCALE
4:1

SHEET
1

OF
1

REV
B